

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929908

Luminaire Tested: DFN2DS-4P3F0-050DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929908
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P3F0-050DS935-RLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3655.0 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.07' x L: 3.07' x H: 0')
CIE Type: Direct

Input Watts (W): 51.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929908

CATALOG NUMBER: DFN2DS-4P3F0-050DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P929908

CATALOG NUMBER: DFN2DS-4P3F0-050DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2025	2025	2025
5°	2033	2000	2011
10°	2017	1967	1950
15°	1994	1909	1854
20°	1962	1826	1734
25°	1929	1731	1618
30°	1884	1634	1469
35°	1839	1528	1338
40°	1794	1419	1187
45°	1742	1296	1050
50°	1688	1172	915
55°	1633	1038	786
60°	1569	898	653
65°	1496	754	594
70°	1409	621	546
75°	1303	567	510
80°	1150	506	465
85°	904	399	399

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1742 cd/sqm

TEST NUMBER: P929908

CATALOG NUMBER: DFN2DS-4P3F0-050DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.6	4.6
10°-20°	457.2	12.5
20°-30°	641.9	17.6
30°-40°	699.8	19.1
40°-50°	643.2	17.6
50°-60°	505.1	13.8
60°-70°	328.8	9.0
70°-80°	169.3	4.6
80°-90°	43.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1265.8	34.6
0°-40°	1965.5	53.8
0°-60°	3113.8	85.2
0°-90°	3655.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3655.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1777	1769	1748	1763	1758	169
15°	1690	1673	1618	1588	1571	476
25°	1534	1483	1377	1311	1287	706
35°	1322	1240	1099	997	962	827
45°	1081	973	804	690	651	835
55°	822	696	523	426	396	734
65°	555	425	280	225	220	550
75°	296	183	129	117	116	313
85°	69	35	30	30	30	83
90°	0	0	0	0	0	

TEST NUMBER: P929908

CATALOG NUMBER: DFN2DS-4P3F0-050DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1777.2	1777.2	1777.2	1777.2	1777.2
2.5°	1785.2	1777.2	1759.5	1775.6	1772.4
5°	1777.2	1769.2	1748.2	1762.7	1757.9
7.5°	1762.7	1753.1	1730.6	1736.9	1728.9
10°	1743.4	1732.1	1700.0	1695.1	1685.5
12.5°	1719.3	1704.9	1661.3	1651.8	1634.0
15°	1690.3	1672.6	1618.0	1587.5	1571.4
17.5°	1656.5	1630.8	1563.2	1527.9	1502.1
20°	1618.0	1585.8	1505.3	1465.3	1429.8
22.5°	1576.2	1539.1	1445.8	1391.2	1367.1
25°	1534.3	1482.8	1376.7	1310.8	1286.6
27.5°	1484.5	1429.8	1312.4	1236.8	1199.8
30°	1431.5	1370.2	1241.6	1159.6	1116.1
32.5°	1380.0	1305.9	1174.2	1077.6	1037.3
35°	1322.1	1240.0	1098.6	997.2	961.7
37.5°	1265.7	1177.3	1027.8	916.7	876.6
40°	1206.2	1109.8	953.7	839.5	797.7
42.5°	1145.2	1042.2	879.8	760.7	720.6
45°	1080.8	973.0	804.2	689.9	651.3
47.5°	1019.7	905.6	731.9	617.6	582.2
50°	952.2	838.0	661.1	550.0	516.3
52.5°	886.1	765.5	593.5	487.4	456.8
55°	821.8	696.3	522.6	426.2	395.7
57.5°	755.9	627.3	460.0	370.0	344.2
60°	688.3	559.7	394.0	312.1	286.3
62.5°	622.5	493.8	337.7	260.6	247.8
65°	554.9	424.6	279.8	225.2	220.3
67.5°	490.5	360.3	225.2	197.8	193.0
70°	423.0	297.6	186.5	170.5	164.0
72.5°	358.7	239.6	156.0	143.2	139.9
75°	295.9	183.3	128.7	117.4	115.8
77.5°	233.2	130.2	101.4	94.9	91.6
80°	175.3	93.3	77.1	70.8	70.8
82.5°	122.2	62.8	53.1	49.8	49.8
85°	69.1	35.3	30.5	30.5	30.5
87.5°	25.8	12.8	12.8	11.3	11.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929908

CATALOG NUMBER: DFN2DS-4P3F0-050DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.69	15.21	14.05	15.52	15.84	9.65	11.17	10.01	11.48	11.80
	3H	15.45	16.82	15.83	17.14	17.51	10.91	12.28	11.29	12.61	12.97
	4H	16.12	17.40	16.52	17.75	18.13	11.41	12.70	11.81	13.04	13.42
	6H	16.61	17.79	17.02	18.16	18.55	11.80	12.98	12.21	13.34	13.74
	8H	16.77	17.90	17.20	18.29	18.69	11.92	13.05	12.35	13.44	13.84
	12H	16.88	17.95	17.31	18.34	18.77	12.00	13.08	12.43	13.46	13.89
4H	2H	13.79	15.07	14.19	15.42	15.80	10.34	11.62	10.74	11.97	12.35
	3H	15.72	16.79	16.13	17.19	17.59	11.79	12.85	12.20	13.25	13.65
	4H	16.47	17.43	16.91	17.85	18.28	12.39	13.34	12.82	13.76	14.20
	6H	17.07	17.90	17.52	18.34	18.80	12.87	13.71	13.33	14.15	14.61
	8H	17.28	18.06	17.74	18.50	18.97	13.04	13.81	13.50	14.26	14.72
	12H	17.43	18.13	17.92	18.61	19.08	13.15	13.85	13.63	14.33	14.80
8H	4H	16.50	17.28	16.96	17.72	18.19	12.74	13.52	13.20	13.96	14.43
	6H	17.14	17.78	17.63	18.27	18.75	13.33	13.97	13.82	14.46	14.94
	8H	17.39	17.96	17.90	18.47	18.96	13.55	14.12	14.06	14.63	15.12
	12H	17.59	18.10	18.10	18.59	19.16	13.73	14.24	14.24	14.73	15.29
12H	4H	16.48	17.18	16.96	17.66	18.13	12.78	13.48	13.26	13.96	14.43
	6H	17.12	17.69	17.63	18.20	18.69	13.39	13.97	13.90	14.48	14.96
	8H	17.40	17.91	17.91	18.40	18.97	13.66	14.17	14.17	14.66	15.23