

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929985

Luminaire Tested: DFN2DS-4P4F0-060DS830-FLL

Issue Date: 11/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P929985  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)  
Test Lab: INNOVATION CENTER  
Issue Date: 11/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DS-4P4F0-060DS830-FLL  
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5595.4 lumens  
Efficiency: N/A  
Efficacy: 90.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')  
CIE Type: Direct

Input Watts (W): 62  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9933  
Total Harmonic Distortion (THDi): 0.066  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P929985

CATALOG NUMBER: DFN2DS-4P4F0-060DS830-FLL

### Luminous Intensity Polar Plot



TEST NUMBER: P929985

CATALOG NUMBER: DFN2DS-4P4F0-060DS830-FLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 109 | 104 | 100 | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 92  |  | 94  | 91  | 89  |  | 90  |
| 2   | 99  | 91  | 85  | 79  | 97  | 89  | 83  | 78  | 86  | 81  | 76  |  | 83  | 78  | 74  |  | 80  |
| 3   | 91  | 80  | 72  | 66  | 88  | 79  | 71  | 65  | 76  | 69  | 64  |  | 73  | 68  | 63  |  | 71  |
| 4   | 83  | 71  | 63  | 56  | 81  | 70  | 62  | 56  | 68  | 61  | 55  |  | 65  | 59  | 54  |  | 63  |
| 5   | 77  | 64  | 55  | 49  | 75  | 63  | 55  | 48  | 61  | 53  | 48  |  | 59  | 52  | 47  |  | 57  |
| 6   | 71  | 58  | 49  | 43  | 69  | 57  | 48  | 42  | 55  | 48  | 42  |  | 53  | 47  | 42  |  | 52  |
| 7   | 66  | 52  | 44  | 38  | 64  | 52  | 43  | 38  | 50  | 43  | 37  |  | 49  | 42  | 37  |  | 47  |
| 8   | 61  | 48  | 40  | 34  | 60  | 47  | 39  | 34  | 46  | 39  | 33  |  | 45  | 38  | 33  |  | 44  |
| 9   | 57  | 44  | 36  | 30  | 56  | 43  | 36  | 30  | 42  | 35  | 30  |  | 41  | 35  | 30  |  | 40  |
| 10  | 54  | 41  | 33  | 28  | 53  | 40  | 33  | 28  | 39  | 32  | 27  |  | 38  | 32  | 27  |  | 37  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 1427 | 1427 | 1427 |
| 5°  | 1432 | 1412 | 1420 |
| 10° | 1424 | 1397 | 1404 |
| 15° | 1406 | 1379 | 1378 |
| 20° | 1381 | 1352 | 1351 |
| 25° | 1356 | 1319 | 1319 |
| 30° | 1324 | 1288 | 1277 |
| 35° | 1295 | 1251 | 1233 |
| 40° | 1257 | 1214 | 1191 |
| 45° | 1220 | 1178 | 1149 |
| 50° | 1180 | 1140 | 1099 |
| 55° | 1139 | 1096 | 1055 |
| 60° | 1092 | 1043 | 1004 |
| 65° | 1042 | 990  | 945  |
| 70° | 979  | 926  | 883  |
| 75° | 890  | 853  | 832  |
| 80° | 791  | 766  | 727  |
| 85° | 645  | 614  | 551  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1220 cd/sqm

TEST NUMBER: P929985

CATALOG NUMBER: DFN2DS-4P4F0-060DS830-FLL

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 207.0  | 3.7       |
| 10°-20°   | 582.4  | 10.4      |
| 20°-30°   | 855.9  | 15.3      |
| 30°-40°   | 994.1  | 17.8      |
| 40°-50°   | 992.8  | 17.7      |
| 50°-60°   | 865.7  | 15.5      |
| 60°-70°   | 639.9  | 11.4      |
| 70°-80°   | 362.1  | 6.5       |
| 80°-90°   | 95.6   | 1.7       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1645.3 | 29.4      |
| 0°-40°    | 2639.3 | 47.2      |
| 0°-60°    | 4497.9 | 80.4      |
| 0°-90°    | 5595.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 5595.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 2199 | 2199  | 2199 | 2199  | 2199 |      |
| 5°  | 2199 | 2191  | 2168 | 2184  | 2180 | 209  |
| 15° | 2094 | 2081  | 2053 | 2062  | 2051 | 590  |
| 25° | 1895 | 1878  | 1842 | 1846  | 1842 | 872  |
| 35° | 1635 | 1614  | 1580 | 1567  | 1556 | 1021 |
| 45° | 1330 | 1315  | 1284 | 1260  | 1252 | 1027 |
| 55° | 1007 | 994   | 969  | 943   | 933  | 900  |
| 65° | 679  | 666   | 645  | 626   | 615  | 671  |
| 75° | 355  | 351   | 340  | 328   | 332  | 379  |
| 85° | 87   | 85    | 82   | 76    | 74   | 102  |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P929985

CATALOG NUMBER: DFN2DS-4P4F0-060DS830-FLL

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 2199.2 | 2199.2 | 2199.2 | 2199.2 | 2199.2 |
| 2.5°  | 2212.0 | 2201.5 | 2178.1 | 2199.2 | 2195.1 |
| 5°    | 2199.2 | 2190.9 | 2167.5 | 2184.4 | 2180.4 |
| 7.5°  | 2184.4 | 2171.9 | 2148.5 | 2165.6 | 2161.3 |
| 10°   | 2161.3 | 2146.5 | 2121.1 | 2138.0 | 2131.7 |
| 12.5° | 2129.5 | 2116.9 | 2091.5 | 2102.1 | 2097.8 |
| 15°   | 2093.5 | 2081.0 | 2053.4 | 2061.9 | 2051.4 |
| 17.5° | 2049.1 | 2036.6 | 2009.0 | 2019.5 | 2009.0 |
| 20°   | 2000.4 | 1987.9 | 1958.2 | 1964.5 | 1956.3 |
| 22.5° | 1952.0 | 1932.9 | 1905.3 | 1905.3 | 1901.1 |
| 25°   | 1894.7 | 1878.0 | 1842.0 | 1846.0 | 1842.0 |
| 27.5° | 1831.2 | 1816.5 | 1789.0 | 1782.8 | 1772.3 |
| 30°   | 1768.0 | 1750.9 | 1719.3 | 1713.0 | 1704.5 |
| 32.5° | 1700.2 | 1687.7 | 1653.8 | 1641.0 | 1632.5 |
| 35°   | 1634.7 | 1613.6 | 1579.7 | 1566.9 | 1556.4 |
| 37.5° | 1560.7 | 1541.6 | 1507.8 | 1492.9 | 1482.3 |
| 40°   | 1484.6 | 1467.5 | 1433.7 | 1414.9 | 1406.3 |
| 42.5° | 1410.6 | 1393.5 | 1359.9 | 1338.6 | 1326.0 |
| 45°   | 1330.3 | 1315.4 | 1283.6 | 1260.5 | 1251.9 |
| 47.5° | 1251.9 | 1237.1 | 1203.3 | 1179.9 | 1167.3 |
| 50°   | 1169.4 | 1158.8 | 1129.3 | 1099.6 | 1089.0 |
| 52.5° | 1089.0 | 1074.3 | 1046.8 | 1023.6 | 1008.8 |
| 55°   | 1006.7 | 993.9  | 968.6  | 943.2  | 932.7  |
| 57.5° | 924.2  | 913.6  | 886.0  | 860.7  | 852.1  |
| 60°   | 841.6  | 833.3  | 803.7  | 780.4  | 774.0  |
| 62.5° | 761.2  | 746.4  | 725.3  | 704.2  | 695.8  |
| 65°   | 678.9  | 666.2  | 645.1  | 626.0  | 615.4  |
| 67.5° | 594.3  | 583.6  | 564.7  | 549.9  | 541.4  |
| 70°   | 516.0  | 507.5  | 488.4  | 473.6  | 465.3  |
| 72.5° | 435.7  | 427.2  | 416.6  | 401.9  | 395.5  |
| 75°   | 355.1  | 351.2  | 340.3  | 327.8  | 332.1  |
| 77.5° | 283.4  | 274.9  | 270.5  | 264.3  | 258.0  |
| 80°   | 211.6  | 209.3  | 205.1  | 198.8  | 194.5  |
| 82.5° | 143.8  | 143.8  | 141.8  | 133.3  | 133.3  |
| 85°   | 86.6   | 84.6   | 82.5   | 76.0   | 74.0   |
| 87.5° | 38.2   | 33.9   | 29.6   | 23.4   | 21.1   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

TEST NUMBER: P929985

CATALOG NUMBER: DFN2DS-4P4F0-060DS830-FLL

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |       |       |       |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7   | 0.5   | 0.5   | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3   | 0.5   | 0.3   | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2   | 0.2   | 0.2   | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |       |       |       |       |
| X=2H            | Y=2H | 12.52            | 14.13 | 12.88 | 14.44 | 14.76 | 12.07          | 13.68 | 12.44 | 14.00 | 14.31 |
|                 | 3H   | 14.27            | 15.72 | 14.64 | 16.05 | 16.41 | 13.78          | 15.23 | 14.15 | 15.56 | 15.92 |
|                 | 4H   | 14.91            | 16.28 | 15.31 | 16.63 | 17.01 | 14.42          | 15.79 | 14.82 | 16.14 | 16.51 |
|                 | 6H   | 15.38            | 16.65 | 15.79 | 17.02 | 17.41 | 14.88          | 16.15 | 15.29 | 16.51 | 16.91 |
|                 | 8H   | 15.53            | 16.74 | 15.95 | 17.13 | 17.52 | 15.02          | 16.23 | 15.45 | 16.62 | 17.02 |
|                 | 12H  | 15.62            | 16.78 | 16.05 | 17.16 | 17.59 | 15.10          | 16.26 | 15.53 | 16.65 | 17.07 |
| 4H              | 2H   | 13.08            | 14.45 | 13.48 | 14.79 | 15.17 | 12.73          | 14.09 | 13.12 | 14.44 | 14.82 |
|                 | 3H   | 15.05            | 16.20 | 15.46 | 16.60 | 17.00 | 14.65          | 15.79 | 15.06 | 16.19 | 16.59 |
|                 | 4H   | 15.83            | 16.87 | 16.26 | 17.28 | 17.72 | 15.41          | 16.44 | 15.84 | 16.86 | 17.29 |
|                 | 6H   | 16.43            | 17.33 | 16.88 | 17.77 | 18.23 | 15.99          | 16.90 | 16.45 | 17.34 | 17.80 |
|                 | 8H   | 16.62            | 17.46 | 17.08 | 17.90 | 18.37 | 16.18          | 17.02 | 16.64 | 17.47 | 17.93 |
|                 | 12H  | 16.75            | 17.51 | 17.23 | 17.98 | 18.45 | 16.30          | 17.05 | 16.78 | 17.53 | 18.00 |
| 8H              | 4H   | 16.10            | 16.95 | 16.56 | 17.39 | 17.86 | 15.73          | 16.57 | 16.19 | 17.02 | 17.48 |
|                 | 6H   | 16.82            | 17.52 | 17.31 | 18.01 | 18.48 | 16.44          | 17.14 | 16.93 | 17.63 | 18.10 |
|                 | 8H   | 17.08            | 17.71 | 17.59 | 18.21 | 18.70 | 16.68          | 17.32 | 17.19 | 17.82 | 18.31 |
|                 | 12H  | 17.28            | 17.83 | 17.78 | 18.32 | 18.89 | 16.86          | 17.42 | 17.37 | 17.91 | 18.47 |
| 12H             | 4H   | 16.13            | 16.89 | 16.61 | 17.36 | 17.83 | 15.76          | 16.52 | 16.24 | 17.00 | 17.47 |
|                 | 6H   | 16.86            | 17.49 | 17.37 | 18.00 | 18.49 | 16.49          | 17.13 | 17.00 | 17.63 | 18.12 |
|                 | 8H   | 17.18            | 17.73 | 17.68 | 18.22 | 18.79 | 16.80          | 17.36 | 17.31 | 17.85 | 18.41 |

END OF REPORT