

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930003

Luminaire Tested: DFN2DS-4P4F0-070DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930003
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-070DS830-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6528.1 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 74.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930003

CATALOG NUMBER: DFN2DS-4P4F0-070DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930003

CATALOG NUMBER: DFN2DS-4P4F0-070DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1664	1664	1664
5°	1671	1647	1657
10°	1661	1630	1638
15°	1640	1609	1607
20°	1611	1577	1576
25°	1582	1538	1538
30°	1545	1503	1490
35°	1510	1460	1438
40°	1467	1416	1389
45°	1424	1374	1340
50°	1377	1330	1282
55°	1328	1278	1231
60°	1274	1217	1172
65°	1216	1155	1102
70°	1142	1081	1030
75°	1039	995	971
80°	922	894	848
85°	753	718	643

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1424 cd/sqm

TEST NUMBER: P930003

CATALOG NUMBER: DFN2DS-4P4F0-070DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.5	3.7
10°-20°	679.5	10.4
20°-30°	998.5	15.3
30°-40°	1159.7	17.8
40°-50°	1158.3	17.7
50°-60°	1010.0	15.5
60°-70°	746.6	11.4
70°-80°	422.4	6.5
80°-90°	111.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1919.5	29.4
0°-40°	3079.2	47.2
0°-60°	5247.5	80.4
0°-90°	6528.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6528.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2566	2566	2566	2566	2566	
5°	2566	2556	2529	2548	2544	244
15°	2442	2428	2396	2406	2393	688
25°	2211	2191	2149	2154	2149	1017
35°	1907	1883	1843	1828	1816	1191
45°	1552	1535	1498	1471	1461	1198
55°	1174	1160	1130	1100	1088	1050
65°	792	777	753	730	718	783
75°	414	410	397	382	387	442
85°	101	99	96	89	86	119
90°	0	0	0	0	0	

TEST NUMBER: P930003

CATALOG NUMBER: DFN2DS-4P4F0-070DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2565.7	2565.7	2565.7	2565.7	2565.7
2.5°	2580.7	2568.4	2541.1	2565.7	2561.0
5°	2565.7	2556.1	2528.9	2548.5	2543.8
7.5°	2548.5	2533.8	2506.6	2526.5	2521.5
10°	2521.5	2504.2	2474.6	2494.3	2487.0
12.5°	2484.3	2469.7	2440.2	2452.4	2447.4
15°	2442.5	2427.8	2395.6	2405.6	2393.2
17.5°	2390.6	2376.0	2343.8	2356.1	2343.8
20°	2333.8	2319.2	2284.6	2292.0	2282.3
22.5°	2277.3	2255.1	2222.8	2222.8	2217.8
25°	2210.6	2190.9	2149.1	2153.8	2149.1
27.5°	2136.5	2119.2	2087.3	2079.9	2067.6
30°	2062.7	2042.7	2005.9	1998.5	1988.6
32.5°	1983.6	1969.0	1929.4	1914.5	1904.5
35°	1907.2	1882.6	1843.0	1828.1	1815.8
37.5°	1820.8	1798.6	1759.0	1741.8	1729.4
40°	1732.1	1712.2	1672.6	1650.7	1640.7
42.5°	1645.7	1625.8	1586.5	1561.6	1547.0
45°	1551.9	1534.7	1497.5	1470.6	1460.6
47.5°	1460.6	1443.3	1403.8	1376.5	1361.9
50°	1364.3	1352.0	1317.4	1282.9	1270.6
52.5°	1270.6	1253.3	1221.4	1194.2	1176.8
55°	1174.5	1159.6	1130.0	1100.4	1088.1
57.5°	1078.2	1065.9	1033.7	1004.1	994.2
60°	981.8	972.1	937.7	910.4	903.1
62.5°	888.1	870.9	846.3	821.7	811.7
65°	792.1	777.2	752.6	730.3	718.0
67.5°	693.4	680.9	658.8	641.6	631.6
70°	602.0	592.1	569.8	552.6	542.9
72.5°	508.3	498.4	486.1	468.8	461.5
75°	414.4	409.7	397.1	382.5	387.4
77.5°	330.6	320.7	315.7	308.3	301.1
80°	246.8	244.3	239.3	231.9	226.9
82.5°	167.8	167.8	165.4	155.5	155.5
85°	101.1	98.7	96.4	88.7	86.4
87.5°	44.5	39.6	34.6	27.2	24.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930003

CATALOG NUMBER: DFN2DS-4P4F0-070DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.05	14.66	13.42	14.98	15.29	12.61	14.22	12.97	14.53	14.85
	3H	14.80	16.26	15.18	16.58	16.94	14.31	15.77	14.69	16.09	16.45
	4H	15.45	16.82	15.85	17.17	17.54	14.95	16.32	15.35	16.67	17.05
	6H	15.92	17.19	16.33	17.55	17.94	15.42	16.69	15.83	17.05	17.44
	8H	16.06	17.27	16.49	17.66	18.06	15.56	16.77	15.98	17.16	17.56
	12H	16.15	17.31	16.58	17.69	18.12	15.64	16.80	16.07	17.18	17.61
4H	2H	13.61	14.98	14.01	15.33	15.71	13.26	14.63	13.66	14.98	15.35
	3H	15.59	16.73	16.00	17.13	17.53	15.18	16.33	15.59	16.73	17.13
	4H	16.37	17.40	16.80	17.81	18.25	15.94	16.98	16.37	17.39	17.83
	6H	16.96	17.87	17.42	18.31	18.76	16.53	17.43	16.98	17.87	18.33
	8H	17.15	18.00	17.61	18.44	18.91	16.71	17.56	17.17	18.00	18.47
	12H	17.28	18.04	17.76	18.52	18.99	16.83	17.59	17.31	18.07	18.54
8H	4H	16.64	17.48	17.10	17.93	18.39	16.26	17.11	16.72	17.55	18.02
	6H	17.35	18.06	17.85	18.54	19.02	16.97	17.67	17.46	18.16	18.64
	8H	17.61	18.24	18.12	18.75	19.24	17.22	17.85	17.73	18.36	18.84
	12H	17.81	18.37	18.32	18.86	19.42	17.40	17.96	17.91	18.45	19.01
12H	4H	16.66	17.42	17.14	17.90	18.37	16.30	17.06	16.78	17.54	18.00
	6H	17.40	18.03	17.91	18.54	19.02	17.03	17.66	17.54	18.17	18.65
	8H	17.71	18.27	18.22	18.76	19.32	17.33	17.89	17.84	18.38	18.94