

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930024

Luminaire Tested: DFN2DS-4P4F0-080DS835-RLL

Issue Date: 11/20/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P930024  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)  
Test Lab: INNOVATION CENTER  
Issue Date: 11/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DS-4P4F0-080DS835-RLL  
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6800.0 lumens  
Efficiency: N/A  
Efficacy: 78.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 86.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9971  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P930024  
CATALOG NUMBER: DFN2DS-4P4F0-080DS835-RLL

### Luminous Intensity Polar Plot





TEST NUMBER: P930024

CATALOG NUMBER: DFN2DS-4P4F0-080DS835-RLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	88	88	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	76	76	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	66	66	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	57	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	51	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	45	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	41	41	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	37	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	34	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	31	31	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2145	2145	2145
5°	2153	2118	2130
10°	2137	2084	2066
15°	2112	2022	1963
20°	2078	1934	1836
25°	2043	1833	1713
30°	1995	1730	1556
35°	1948	1619	1417
40°	1901	1503	1257
45°	1845	1373	1112
50°	1788	1241	969
55°	1729	1100	833
60°	1662	951	691
65°	1585	799	629
70°	1493	658	579
75°	1380	600	540
80°	1218	536	492
85°	957	423	423

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1845 cd/sqm



TEST NUMBER: P930024  
 CATALOG NUMBER: DFN2DS-4P4F0-080DS835-RLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	309.9	4.6
10°-20°	850.7	12.5
20°-30°	1194.3	17.6
30°-40°	1301.9	19.1
40°-50°	1196.6	17.6
50°-60°	939.7	13.8
60°-70°	611.7	9.0
70°-80°	314.9	4.6
80°-90°	80.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2354.9	34.6
0°-40°	3656.8	53.8
0°-60°	5793.1	85.2
0°-90°	6800.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6800.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3306	3306	3306	3306	3306	
5°	3306	3292	3252	3279	3270	314
15°	3145	3112	3010	2953	2924	886
25°	2855	2759	2561	2439	2394	1313
35°	2460	2307	2044	1855	1789	1540
45°	2011	1810	1496	1284	1212	1553
55°	1529	1296	972	793	736	1366
65°	1032	790	521	419	410	1024
75°	550	341	239	218	216	582
85°	129	66	57	57	57	154
90°	0	0	0	0	0	



TEST NUMBER: P930024

CATALOG NUMBER: DFN2DS-4P4F0-080DS835-RLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3306.4	3306.4	3306.4	3306.4	3306.4
2.5°	3321.3	3306.4	3273.4	3303.5	3297.5
5°	3306.4	3291.5	3252.4	3279.4	3270.5
7.5°	3279.4	3261.6	3219.7	3231.5	3216.5
10°	3243.5	3222.6	3162.9	3153.7	3135.9
12.5°	3198.8	3171.8	3090.8	3073.0	3040.0
15°	3144.8	3111.8	3010.2	2953.4	2923.5
17.5°	3081.9	3034.0	2908.3	2842.6	2794.6
20°	3010.2	2950.2	2800.7	2726.1	2660.0
22.5°	2932.4	2863.5	2689.9	2588.3	2543.5
25°	2854.6	2758.8	2561.3	2438.8	2393.7
27.5°	2761.9	2660.0	2441.6	2301.0	2232.1
30°	2663.2	2549.2	2309.9	2157.5	2076.5
32.5°	2567.3	2429.6	2184.5	2004.8	1929.9
35°	2459.7	2307.0	2043.8	1855.3	1789.2
37.5°	2354.9	2190.2	1912.1	1705.4	1630.8
40°	2244.2	2064.8	1774.3	1561.9	1484.1
42.5°	2130.5	1939.1	1636.8	1415.3	1340.6
45°	2010.8	1810.2	1496.2	1283.5	1211.8
47.5°	1897.2	1684.8	1361.6	1148.9	1083.2
50°	1771.4	1559.1	1229.9	1023.2	960.6
52.5°	1648.6	1424.1	1104.1	906.7	849.9
55°	1528.9	1295.6	972.4	793.0	736.2
57.5°	1406.4	1167.0	855.9	688.3	640.3
60°	1280.6	1041.3	733.0	580.6	532.7
62.5°	1158.1	918.7	628.3	484.8	461.0
65°	1032.4	789.8	520.6	419.1	409.8
67.5°	912.7	670.2	419.1	367.9	359.1
70°	787.0	553.7	347.0	317.1	305.1
72.5°	667.3	445.7	290.2	266.4	260.3
75°	550.5	341.0	239.4	218.4	215.6
77.5°	434.0	242.2	188.6	176.5	170.5
80°	326.0	173.7	143.5	131.7	131.7
82.5°	227.3	116.8	98.7	92.7	92.7
85°	128.6	65.7	56.8	56.8	56.8
87.5°	47.9	23.8	23.8	21.0	21.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P930024  
 CATALOG NUMBER: DFN2DS-4P4F0-080DS835-RL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.89	15.41	14.25	15.72	16.04	9.85	11.37	10.21	11.68	12.00
	3H	15.65	17.02	16.03	17.34	17.71	11.11	12.48	11.49	12.80	13.17
	4H	16.32	17.60	16.72	17.95	18.33	11.61	12.89	12.01	13.24	13.62
	6H	16.81	17.99	17.22	18.36	18.75	11.99	13.18	12.41	13.54	13.94
	8H	16.97	18.10	17.40	18.49	18.89	12.12	13.25	12.55	13.64	14.04
	12H	17.08	18.15	17.51	18.54	18.96	12.20	13.28	12.63	13.66	14.09
4H	2H	13.99	15.27	14.39	15.62	16.00	10.54	11.82	10.94	12.17	12.55
	3H	15.92	16.99	16.33	17.39	17.79	11.99	13.05	12.40	13.45	13.85
	4H	16.67	17.63	17.11	18.05	18.48	12.58	13.54	13.02	13.96	14.40
	6H	17.26	18.10	17.72	18.54	19.00	13.07	13.90	13.53	14.35	14.81
	8H	17.48	18.26	17.94	18.70	19.17	13.23	14.01	13.70	14.46	14.92
	12H	17.63	18.33	18.11	18.81	19.28	13.35	14.05	13.83	14.52	15.00
8H	4H	16.70	17.47	17.16	17.92	18.39	12.94	13.72	13.40	14.16	14.63
	6H	17.33	17.98	17.83	18.47	18.95	13.53	14.17	14.02	14.66	15.14
	8H	17.58	18.16	18.10	18.67	19.16	13.75	14.32	14.26	14.83	15.32
	12H	17.79	18.30	18.30	18.79	19.36	13.93	14.44	14.43	14.93	15.49
12H	4H	16.68	17.38	17.16	17.85	18.33	12.98	13.68	13.46	14.15	14.63
	6H	17.32	17.89	17.83	18.40	18.89	13.59	14.17	14.10	14.68	15.16
	8H	17.60	18.11	18.11	18.60	19.17	13.86	14.37	14.37	14.86	15.43