

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929974

Luminaire Tested: DFN2DS-4P4F0-050DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929974
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-050DS850-RLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4713.3 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 50.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929974

CATALOG NUMBER: DFN2DS-4P4F0-050DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P929974

CATALOG NUMBER: DFN2DS-4P4F0-050DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1487	1487	1487
5°	1492	1468	1476
10°	1481	1444	1432
15°	1464	1401	1361
20°	1440	1340	1273
25°	1416	1271	1188
30°	1383	1199	1078
35°	1350	1122	982
40°	1317	1041	871
45°	1279	951	770
50°	1239	860	672
55°	1199	762	577
60°	1152	659	479
65°	1098	554	436
70°	1035	456	401
75°	956	416	374
80°	844	372	341
85°	664	293	293

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1279 cd/sqm

TEST NUMBER: P929974

CATALOG NUMBER: DFN2DS-4P4F0-050DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	4.6
10°-20°	589.6	12.5
20°-30°	827.8	17.6
30°-40°	902.4	19.1
40°-50°	829.4	17.6
50°-60°	651.3	13.8
60°-70°	424.0	9.0
70°-80°	218.2	4.6
80°-90°	55.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1632.2	34.6
0°-40°	2534.6	53.8
0°-60°	4015.3	85.2
0°-90°	4713.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4713.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	2292	2281	2254	2273	2267	217
15°	2180	2157	2086	2047	2026	614
25°	1979	1912	1775	1690	1659	910
35°	1705	1599	1417	1286	1240	1067
45°	1394	1255	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	716	548	361	290	284	709
75°	382	236	166	151	149	404
85°	89	46	39	39	39	107
90°	0	0	0	0	0	

TEST NUMBER: P929974

CATALOG NUMBER: DFN2DS-4P4F0-050DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.7	2291.7	2291.7	2291.7	2291.7
2.5°	2302.1	2291.7	2268.9	2289.8	2285.5
5°	2291.7	2281.4	2254.4	2273.0	2266.9
7.5°	2273.0	2260.7	2231.6	2239.8	2229.4
10°	2248.2	2233.6	2192.3	2185.9	2173.5
12.5°	2217.1	2198.5	2142.4	2130.1	2107.1
15°	2179.7	2156.9	2086.5	2047.1	2026.4
17.5°	2136.2	2103.0	2015.8	1970.2	1937.0
20°	2086.5	2044.9	1941.2	1889.5	1843.7
22.5°	2032.6	1984.8	1864.5	1794.0	1763.0
25°	1978.6	1912.1	1775.3	1690.3	1659.1
27.5°	1914.4	1843.7	1692.3	1594.9	1547.2
30°	1845.9	1767.0	1601.1	1495.4	1439.3
32.5°	1779.5	1684.0	1514.1	1389.6	1337.7
35°	1704.9	1599.1	1416.6	1285.9	1240.2
37.5°	1632.2	1518.1	1325.4	1182.1	1130.4
40°	1555.5	1431.2	1229.8	1082.6	1028.7
42.5°	1476.7	1344.0	1134.5	980.9	929.2
45°	1393.8	1254.7	1037.0	889.6	839.8
47.5°	1314.9	1167.8	943.8	796.4	750.8
50°	1227.9	1080.6	852.5	709.2	665.8
52.5°	1142.7	987.1	765.3	628.5	589.1
55°	1059.8	898.0	673.9	549.6	510.3
57.5°	974.8	808.9	593.2	477.1	443.8
60°	887.6	721.7	508.0	402.5	369.2
62.5°	802.7	636.8	435.5	336.0	319.5
65°	715.5	547.5	360.9	290.4	284.1
67.5°	632.6	464.6	290.4	255.1	248.9
70°	545.5	383.7	240.5	219.8	211.5
72.5°	462.6	309.0	201.2	184.6	180.4
75°	381.6	236.3	165.9	151.4	149.4
77.5°	300.8	167.9	130.8	122.3	118.1
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.6	81.0	68.4	64.2	64.2
85°	89.2	45.6	39.4	39.4	39.4
87.5°	33.3	16.5	16.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929974

CATALOG NUMBER: DFN2DS-4P4F0-050DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.61	14.13	12.98	14.45	14.76	8.57	10.10	8.94	10.41	10.72
	3H	14.38	15.74	14.76	16.07	16.43	9.84	11.20	10.22	11.53	11.89
	4H	15.04	16.33	15.44	16.67	17.05	10.34	11.62	10.74	11.97	12.35
	6H	15.53	16.72	15.95	17.08	17.47	10.72	11.90	11.13	12.27	12.66
	8H	15.70	16.83	16.13	17.21	17.62	10.85	11.97	11.27	12.36	12.76
	12H	15.80	16.88	16.23	17.26	17.69	10.93	12.00	11.36	12.39	12.82
4H	2H	12.72	14.00	13.12	14.35	14.72	9.27	10.55	9.67	10.90	11.28
	3H	14.65	15.71	15.06	16.11	16.51	10.71	11.78	11.12	12.17	12.58
	4H	15.40	16.36	15.83	16.77	17.21	11.31	12.27	11.74	12.68	13.12
	6H	15.99	16.82	16.45	17.27	17.73	11.80	12.63	12.26	13.07	13.53
	8H	16.21	16.98	16.67	17.43	17.89	11.96	12.74	12.42	13.18	13.65
	12H	16.36	17.05	16.84	17.53	18.00	12.08	12.77	12.56	13.25	13.72
8H	4H	15.42	16.20	15.89	16.65	17.11	11.67	12.44	12.13	12.89	13.35
	6H	16.06	16.70	16.56	17.19	17.67	12.25	12.89	12.75	13.39	13.86
	8H	16.31	16.89	16.83	17.40	17.89	12.47	13.05	12.99	13.56	14.05
	12H	16.52	17.03	17.03	17.52	18.08	12.65	13.16	13.16	13.65	14.22
12H	4H	15.41	16.10	15.89	16.58	17.05	11.71	12.40	12.19	12.88	13.35
	6H	16.04	16.62	16.56	17.13	17.62	12.31	12.89	12.83	13.40	13.89
	8H	16.33	16.84	16.84	17.33	17.89	12.59	13.10	13.10	13.59	14.15