

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930013

Luminaire Tested: DFN2DS-4P4F0-070DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-070DS930-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5648.0 lumens
Efficiency: N/A
Efficacy: 75.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 74.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930013

CATALOG NUMBER: DFN2DS-4P4F0-070DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930013

CATALOG NUMBER: DFN2DS-4P4F0-070DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1440	1440	1440
5°	1446	1425	1433
10°	1437	1410	1417
15°	1419	1392	1391
20°	1394	1365	1363
25°	1369	1331	1331
30°	1337	1300	1289
35°	1307	1263	1244
40°	1269	1226	1202
45°	1232	1189	1159
50°	1191	1150	1109
55°	1149	1106	1065
60°	1102	1053	1014
65°	1052	999	954
70°	988	935	891
75°	899	861	840
80°	798	773	733
85°	651	621	556

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1232 cd/sqm

TEST NUMBER: P930013

CATALOG NUMBER: DFN2DS-4P4F0-070DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.9	3.7
10°-20°	587.9	10.4
20°-30°	863.9	15.3
30°-40°	1003.4	17.8
40°-50°	1002.1	17.7
50°-60°	873.8	15.5
60°-70°	646.0	11.4
70°-80°	365.5	6.5
80°-90°	96.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1660.7	29.4
0°-40°	2664.1	47.2
0°-60°	4540.1	80.4
0°-90°	5648.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5648.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2220	2220	2220	2220	2220	
5°	2220	2212	2188	2205	2201	211
15°	2113	2100	2073	2081	2071	595
25°	1913	1896	1859	1863	1859	880
35°	1650	1629	1594	1582	1571	1030
45°	1343	1328	1296	1272	1264	1036
55°	1016	1003	978	952	941	908
65°	685	672	651	632	621	678
75°	358	354	344	331	335	383
85°	87	85	83	77	75	103
90°	0	0	0	0	0	

TEST NUMBER: P930013

CATALOG NUMBER: DFN2DS-4P4F0-070DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2219.8	2219.8	2219.8	2219.8	2219.8
2.5°	2232.8	2222.1	2198.5	2219.8	2215.7
5°	2219.8	2211.5	2187.9	2204.9	2200.8
7.5°	2204.9	2192.2	2168.6	2185.9	2181.6
10°	2181.6	2166.6	2141.0	2158.0	2151.7
12.5°	2149.4	2136.8	2111.2	2121.8	2117.5
15°	2113.2	2100.5	2072.6	2081.3	2070.6
17.5°	2068.3	2055.7	2027.8	2038.5	2027.8
20°	2019.2	2006.5	1976.6	1983.0	1974.6
22.5°	1970.3	1951.0	1923.2	1923.2	1918.8
25°	1912.6	1895.5	1859.3	1863.4	1859.3
27.5°	1848.4	1833.5	1805.9	1799.5	1788.8
30°	1784.6	1767.3	1735.5	1729.1	1720.5
32.5°	1716.1	1703.5	1669.3	1656.4	1647.8
35°	1650.0	1628.8	1594.5	1581.7	1571.0
37.5°	1575.3	1556.1	1521.8	1506.9	1496.3
40°	1498.5	1481.3	1447.1	1428.1	1419.5
42.5°	1423.8	1406.6	1372.6	1351.1	1338.4
45°	1342.7	1327.8	1295.6	1272.3	1263.7
47.5°	1263.7	1248.7	1214.5	1191.0	1178.3
50°	1180.4	1169.7	1139.8	1109.9	1099.3
52.5°	1099.3	1084.4	1056.7	1033.2	1018.2
55°	1016.1	1003.3	977.7	952.1	941.4
57.5°	932.8	922.2	894.3	868.7	860.2
60°	849.5	841.1	811.3	787.7	781.3
62.5°	768.4	753.5	732.2	710.9	702.3
65°	685.3	672.4	651.1	631.9	621.2
67.5°	599.9	589.1	570.0	555.1	546.5
70°	520.9	512.3	493.0	478.1	469.7
72.5°	439.8	431.2	420.5	405.6	399.3
75°	358.5	354.4	343.5	330.9	335.2
77.5°	286.1	277.4	273.1	266.7	260.5
80°	213.5	211.3	207.0	200.7	196.3
82.5°	145.2	145.2	143.1	134.6	134.6
85°	87.4	85.4	83.4	76.8	74.7
87.5°	38.5	34.2	29.9	23.6	21.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930013

CATALOG NUMBER: DFN2DS-4P4F0-070DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.55	14.16	12.91	14.47	14.79	12.11	13.72	12.47	14.03	14.34
	3H	14.30	15.75	14.68	16.08	16.44	13.81	15.26	14.19	15.59	15.95
	4H	14.95	16.32	15.34	16.66	17.04	14.45	15.82	14.85	16.17	16.54
	6H	15.42	16.68	15.83	17.05	17.44	14.91	16.18	15.33	16.55	16.94
	8H	15.56	16.77	15.98	17.16	17.56	15.06	16.27	15.48	16.66	17.05
	12H	15.65	16.81	16.08	17.19	17.62	15.14	16.30	15.57	16.68	17.11
4H	2H	13.11	14.48	13.51	14.83	15.20	12.76	14.13	13.16	14.47	14.85
	3H	15.09	16.23	15.50	16.63	17.03	14.68	15.82	15.09	16.22	16.62
	4H	15.86	16.90	16.29	17.31	17.75	15.44	16.47	15.87	16.89	17.32
	6H	16.46	17.36	16.91	17.80	18.26	16.03	16.93	16.48	17.37	17.83
	8H	16.65	17.49	17.11	17.94	18.40	16.21	17.06	16.67	17.50	17.96
	12H	16.78	17.54	17.26	18.02	18.48	16.33	17.09	16.81	17.56	18.03
8H	4H	16.14	16.98	16.60	17.42	17.89	15.76	16.61	16.22	17.05	17.52
	6H	16.85	17.55	17.34	18.04	18.52	16.47	17.17	16.96	17.66	18.13
	8H	17.11	17.74	17.62	18.25	18.73	16.72	17.35	17.23	17.85	18.34
	12H	17.31	17.87	17.82	18.36	18.92	16.90	17.45	17.40	17.94	18.51
12H	4H	16.16	16.92	16.64	17.40	17.87	15.80	16.56	16.28	17.03	17.50
	6H	16.89	17.53	17.40	18.03	18.52	16.53	17.16	17.04	17.66	18.15
	8H	17.21	17.77	17.72	18.26	18.82	16.83	17.39	17.34	17.88	18.44