

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929961

Luminaire Tested: DFN2DS-4P4F0-040DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P929961
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-040DS935-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3405.6 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 39.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929961

CATALOG NUMBER: DFN2DS-4P4F0-040DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P929961

CATALOG NUMBER: DFN2DS-4P4F0-040DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	868	868	868
5°	872	859	864
10°	867	850	855
15°	856	839	839
20°	841	823	822
25°	825	802	802
30°	806	784	777
35°	788	761	750
40°	765	739	725
45°	743	717	699
50°	718	694	669
55°	693	667	642
60°	665	635	611
65°	634	603	575
70°	596	564	537
75°	542	519	507
80°	481	466	442
85°	392	374	336

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 743 cd/sqm

TEST NUMBER: P929961

CATALOG NUMBER: DFN2DS-4P4F0-040DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.0	3.7
10°-20°	354.5	10.4
20°-30°	520.9	15.3
30°-40°	605.0	17.8
40°-50°	604.3	17.7
50°-60°	526.9	15.5
60°-70°	389.5	11.4
70°-80°	220.4	6.5
80°-90°	58.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1001.4	29.4
0°-40°	1606.4	47.2
0°-60°	2737.6	80.4
0°-90°	3405.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3405.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1338	1338	1338	1338	1338	
5°	1338	1333	1319	1330	1327	127
15°	1274	1266	1250	1255	1248	359
25°	1153	1143	1121	1124	1121	531
35°	995	982	962	954	947	621
45°	810	801	781	767	762	625
55°	613	605	590	574	568	548
65°	413	405	393	381	375	409
75°	216	214	207	200	202	231
85°	53	52	50	46	45	62
90°	0	0	0	0	0	

TEST NUMBER: P929961

CATALOG NUMBER: DFN2DS-4P4F0-040DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1338.5	1338.5	1338.5	1338.5	1338.5
2.5°	1346.3	1339.9	1325.7	1338.5	1336.1
5°	1338.5	1333.4	1319.2	1329.5	1327.1
7.5°	1329.5	1321.8	1307.6	1318.0	1315.5
10°	1315.5	1306.4	1291.0	1301.3	1297.4
12.5°	1296.0	1288.4	1273.0	1279.4	1276.8
15°	1274.2	1266.5	1249.8	1254.9	1248.5
17.5°	1247.2	1239.5	1222.7	1229.1	1222.7
20°	1217.5	1209.8	1191.9	1195.7	1190.7
22.5°	1188.0	1176.4	1159.6	1159.6	1157.0
25°	1153.2	1142.9	1121.1	1123.6	1121.1
27.5°	1114.6	1105.5	1088.9	1085.1	1078.7
30°	1076.0	1065.7	1046.4	1042.6	1037.4
32.5°	1034.8	1027.2	1006.5	998.8	993.6
35°	994.9	982.1	961.5	953.7	947.3
37.5°	949.9	938.3	917.6	908.7	902.2
40°	903.6	893.2	872.6	861.1	856.0
42.5°	858.5	848.1	827.7	814.7	807.0
45°	809.6	800.7	781.2	767.2	762.0
47.5°	762.0	752.9	732.4	718.2	710.5
50°	711.7	705.3	687.3	669.3	662.8
52.5°	662.8	653.9	637.2	623.0	614.0
55°	612.8	604.9	589.5	574.0	567.7
57.5°	562.4	556.1	539.2	523.8	518.7
60°	512.2	507.1	489.2	475.0	471.1
62.5°	463.4	454.3	441.5	428.6	423.5
65°	413.2	405.4	392.6	381.0	374.6
67.5°	361.7	355.2	343.7	334.7	329.6
70°	314.1	308.9	297.3	288.3	283.2
72.5°	265.2	260.0	253.6	244.6	240.7
75°	216.2	213.7	207.2	199.5	202.1
77.5°	172.4	167.3	164.7	160.8	157.0
80°	128.7	127.4	124.8	121.0	118.4
82.5°	87.5	87.5	86.3	81.1	81.1
85°	52.7	51.5	50.2	46.3	45.1
87.5°	23.2	20.6	18.1	14.2	12.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P929961

CATALOG NUMBER: DFN2DS-4P4F0-040DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.79	12.40	11.16	12.72	13.03	10.35	11.96	10.71	12.27	12.59
	3H	12.54	14.00	12.92	14.32	14.68	12.05	13.51	12.43	13.83	14.19
	4H	13.19	14.56	13.59	14.91	15.28	12.69	14.06	13.09	14.41	14.79
	6H	13.66	14.93	14.07	15.29	15.68	13.16	14.42	13.57	14.79	15.18
	8H	13.80	15.01	14.23	15.40	15.80	13.30	14.51	13.72	14.90	15.30
	12H	13.89	15.05	14.32	15.43	15.86	13.38	14.54	13.81	14.92	15.35
4H	2H	11.35	12.72	11.75	13.07	13.45	11.00	12.37	11.40	12.72	13.09
	3H	13.33	14.47	13.74	14.87	15.27	12.92	14.07	13.33	14.47	14.87
	4H	14.10	15.14	14.54	15.55	15.99	13.68	14.72	14.11	15.13	15.57
	6H	14.70	15.61	15.15	16.05	16.50	14.27	15.17	14.72	15.61	16.07
	8H	14.89	15.74	15.35	16.18	16.64	14.45	15.30	14.91	15.74	16.21
	12H	15.02	15.78	15.50	16.26	16.73	14.57	15.33	15.05	15.81	16.28
8H	4H	14.38	15.22	14.84	15.67	16.13	14.00	14.85	14.46	15.29	15.76
	6H	15.09	15.79	15.59	16.28	16.76	14.71	15.41	15.20	15.90	16.38
	8H	15.35	15.98	15.86	16.49	16.97	14.96	15.59	15.47	16.10	16.58
	12H	15.55	16.11	16.06	16.60	17.16	15.14	15.70	15.64	16.19	16.75
12H	4H	14.40	15.16	14.88	15.64	16.11	14.04	14.80	14.52	15.27	15.74
	6H	15.14	15.77	15.65	16.28	16.76	14.77	15.40	15.28	15.91	16.39
	8H	15.45	16.01	15.96	16.50	17.06	15.07	15.63	15.58	16.12	16.68

END OF REPORT