

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930033

Luminaire Tested: DFN2DS-4P4F0-080DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-4P4F0-080DS935-FLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6811.2 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 4.07' x L: 4.07' x H: 0')
CIE Type: Direct

Input Watts (W): 86.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930033
CATALOG NUMBER: DFN2DS-4P4F0-080DS935-FLL

Luminous Intensity Polar Plot





TEST NUMBER: P930033

CATALOG NUMBER: DFN2DS-4P4F0-080DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	86	86	86	84
2	99	91	85	79	97	89	83	78	86	81	76	83	78	74	80	76	73	73	73	73	71
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	71	66	62	62	62	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	54	54	54	51
5	77	64	55	49	75	63	55	48	61	53	48	59	52	47	57	51	47	47	47	47	45
6	71	58	49	43	69	57	48	42	55	48	42	53	47	42	52	46	41	41	41	41	39
7	66	52	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37	37	37	37	35
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	33	33	33	31
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	30	30	30	28
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	32	27	27	27	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1737	1737	1737
5°	1743	1718	1728
10°	1733	1701	1709
15°	1712	1679	1677
20°	1681	1646	1644
25°	1651	1605	1605
30°	1612	1568	1554
35°	1576	1523	1500
40°	1530	1478	1450
45°	1486	1433	1398
50°	1437	1387	1338
55°	1386	1334	1284
60°	1329	1269	1222
65°	1269	1205	1150
70°	1191	1128	1074
75°	1084	1038	1013
80°	962	933	885
85°	785	748	671

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1486 cd/sqm



TEST NUMBER: P930033
 CATALOG NUMBER: DFN2DS-4P4F0-080DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.0	3.7
10°-20°	708.9	10.4
20°-30°	1041.8	15.3
30°-40°	1210.0	17.8
40°-50°	1208.5	17.7
50°-60°	1053.8	15.5
60°-70°	779.0	11.4
70°-80°	440.7	6.5
80°-90°	116.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2002.7	29.4
0°-40°	3212.8	47.2
0°-60°	5475.1	80.4
0°-90°	6811.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6811.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2677	2677	2677	2677	2677	
5°	2677	2667	2639	2659	2654	254
15°	2548	2533	2500	2510	2497	718
25°	2306	2286	2242	2247	2242	1061
35°	1990	1964	1923	1907	1895	1243
45°	1619	1601	1562	1534	1524	1250
55°	1225	1210	1179	1148	1135	1096
65°	826	811	785	762	749	817
75°	432	427	414	399	404	462
85°	105	103	100	93	90	124
90°	0	0	0	0	0	



TEST NUMBER: P930033

CATALOG NUMBER: DFN2DS-4P4F0-080DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2677.0	2677.0	2677.0	2677.0	2677.0
2.5°	2692.6	2679.8	2651.4	2677.0	2672.1
5°	2677.0	2666.9	2638.6	2659.0	2654.1
7.5°	2659.0	2643.7	2615.3	2636.1	2630.9
10°	2630.9	2612.9	2582.0	2602.4	2594.9
12.5°	2592.1	2576.8	2545.9	2558.8	2553.6
15°	2548.4	2533.1	2499.5	2509.9	2497.1
17.5°	2494.3	2479.0	2445.4	2458.3	2445.4
20°	2435.1	2419.8	2383.7	2391.4	2381.3
22.5°	2376.1	2352.9	2319.2	2319.2	2314.1
25°	2306.4	2286.0	2242.3	2247.2	2242.3
27.5°	2229.1	2211.1	2177.8	2170.1	2157.3
30°	2152.2	2131.3	2092.9	2085.2	2074.8
32.5°	2069.7	2054.4	2013.1	1997.5	1987.2
35°	1989.9	1964.2	1923.0	1907.4	1894.6
37.5°	1899.7	1876.5	1835.3	1817.3	1804.5
40°	1807.2	1786.4	1745.2	1722.2	1711.8
42.5°	1717.1	1696.3	1655.3	1629.4	1614.1
45°	1619.3	1601.2	1562.4	1534.3	1524.0
47.5°	1524.0	1505.9	1464.7	1436.3	1421.0
50°	1423.5	1410.7	1374.5	1338.5	1325.7
52.5°	1325.7	1307.6	1274.3	1246.0	1227.9
55°	1225.4	1209.8	1179.1	1148.2	1135.3
57.5°	1125.0	1112.2	1078.5	1047.7	1037.2
60°	1024.4	1014.4	978.2	949.9	942.2
62.5°	926.6	908.7	883.0	857.3	846.9
65°	826.5	810.9	785.2	762.0	749.1
67.5°	723.4	710.4	687.4	669.4	659.0
70°	628.1	617.7	594.6	576.5	566.4
72.5°	530.4	520.0	507.1	489.2	481.5
75°	432.3	427.4	414.3	399.0	404.2
77.5°	344.9	334.5	329.4	321.7	314.1
80°	257.6	254.8	249.7	242.0	236.8
82.5°	175.1	175.1	172.6	162.2	162.2
85°	105.4	102.9	100.5	92.6	90.1
87.5°	46.4	41.3	36.0	28.4	25.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P930033
 CATALOG NUMBER: DFN2DS-4P4F0-080DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.20	14.81	13.57	15.13	15.44	12.76	14.37	13.12	14.68	15.00
	3H	14.95	16.41	15.33	16.73	17.09	14.46	15.91	14.84	16.24	16.60
	4H	15.60	16.97	16.00	17.31	17.69	15.10	16.47	15.50	16.82	17.19
	6H	16.07	17.33	16.48	17.70	18.09	15.56	16.83	15.98	17.20	17.59
	8H	16.21	17.42	16.63	17.81	18.21	15.71	16.92	16.13	17.31	17.70
	12H	16.30	17.46	16.73	17.84	18.27	15.79	16.95	16.22	17.33	17.76
4H	2H	13.76	15.13	14.16	15.48	15.85	13.41	14.78	13.81	15.12	15.50
	3H	15.74	16.88	16.15	17.28	17.68	15.33	16.48	15.74	16.87	17.27
	4H	16.51	17.55	16.94	17.96	18.40	16.09	17.12	16.52	17.54	17.97
	6H	17.11	18.01	17.56	18.45	18.91	16.68	17.58	17.13	18.02	18.48
	8H	17.30	18.14	17.76	18.59	19.05	16.86	17.71	17.32	18.15	18.61
	12H	17.43	18.19	17.91	18.67	19.14	16.98	17.74	17.46	18.21	18.68
8H	4H	16.79	17.63	17.25	18.07	18.54	16.41	17.26	16.87	17.70	18.17
	6H	17.50	18.20	17.99	18.69	19.17	17.12	17.82	17.61	18.31	18.79
	8H	17.76	18.39	18.27	18.90	19.38	17.37	18.00	17.88	18.51	18.99
	12H	17.96	18.52	18.47	19.01	19.57	17.55	18.10	18.05	18.59	19.16
12H	4H	16.81	17.57	17.29	18.05	18.52	16.45	17.21	16.93	17.68	18.15
	6H	17.55	18.18	18.05	18.68	19.17	17.18	17.81	17.69	18.32	18.80
	8H	17.86	18.42	18.37	18.91	19.47	17.48	18.04	17.99	18.53	19.09