

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930116

Luminaire Tested: DFN2DS-HX2F0-060DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930116
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-060DS840-RLL
Description: 2 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5105.1 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 61.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930116

CATALOG NUMBER: DFN2DS-HX2F0-060DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930116

CATALOG NUMBER: DFN2DS-HX2F0-060DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5849	5849	5849
5°	5871	5775	5807
10°	5826	5681	5633
15°	5759	5512	5354
20°	5666	5272	5007
25°	5571	4999	4672
30°	5440	4718	4241
35°	5311	4413	3863
40°	5182	4097	3427
45°	5030	3743	3031
50°	4875	3384	2644
55°	4715	2999	2270
60°	4531	2593	1884
65°	4321	2179	1715
70°	4070	1795	1578
75°	3762	1636	1474
80°	3320	1461	1342
85°	2609	1152	1152

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5030 cd/sqm

TEST NUMBER: P930116

CATALOG NUMBER: DFN2DS-HX2F0-060DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.6	4.6
10°-20°	638.6	12.5
20°-30°	896.6	17.6
30°-40°	977.4	19.1
40°-50°	898.3	17.6
50°-60°	705.5	13.8
60°-70°	459.2	9.0
70°-80°	236.4	4.6
80°-90°	60.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1767.9	34.6
0°-40°	2745.3	53.8
0°-60°	4349.1	85.2
0°-90°	5105.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5105.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2482	2482	2482	2482	2482	
5°	2482	2471	2442	2462	2455	235
15°	2361	2336	2260	2217	2195	665
25°	2143	2071	1923	1831	1797	986
35°	1847	1732	1534	1393	1343	1156
45°	1510	1359	1123	964	910	1166
55°	1148	973	730	595	553	1026
65°	775	593	391	315	308	768
75°	413	256	180	164	162	437
85°	96	49	43	43	43	116
90°	0	0	0	0	0	



TEST NUMBER: P930116

CATALOG NUMBER: DFN2DS-HX2F0-060DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2482.3	2482.3	2482.3	2482.3	2482.3
2.5°	2493.5	2482.3	2457.5	2480.1	2475.6
5°	2482.3	2471.1	2441.7	2462.1	2455.4
7.5°	2462.1	2448.6	2417.2	2426.0	2414.8
10°	2435.0	2419.3	2374.6	2367.7	2354.3
12.5°	2401.5	2381.2	2320.4	2307.1	2282.3
15°	2361.0	2336.1	2259.9	2217.2	2194.8
17.5°	2313.8	2277.8	2183.4	2134.0	2098.1
20°	2259.9	2214.8	2102.6	2046.5	1997.0
22.5°	2201.5	2149.7	2019.4	1943.1	1909.5
25°	2143.1	2071.2	1922.9	1830.9	1797.1
27.5°	2073.6	1997.0	1833.0	1727.4	1675.8
30°	1999.4	1913.8	1734.1	1619.7	1559.0
32.5°	1927.4	1824.0	1640.0	1505.1	1448.8
35°	1846.6	1732.0	1534.4	1392.8	1343.2
37.5°	1768.0	1644.2	1435.5	1280.4	1224.3
40°	1684.8	1550.1	1332.0	1172.6	1114.2
42.5°	1599.5	1455.8	1228.8	1062.5	1006.5
45°	1509.6	1359.0	1123.3	963.6	909.7
47.5°	1424.3	1264.9	1022.2	862.6	813.2
50°	1329.9	1170.5	923.3	768.2	721.2
52.5°	1237.6	1069.2	828.9	680.7	638.0
55°	1147.8	972.7	730.0	595.4	552.7
57.5°	1055.9	876.1	642.5	516.7	480.7
60°	961.5	781.8	550.3	435.9	399.9
62.5°	869.5	689.8	471.7	364.0	346.0
65°	775.1	593.0	390.9	314.6	307.7
67.5°	685.2	503.1	314.6	276.3	269.6
70°	590.8	415.6	260.5	238.1	229.0
72.5°	501.0	334.6	217.8	200.0	195.4
75°	413.3	256.0	179.7	164.0	161.9
77.5°	325.8	181.9	141.5	132.5	128.0
80°	244.7	130.3	107.7	98.9	98.9
82.5°	170.7	87.7	74.1	69.6	69.6
85°	96.5	49.3	42.6	42.6	42.6
87.5°	36.0	17.9	17.9	15.7	15.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930116

CATALOG NUMBER: DFN2DS-HX2F0-060DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.37	18.89	17.74	19.21	19.52	13.33	14.85	13.70	15.17	15.48
	3H	19.14	20.50	19.51	20.83	21.19	14.60	15.96	14.97	16.29	16.65
	4H	19.80	21.08	20.20	21.43	21.81	15.10	16.38	15.50	16.73	17.11
	6H	20.29	21.47	20.70	21.84	22.23	15.48	16.66	15.89	17.03	17.42
	8H	20.46	21.58	20.88	21.97	22.37	15.60	16.73	16.03	17.12	17.52
	12H	20.56	21.64	20.99	22.02	22.45	15.69	16.76	16.12	17.15	17.57
4H	2H	17.48	18.76	17.87	19.10	19.48	14.03	15.31	14.43	15.66	16.03
	3H	19.41	20.47	19.82	20.87	21.27	15.47	16.53	15.88	16.93	17.33
	4H	20.16	21.11	20.59	21.53	21.97	16.07	17.03	16.50	17.44	17.88
	6H	20.75	21.58	21.21	22.02	22.48	16.56	17.39	17.02	17.83	18.29
	8H	20.96	21.74	21.43	22.19	22.65	16.72	17.50	17.18	17.94	18.41
	12H	21.12	21.81	21.60	22.29	22.76	16.84	17.53	17.32	18.01	18.48
8H	4H	20.18	20.96	20.65	21.40	21.87	16.42	17.20	16.89	17.65	18.11
	6H	20.82	21.46	21.32	21.95	22.43	17.01	17.65	17.51	18.14	18.62
	8H	21.07	21.65	21.58	22.16	22.64	17.23	17.81	17.75	18.32	18.81
	12H	21.27	21.78	21.78	22.28	22.84	17.41	17.92	17.92	18.41	18.98
12H	4H	20.17	20.86	20.65	21.34	21.81	16.47	17.16	16.95	17.64	18.11
	6H	20.80	21.38	21.31	21.89	22.38	17.07	17.65	17.59	18.16	18.65
	8H	21.08	21.59	21.59	22.09	22.65	17.35	17.86	17.86	18.35	18.91