

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930087

Luminaire Tested: DFN2DS-HX2F0-040DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930087
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-040DS935-FLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3405.6 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930087

CATALOG NUMBER: DFN2DS-HX2F0-040DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930087

CATALOG NUMBER: DFN2DS-HX2F0-040DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3154	3154	3154
5°	3166	3120	3139
10°	3147	3089	3104
15°	3108	3049	3045
20°	3053	2989	2986
25°	2998	2915	2915
30°	2927	2847	2822
35°	2862	2766	2725
40°	2779	2684	2633
45°	2698	2603	2539
50°	2609	2519	2429
55°	2517	2422	2332
60°	2414	2305	2220
65°	2304	2189	2088
70°	2164	2048	1951
75°	1968	1886	1840
80°	1746	1693	1607
85°	1425	1357	1219

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2698 cd/sqm

TEST NUMBER: P930087

CATALOG NUMBER: DFN2DS-HX2F0-040DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.0	3.7
10°-20°	354.5	10.4
20°-30°	520.9	15.3
30°-40°	605.0	17.8
40°-50°	604.3	17.7
50°-60°	526.9	15.5
60°-70°	389.5	11.4
70°-80°	220.4	6.5
80°-90°	58.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1001.4	29.4
0°-40°	1606.4	47.2
0°-60°	2737.6	80.4
0°-90°	3405.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3405.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1338	1338	1338	1338	1338	
5°	1338	1333	1319	1330	1327	127
15°	1274	1266	1250	1255	1248	359
25°	1153	1143	1121	1124	1121	531
35°	995	982	962	954	947	621
45°	810	801	781	767	762	625
55°	613	605	590	574	568	548
65°	413	405	393	381	375	409
75°	216	214	207	200	202	231
85°	53	52	50	46	45	62
90°	0	0	0	0	0	

TEST NUMBER: P930087

CATALOG NUMBER: DFN2DS-HX2F0-040DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1338.5	1338.5	1338.5	1338.5	1338.5
2.5°	1346.3	1339.9	1325.7	1338.5	1336.1
5°	1338.5	1333.4	1319.2	1329.5	1327.1
7.5°	1329.5	1321.8	1307.6	1318.0	1315.5
10°	1315.5	1306.4	1291.0	1301.3	1297.4
12.5°	1296.0	1288.4	1273.0	1279.4	1276.8
15°	1274.2	1266.5	1249.8	1254.9	1248.5
17.5°	1247.2	1239.5	1222.7	1229.1	1222.7
20°	1217.5	1209.8	1191.9	1195.7	1190.7
22.5°	1188.0	1176.4	1159.6	1159.6	1157.0
25°	1153.2	1142.9	1121.1	1123.6	1121.1
27.5°	1114.6	1105.5	1088.9	1085.1	1078.7
30°	1076.0	1065.7	1046.4	1042.6	1037.4
32.5°	1034.8	1027.2	1006.5	998.8	993.6
35°	994.9	982.1	961.5	953.7	947.3
37.5°	949.9	938.3	917.6	908.7	902.2
40°	903.6	893.2	872.6	861.1	856.0
42.5°	858.5	848.1	827.7	814.7	807.0
45°	809.6	800.7	781.2	767.2	762.0
47.5°	762.0	752.9	732.4	718.2	710.5
50°	711.7	705.3	687.3	669.3	662.8
52.5°	662.8	653.9	637.2	623.0	614.0
55°	612.8	604.9	589.5	574.0	567.7
57.5°	562.4	556.1	539.2	523.8	518.7
60°	512.2	507.1	489.2	475.0	471.1
62.5°	463.4	454.3	441.5	428.6	423.5
65°	413.2	405.4	392.6	381.0	374.6
67.5°	361.7	355.2	343.7	334.7	329.6
70°	314.1	308.9	297.3	288.3	283.2
72.5°	265.2	260.0	253.6	244.6	240.7
75°	216.2	213.7	207.2	199.5	202.1
77.5°	172.4	167.3	164.7	160.8	157.0
80°	128.7	127.4	124.8	121.0	118.4
82.5°	87.5	87.5	86.3	81.1	81.1
85°	52.7	51.5	50.2	46.3	45.1
87.5°	23.2	20.6	18.1	14.2	12.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930087

CATALOG NUMBER: DFN2DS-HX2F0-040DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.27	16.88	15.64	17.20	17.51	14.83	16.44	15.19	16.75	17.07
	3H	17.02	18.48	17.40	18.80	19.17	16.53	17.99	16.91	18.31	18.67
	4H	17.67	19.04	18.07	19.39	19.76	17.17	18.54	17.57	18.89	19.27
	6H	18.14	19.41	18.55	19.77	20.16	17.64	18.91	18.05	19.27	19.66
	8H	18.28	19.49	18.71	19.88	20.28	17.78	18.99	18.20	19.38	19.78
	12H	18.37	19.53	18.80	19.91	20.34	17.86	19.02	18.29	19.40	19.83
4H	2H	15.83	17.20	16.23	17.55	17.93	15.48	16.85	15.88	17.20	17.57
	3H	17.81	18.96	18.22	19.35	19.75	17.40	18.55	17.81	18.95	19.35
	4H	18.59	19.62	19.02	20.03	20.47	18.16	19.20	18.59	19.61	20.05
	6H	19.18	20.09	19.64	20.53	20.98	18.75	19.65	19.20	20.09	20.55
	8H	19.37	20.22	19.83	20.66	21.13	18.93	19.78	19.39	20.22	20.69
	12H	19.50	20.26	19.98	20.74	21.21	19.05	19.81	19.53	20.29	20.76
8H	4H	18.86	19.71	19.32	20.15	20.61	18.48	19.33	18.95	19.77	20.24
	6H	19.57	20.28	20.07	20.76	21.24	19.19	19.89	19.69	20.38	20.86
	8H	19.83	20.46	20.34	20.97	21.46	19.44	20.07	19.95	20.58	21.06
	12H	20.03	20.59	20.54	21.08	21.64	19.62	20.18	20.13	20.67	21.23
12H	4H	18.88	19.64	19.36	20.12	20.59	18.52	19.28	19.00	19.76	20.23
	6H	19.62	20.25	20.13	20.76	21.24	19.25	19.88	19.76	20.39	20.87
	8H	19.93	20.49	20.44	20.98	21.54	19.55	20.11	20.06	20.60	21.16