

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930105

Luminaire Tested: DFN2DS-HX2F0-050DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930105
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX2F0-050DS935-FLL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4257.0 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 2.3' x L: 1.99' x H: 0')
CIE Type: Direct

Input Watts (W): 49.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930105

CATALOG NUMBER: DFN2DS-HX2F0-050DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930105

CATALOG NUMBER: DFN2DS-HX2F0-050DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3942	3942	3942
5°	3957	3900	3924
10°	3934	3861	3880
15°	3885	3811	3807
20°	3816	3736	3732
25°	3747	3643	3643
30°	3659	3559	3528
35°	3577	3457	3406
40°	3474	3355	3291
45°	3372	3254	3173
50°	3261	3149	3037
55°	3146	3027	2915
60°	3017	2882	2775
65°	2880	2736	2610
70°	2705	2560	2439
75°	2460	2357	2300
80°	2185	2117	2008
85°	1782	1698	1522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3372 cd/sqm

TEST NUMBER: P930105

CATALOG NUMBER: DFN2DS-HX2F0-050DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	3.7
10°-20°	443.1	10.4
20°-30°	651.1	15.3
30°-40°	756.3	17.8
40°-50°	755.3	17.7
50°-60°	658.6	15.5
60°-70°	486.9	11.4
70°-80°	275.5	6.5
80°-90°	72.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1251.7	29.4
0°-40°	2008.0	47.2
0°-60°	3421.9	80.4
0°-90°	4257.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4257.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1673	1673	1673	1673	1673	
5°	1673	1667	1649	1662	1659	159
15°	1593	1583	1562	1569	1561	449
25°	1442	1429	1401	1404	1401	663
35°	1244	1228	1202	1192	1184	777
45°	1012	1001	976	959	952	781
55°	766	756	737	718	710	685
65°	516	507	491	476	468	511
75°	270	267	259	249	253	288
85°	66	64	63	58	56	77
90°	0	0	0	0	0	

TEST NUMBER: P930105

CATALOG NUMBER: DFN2DS-HX2F0-050DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1673.1	1673.1	1673.1	1673.1	1673.1
2.5°	1682.8	1674.8	1657.1	1673.1	1670.1
5°	1673.1	1666.9	1649.0	1661.9	1658.9
7.5°	1661.9	1652.3	1634.6	1647.6	1644.3
10°	1644.3	1633.1	1613.8	1626.5	1621.8
12.5°	1620.1	1610.5	1591.3	1599.3	1596.0
15°	1592.7	1583.2	1562.2	1568.7	1560.6
17.5°	1558.9	1549.4	1528.4	1536.4	1528.4
20°	1521.9	1512.4	1489.9	1494.6	1488.3
22.5°	1485.0	1470.5	1449.5	1449.5	1446.3
25°	1441.5	1428.7	1401.4	1404.5	1401.4
27.5°	1393.2	1381.9	1361.1	1356.3	1348.3
30°	1345.0	1332.1	1308.1	1303.2	1296.8
32.5°	1293.5	1284.0	1258.2	1248.5	1242.0
35°	1243.6	1227.6	1201.8	1192.1	1184.1
37.5°	1187.3	1172.9	1147.1	1135.8	1127.8
40°	1129.5	1116.5	1090.7	1076.4	1069.9
42.5°	1073.2	1060.2	1034.6	1018.3	1008.8
45°	1012.0	1000.8	976.5	959.0	952.4
47.5°	952.4	941.2	915.5	897.7	888.1
50°	889.7	881.7	859.1	836.6	828.5
52.5°	828.5	817.3	796.4	778.7	767.5
55°	765.9	756.2	736.8	717.6	709.6
57.5°	703.0	695.1	674.1	654.8	648.3
60°	640.3	634.0	611.5	593.7	588.9
62.5°	579.2	567.9	551.9	535.8	529.3
65°	516.5	506.8	490.7	476.3	468.2
67.5°	452.2	444.0	429.7	418.4	411.9
70°	392.6	386.1	371.6	360.3	354.1
72.5°	331.5	325.0	317.0	305.7	300.9
75°	270.2	267.1	258.9	249.4	252.7
77.5°	215.6	209.1	205.9	201.1	196.3
80°	161.0	159.3	156.0	151.3	148.0
82.5°	109.4	109.4	107.8	101.4	101.4
85°	65.9	64.3	62.8	57.9	56.3
87.5°	29.0	25.8	22.5	17.7	16.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930105

CATALOG NUMBER: DFN2DS-HX2F0-050DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.05	17.66	16.41	17.97	18.29	15.60	17.21	15.97	17.53	17.84
	3H	17.80	19.25	18.18	19.58	19.94	17.31	18.76	17.68	19.09	19.45
	4H	18.44	19.81	18.84	20.16	20.54	17.95	19.32	18.35	19.67	20.04
	6H	18.91	20.18	19.33	20.55	20.94	18.41	19.68	18.82	20.05	20.44
	8H	19.06	20.27	19.48	20.66	21.06	18.55	19.77	18.98	20.15	20.55
	12H	19.15	20.31	19.58	20.69	21.12	18.64	19.80	19.06	20.18	20.61
4H	2H	16.61	17.98	17.01	18.33	18.70	16.26	17.63	16.65	17.97	18.35
	3H	18.58	19.73	18.99	20.13	20.53	18.18	19.32	18.59	19.72	20.12
	4H	19.36	20.40	19.79	20.81	21.25	18.94	19.97	19.37	20.39	20.82
	6H	19.96	20.86	20.41	21.30	21.76	19.52	20.43	19.98	20.87	21.33
	8H	20.15	20.99	20.61	21.44	21.90	19.71	20.56	20.17	21.00	21.46
	12H	20.28	21.04	20.76	21.51	21.98	19.83	20.59	20.31	21.06	21.53
8H	4H	19.63	20.48	20.09	20.92	21.39	19.26	20.11	19.72	20.55	21.01
	6H	20.35	21.05	20.84	21.54	22.02	19.97	20.67	20.46	21.16	21.63
	8H	20.61	21.24	21.12	21.74	22.23	20.22	20.85	20.73	21.35	21.84
	12H	20.81	21.36	21.31	21.86	22.42	20.39	20.95	20.90	21.44	22.00
12H	4H	19.66	20.42	20.14	20.90	21.36	19.30	20.06	19.78	20.53	21.00
	6H	20.39	21.03	20.90	21.53	22.02	20.03	20.66	20.53	21.16	21.65
	8H	20.71	21.27	21.21	21.76	22.32	20.33	20.89	20.84	21.38	21.94