

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930191

Luminaire Tested: DFN2DS-HX3F0-060DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930191
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-060DS927-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4704.5 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 61.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930191

CATALOG NUMBER: DFN2DS-HX3F0-060DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930191

CATALOG NUMBER: DFN2DS-HX3F0-060DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2142	2142	2142
5°	2150	2119	2132
10°	2137	2098	2108
15°	2111	2070	2068
20°	2073	2030	2027
25°	2036	1979	1979
30°	1988	1934	1917
35°	1944	1878	1850
40°	1887	1823	1788
45°	1832	1768	1724
50°	1772	1711	1650
55°	1709	1644	1584
60°	1639	1565	1508
65°	1565	1487	1418
70°	1470	1391	1325
75°	1336	1280	1250
80°	1187	1150	1091
85°	968	922	828

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1832 cd/sqm

TEST NUMBER: P930191

CATALOG NUMBER: DFN2DS-HX3F0-060DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.0	3.7
10°-20°	489.7	10.4
20°-30°	719.6	15.3
30°-40°	835.8	17.8
40°-50°	834.7	17.7
50°-60°	727.9	15.5
60°-70°	538.1	11.4
70°-80°	304.4	6.5
80°-90°	80.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1383.3	29.4
0°-40°	2219.1	47.2
0°-60°	3781.7	80.4
0°-90°	4704.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4704.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1849	1849	1849	1849	1849	
5°	1849	1842	1822	1837	1833	176
15°	1760	1750	1726	1734	1725	496
25°	1593	1579	1549	1552	1549	733
35°	1374	1357	1328	1317	1308	858
45°	1118	1106	1079	1060	1053	863
55°	846	836	814	793	784	757
65°	571	560	542	526	517	564
75°	299	295	286	276	279	319
85°	73	71	69	64	62	86
90°	0	0	0	0	0	

TEST NUMBER: P930191

CATALOG NUMBER: DFN2DS-HX3F0-060DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1849.0	1849.0	1849.0	1849.0	1849.0
2.5°	1859.8	1850.9	1831.3	1849.0	1845.6
5°	1849.0	1842.0	1822.4	1836.6	1833.2
7.5°	1836.6	1826.0	1806.4	1820.7	1817.2
10°	1817.2	1804.7	1783.3	1797.5	1792.2
12.5°	1790.4	1779.8	1758.5	1767.3	1763.8
15°	1760.1	1749.6	1726.4	1733.6	1724.7
17.5°	1722.8	1712.3	1689.1	1697.9	1689.1
20°	1681.9	1671.4	1646.4	1651.7	1644.7
22.5°	1641.2	1625.1	1601.9	1601.9	1598.3
25°	1593.0	1578.9	1548.7	1552.1	1548.7
27.5°	1539.6	1527.2	1504.2	1498.9	1490.1
30°	1486.5	1472.1	1445.6	1440.3	1433.0
32.5°	1429.5	1418.9	1390.4	1379.7	1372.5
35°	1374.4	1356.7	1328.2	1317.4	1308.5
37.5°	1312.2	1296.1	1267.7	1255.2	1246.3
40°	1248.2	1233.9	1205.4	1189.6	1182.4
42.5°	1185.9	1171.6	1143.3	1125.4	1114.8
45°	1118.5	1105.9	1079.2	1059.8	1052.6
47.5°	1052.6	1040.1	1011.7	992.1	981.4
50°	983.2	974.3	949.4	924.5	915.6
52.5°	915.6	903.2	880.1	860.6	848.2
55°	846.4	835.6	814.3	793.0	784.2
57.5°	777.0	768.2	745.0	723.7	716.4
60°	707.6	700.6	675.7	656.1	650.8
62.5°	640.0	627.6	609.8	592.1	585.0
65°	570.8	560.1	542.4	526.3	517.4
67.5°	499.7	490.6	474.8	462.4	455.2
70°	433.9	426.7	410.7	398.2	391.2
72.5°	366.3	359.2	350.3	337.9	332.6
75°	298.6	295.3	286.1	275.6	279.2
77.5°	238.2	231.1	227.5	222.2	216.9
80°	177.9	176.0	172.4	167.1	163.5
82.5°	120.9	120.9	119.2	112.1	112.1
85°	72.8	71.1	69.4	63.9	62.3
87.5°	32.1	28.5	24.9	19.6	17.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930191

CATALOG NUMBER: DFN2DS-HX3F0-060DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.93	15.54	14.29	15.85	16.17	13.49	15.10	13.85	15.41	15.72
	3H	15.68	17.13	16.06	17.46	17.82	15.19	16.64	15.57	16.97	17.33
	4H	16.33	17.69	16.72	18.04	18.42	15.83	17.20	16.23	17.55	17.92
	6H	16.79	18.06	17.21	18.43	18.82	16.29	17.56	16.70	17.93	18.32
	8H	16.94	18.15	17.36	18.54	18.94	16.43	17.65	16.86	18.03	18.43
	12H	17.03	18.19	17.46	18.57	19.00	16.52	17.68	16.95	18.06	18.49
4H	2H	14.49	15.86	14.89	16.21	16.58	14.14	15.51	14.54	15.85	16.23
	3H	16.46	17.61	16.87	18.01	18.41	16.06	17.20	16.47	17.60	18.00
	4H	17.24	18.28	17.67	18.69	19.13	16.82	17.85	17.25	18.27	18.70
	6H	17.84	18.74	18.29	19.18	19.64	17.41	18.31	17.86	18.75	19.21
	8H	18.03	18.87	18.49	19.32	19.78	17.59	18.44	18.05	18.88	19.34
	12H	18.16	18.92	18.64	19.39	19.86	17.71	18.47	18.19	18.94	19.41
8H	4H	17.51	18.36	17.98	18.80	19.27	17.14	17.99	17.60	18.43	18.89
	6H	18.23	18.93	18.72	19.42	19.90	17.85	18.55	18.34	19.04	19.51
	8H	18.49	19.12	19.00	19.63	20.11	18.10	18.73	18.61	19.23	19.72
	12H	18.69	19.25	19.19	19.74	20.30	18.27	18.83	18.78	19.32	19.88
12H	4H	17.54	18.30	18.02	18.78	19.25	17.18	17.94	17.66	18.41	18.88
	6H	18.27	18.91	18.78	19.41	19.90	17.91	18.54	18.41	19.04	19.53
	8H	18.59	19.15	19.09	19.64	20.20	18.21	18.77	18.72	19.26	19.82

END OF REPORT