

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930246

Luminaire Tested: DFN2DS-HX3F0-090DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930246
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-090DS927-RLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6058.8 lumens
Efficiency: N/A
Efficacy: 62.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930246
CATALOG NUMBER: DFN2DS-HX3F0-090DS927-RL

Luminous Intensity Polar Plot





TEST NUMBER: P930246

CATALOG NUMBER: DFN2DS-HX3F0-090DS927-RL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	88	88	88	86
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	76	76	76	74
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66	66	66	66	64
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57	57	57	57	55
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51	51	51	51	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	45	45	45	43
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	41	41	41	39
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37	37	37	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34	34	34	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	31	31	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3413	3413	3413
5°	3426	3370	3388
10°	3399	3315	3286
15°	3360	3216	3124
20°	3306	3076	2922
25°	3251	2917	2726
30°	3174	2753	2475
35°	3099	2575	2254
40°	3024	2391	2000
45°	2935	2184	1769
50°	2844	1975	1542
55°	2751	1750	1325
60°	2643	1513	1100
65°	2521	1271	1001
70°	2375	1047	921
75°	2195	955	860
80°	1938	853	783
85°	1522	673	673

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2935 cd/sqm



TEST NUMBER: P930246

CATALOG NUMBER: DFN2DS-HX3F0-090DS927-RL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.1	4.6
10°-20°	758.0	12.5
20°-30°	1064.1	17.6
30°-40°	1160.0	19.1
40°-50°	1066.2	17.6
50°-60°	837.3	13.8
60°-70°	545.0	9.0
70°-80°	280.5	4.6
80°-90°	71.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2098.2	34.6
0°-40°	3258.2	53.8
0°-60°	5161.6	85.2
0°-90°	6058.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6058.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2946	2946	2946	2946	2946	
5°	2946	2933	2898	2922	2914	279
15°	2802	2773	2682	2631	2605	790
25°	2544	2458	2282	2173	2133	1170
35°	2192	2056	1821	1653	1594	1372
45°	1792	1613	1333	1144	1080	1384
55°	1362	1154	866	707	656	1217
65°	920	704	464	373	365	912
75°	490	304	213	195	192	519
85°	114	58	51	51	51	137
90°	0	0	0	0	0	



TEST NUMBER: P930246

CATALOG NUMBER: DFN2DS-HX3F0-090DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2946.0	2946.0	2946.0	2946.0	2946.0
2.5°	2959.3	2946.0	2916.5	2943.5	2938.1
5°	2946.0	2932.7	2897.9	2921.9	2914.0
7.5°	2921.9	2906.1	2868.8	2879.2	2865.9
10°	2890.0	2871.3	2818.2	2809.9	2794.1
12.5°	2850.1	2826.1	2753.9	2738.1	2708.6
15°	2802.0	2772.6	2682.1	2631.4	2604.9
17.5°	2746.0	2703.3	2591.3	2532.7	2490.0
20°	2682.1	2628.6	2495.4	2428.9	2370.1
22.5°	2612.8	2551.4	2396.7	2306.1	2266.3
25°	2543.5	2458.1	2282.1	2172.9	2132.8
27.5°	2460.9	2370.1	2175.5	2050.2	1988.8
30°	2372.9	2271.4	2058.1	1922.3	1850.2
32.5°	2287.5	2164.7	1946.3	1786.3	1719.5
35°	2191.6	2055.6	1821.0	1653.1	1594.2
37.5°	2098.2	1951.5	1703.7	1519.5	1453.1
40°	1999.6	1839.7	1580.9	1391.7	1322.4
42.5°	1898.3	1727.7	1458.4	1261.0	1194.5
45°	1791.7	1612.9	1333.1	1143.6	1079.7
47.5°	1690.4	1501.2	1213.2	1023.7	965.1
50°	1578.4	1389.1	1095.8	911.7	855.9
52.5°	1468.9	1268.9	983.8	807.8	757.2
55°	1362.2	1154.3	866.4	706.6	655.9
57.5°	1253.1	1039.8	762.6	613.2	570.6
60°	1141.0	927.7	653.2	517.3	474.6
62.5°	1031.9	818.6	559.8	432.0	410.7
65°	919.8	703.8	463.9	373.3	365.2
67.5°	813.2	597.1	373.3	327.8	319.9
70°	701.2	493.3	309.2	282.6	271.8
72.5°	594.6	397.1	258.5	237.3	232.0
75°	490.5	303.8	213.3	194.6	192.1
77.5°	386.7	215.8	168.0	157.3	151.9
80°	290.5	154.8	127.8	117.4	117.4
82.5°	202.5	104.1	88.0	82.6	82.6
85°	114.5	58.5	50.6	50.6	50.6
87.5°	42.7	21.2	21.2	18.7	18.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P930246
 CATALOG NUMBER: DFN2DS-HX3F0-090DS927-RL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.50	17.02	15.86	17.33	17.65	11.46	12.98	11.82	13.29	13.61
	3H	17.26	18.63	17.64	18.96	19.32	12.72	14.09	13.10	14.42	14.78
	4H	17.93	19.21	18.33	19.56	19.94	13.23	14.51	13.63	14.86	15.23
	6H	18.42	19.60	18.83	19.97	20.36	13.61	14.79	14.02	15.16	15.55
	8H	18.59	19.71	19.01	20.10	20.50	13.73	14.86	14.16	15.25	15.65
	12H	18.69	19.77	19.12	20.15	20.58	13.81	14.89	14.24	15.27	15.70
4H	2H	15.60	16.88	16.00	17.23	17.61	12.16	13.44	12.55	13.78	14.16
	3H	17.54	18.60	17.95	19.00	19.40	13.60	14.66	14.01	15.06	15.46
	4H	18.29	19.24	18.72	19.66	20.10	14.20	15.15	14.63	15.57	16.01
	6H	18.88	19.71	19.34	20.15	20.61	14.69	15.52	15.14	15.96	16.42
	8H	19.09	19.87	19.56	20.31	20.78	14.85	15.63	15.31	16.07	16.54
	12H	19.25	19.94	19.73	20.42	20.89	14.97	15.66	15.45	16.14	16.61
8H	4H	18.31	19.09	18.77	19.53	20.00	14.55	15.33	15.01	15.77	16.24
	6H	18.95	19.59	19.44	20.08	20.56	15.14	15.78	15.64	16.27	16.75
	8H	19.20	19.77	19.71	20.28	20.77	15.36	15.94	15.87	16.45	16.93
	12H	19.40	19.91	19.91	20.40	20.97	15.54	16.05	16.05	16.54	17.11
12H	4H	18.29	18.99	18.78	19.47	19.94	14.59	15.29	15.08	15.77	16.24
	6H	18.93	19.51	19.44	20.02	20.50	15.20	15.78	15.72	16.29	16.78
	8H	19.21	19.72	19.72	20.21	20.78	15.48	15.98	15.98	16.48	17.04