

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930175

Luminaire Tested: DFN2DS-HX3F0-050DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930175
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-050DS930-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4034.2 lumens
Efficiency: N/A
Efficacy: 82.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930175

CATALOG NUMBER: DFN2DS-HX3F0-050DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930175

CATALOG NUMBER: DFN2DS-HX3F0-050DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1837	1837	1837
5°	1844	1817	1828
10°	1833	1799	1808
15°	1810	1775	1774
20°	1778	1740	1739
25°	1746	1697	1697
30°	1705	1658	1644
35°	1667	1611	1587
40°	1619	1563	1533
45°	1571	1516	1479
50°	1519	1467	1415
55°	1466	1410	1358
60°	1406	1343	1293
65°	1342	1275	1216
70°	1260	1193	1136
75°	1146	1098	1071
80°	1018	986	936
85°	829	791	710

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1571 cd/sqm

TEST NUMBER: P930175

CATALOG NUMBER: DFN2DS-HX3F0-050DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.2	3.7
10°-20°	419.9	10.4
20°-30°	617.1	15.3
30°-40°	716.7	17.8
40°-50°	715.8	17.7
50°-60°	624.2	15.5
60°-70°	461.4	11.4
70°-80°	261.0	6.5
80°-90°	68.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1186.2	29.4
0°-40°	1902.9	47.2
0°-60°	3242.9	80.4
0°-90°	4034.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4034.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1586	1586	1586	1586	1586	
5°	1586	1580	1563	1575	1572	151
15°	1509	1500	1480	1487	1479	425
25°	1366	1354	1328	1331	1328	629
35°	1179	1163	1139	1130	1122	736
45°	959	948	925	909	903	740
55°	726	717	698	680	672	649
65°	490	480	465	451	444	484
75°	256	253	245	236	239	273
85°	62	61	60	55	53	73
90°	0	0	0	0	0	

TEST NUMBER: P930175

CATALOG NUMBER: DFN2DS-HX3F0-050DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1585.6	1585.6	1585.6	1585.6	1585.6
2.5°	1594.8	1587.2	1570.4	1585.6	1582.7
5°	1585.6	1579.6	1562.8	1574.9	1572.1
7.5°	1574.9	1565.9	1549.1	1561.4	1558.3
10°	1558.3	1547.6	1529.3	1541.4	1536.9
12.5°	1535.3	1526.3	1508.0	1515.6	1512.5
15°	1509.4	1500.3	1480.4	1486.6	1479.0
17.5°	1477.4	1468.3	1448.4	1456.0	1448.4
20°	1442.3	1433.3	1411.9	1416.4	1410.4
22.5°	1407.3	1393.6	1373.7	1373.7	1370.6
25°	1366.1	1354.0	1328.0	1331.0	1328.0
27.5°	1320.3	1309.6	1289.9	1285.3	1277.8
30°	1274.7	1262.4	1239.6	1235.1	1228.9
32.5°	1225.8	1216.8	1192.3	1183.1	1177.0
35°	1178.6	1163.4	1139.0	1129.8	1122.2
37.5°	1125.2	1111.5	1087.0	1076.4	1068.8
40°	1070.4	1058.1	1033.7	1020.1	1013.9
42.5°	1017.0	1004.7	980.4	965.0	956.0
45°	959.1	948.4	925.4	908.8	902.6
47.5°	902.6	891.9	867.6	850.7	841.7
50°	843.1	835.5	814.2	792.8	785.2
52.5°	785.2	774.5	754.8	738.0	727.3
55°	725.8	716.6	698.3	680.0	672.5
57.5°	666.3	658.7	638.8	620.5	614.3
60°	606.8	600.8	579.5	562.6	558.1
62.5°	548.9	538.2	523.0	507.7	501.6
65°	489.5	480.3	465.0	451.3	443.7
67.5°	428.5	420.8	407.2	396.5	390.3
70°	372.0	365.9	352.2	341.5	335.5
72.5°	314.2	308.0	300.4	289.7	285.2
75°	256.1	253.1	245.4	236.4	239.4
77.5°	204.3	198.1	195.1	190.5	186.1
80°	152.6	150.9	147.8	143.4	140.3
82.5°	103.7	103.7	102.2	96.1	96.1
85°	62.4	61.0	59.5	54.8	53.4
87.5°	27.5	24.4	21.4	16.8	15.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930175

CATALOG NUMBER: DFN2DS-HX3F0-050DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.39	15.01	13.76	15.32	15.63	12.95	14.56	13.32	14.87	15.19
	3H	15.14	16.60	15.52	16.93	17.29	14.65	16.11	15.03	16.43	16.80
	4H	15.79	17.16	16.19	17.51	17.88	15.30	16.67	15.69	17.01	17.39
	6H	16.26	17.53	16.67	17.89	18.28	15.76	17.03	16.17	17.39	17.78
	8H	16.40	17.61	16.83	18.00	18.40	15.90	17.11	16.33	17.50	17.90
	12H	16.49	17.65	16.92	18.04	18.46	15.98	17.14	16.41	17.52	17.95
4H	2H	13.96	15.32	14.35	15.67	16.05	13.60	14.97	14.00	15.32	15.69
	3H	15.93	17.08	16.34	17.47	17.87	15.52	16.67	15.93	17.07	17.47
	4H	16.71	17.74	17.14	18.16	18.59	16.28	17.32	16.71	17.73	18.17
	6H	17.30	18.21	17.76	18.65	19.10	16.87	17.78	17.33	18.22	18.67
	8H	17.49	18.34	17.95	18.78	19.25	17.06	17.90	17.52	18.34	18.81
	12H	17.62	18.38	18.10	18.86	19.33	17.17	17.93	17.65	18.41	18.88
8H	4H	16.98	17.83	17.44	18.27	18.73	16.61	17.45	17.07	17.89	18.36
	6H	17.69	18.40	18.19	18.89	19.36	17.31	18.02	17.81	18.50	18.98
	8H	17.95	18.58	18.46	19.09	19.58	17.56	18.19	18.07	18.70	19.19
	12H	18.15	18.71	18.66	19.20	19.76	17.74	18.30	18.25	18.79	19.35
12H	4H	17.01	17.77	17.49	18.24	18.71	16.64	17.40	17.12	17.88	18.35
	6H	17.74	18.37	18.25	18.88	19.36	17.37	18.00	17.88	18.51	19.00
	8H	18.05	18.61	18.56	19.10	19.66	17.68	18.23	18.18	18.72	19.29