

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930247

Luminaire Tested: DFN2DS-HX3F0-090DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930247
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-HX3F0-090DS930-FLL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7261.7 lumens
Efficiency: N/A
Efficacy: 74.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.28' x L: 2.84' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930247

CATALOG NUMBER: DFN2DS-HX3F0-090DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930247

CATALOG NUMBER: DFN2DS-HX3F0-090DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3306	3306	3306
5°	3319	3271	3290
10°	3299	3238	3254
15°	3258	3196	3193
20°	3200	3133	3129
25°	3143	3055	3055
30°	3069	2984	2959
35°	3000	2899	2856
40°	2913	2813	2760
45°	2828	2729	2662
50°	2735	2641	2547
55°	2639	2539	2444
60°	2530	2416	2327
65°	2415	2294	2189
70°	2268	2147	2045
75°	2063	1977	1929
80°	1832	1775	1684
85°	1494	1425	1277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2828 cd/sqm

TEST NUMBER: P930247

CATALOG NUMBER: DFN2DS-HX3F0-090DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.6	3.7
10°-20°	755.8	10.4
20°-30°	1110.7	15.3
30°-40°	1290.1	17.8
40°-50°	1288.5	17.7
50°-60°	1123.5	15.5
60°-70°	830.5	11.4
70°-80°	469.9	6.5
80°-90°	124.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2135.2	29.4
0°-40°	3425.3	47.2
0°-60°	5837.3	80.4
0°-90°	7261.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7261.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2854	2854	2854	2854	2854	
5°	2854	2843	2813	2835	2830	271
15°	2717	2701	2665	2676	2662	765
25°	2459	2437	2391	2396	2391	1131
35°	2122	2094	2050	2034	2020	1325
45°	1726	1707	1666	1636	1625	1332
55°	1306	1290	1257	1224	1210	1168
65°	881	864	837	812	799	871
75°	461	456	442	425	431	492
85°	112	110	107	99	96	132
90°	0	0	0	0	0	

TEST NUMBER: P930247

CATALOG NUMBER: DFN2DS-HX3F0-090DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2854.0	2854.0	2854.0	2854.0	2854.0
2.5°	2870.7	2857.0	2826.7	2854.0	2848.8
5°	2854.0	2843.3	2813.1	2834.9	2829.6
7.5°	2834.9	2818.6	2788.3	2810.4	2804.9
10°	2804.9	2785.7	2752.7	2774.6	2766.4
12.5°	2763.5	2747.2	2714.4	2728.0	2722.5
15°	2717.0	2700.7	2664.8	2675.9	2662.2
17.5°	2659.3	2643.0	2607.2	2620.9	2607.2
20°	2596.1	2579.8	2541.3	2549.5	2538.7
22.5°	2533.2	2508.5	2472.6	2472.6	2467.1
25°	2458.9	2437.1	2390.6	2395.8	2390.6
27.5°	2376.5	2357.3	2321.9	2313.7	2300.0
30°	2294.5	2272.3	2231.2	2223.1	2212.1
32.5°	2206.5	2190.2	2146.2	2129.7	2118.6
35°	2121.5	2094.1	2050.1	2033.6	2019.9
37.5°	2025.4	2000.7	1956.7	1937.5	1923.8
40°	1926.7	1904.6	1860.6	1836.1	1825.1
42.5°	1830.6	1808.5	1764.8	1737.2	1720.9
45°	1726.3	1707.2	1665.8	1635.8	1624.8
47.5°	1624.8	1605.6	1561.5	1531.3	1515.0
50°	1517.6	1503.9	1465.5	1427.1	1413.4
52.5°	1413.4	1394.1	1358.6	1328.4	1309.1
55°	1306.5	1289.9	1257.0	1224.1	1210.4
57.5°	1199.4	1185.7	1149.9	1117.0	1105.9
60°	1092.2	1081.4	1043.0	1012.7	1004.6
62.5°	987.9	968.7	941.3	914.0	902.9
65°	881.1	864.5	837.1	812.4	798.7
67.5°	771.3	757.4	732.8	713.7	702.6
70°	669.7	658.6	633.9	614.7	603.9
72.5°	565.4	554.4	540.7	521.5	513.4
75°	461.0	455.7	441.7	425.4	431.0
77.5°	367.7	356.7	351.2	343.0	334.9
80°	274.6	271.6	266.1	257.9	252.5
82.5°	186.6	186.6	184.0	172.9	172.9
85°	112.4	109.8	107.2	98.7	96.1
87.5°	49.5	43.9	38.5	30.3	27.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930247

CATALOG NUMBER: DFN2DS-HX3F0-090DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.44	17.05	15.80	17.36	17.68	14.99	16.60	15.36	16.92	17.23
	3H	17.19	18.64	17.56	18.97	19.33	16.70	18.15	17.07	18.48	18.84
	4H	17.83	19.20	18.23	19.55	19.93	17.34	18.71	17.74	19.06	19.43
	6H	18.30	19.57	18.71	19.94	20.33	17.80	19.07	18.21	19.43	19.83
	8H	18.45	19.66	18.87	20.05	20.44	17.94	19.15	18.37	19.54	19.94
	12H	18.54	19.70	18.97	20.08	20.51	18.02	19.18	18.45	19.57	19.99
4H	2H	16.00	17.37	16.40	17.71	18.09	15.64	17.01	16.04	17.36	17.74
	3H	17.97	19.12	18.38	19.52	19.92	17.57	18.71	17.98	19.11	19.51
	4H	18.75	19.79	19.18	20.20	20.63	18.33	19.36	18.76	19.77	20.21
	6H	19.35	20.25	19.80	20.69	21.15	18.91	19.82	19.37	20.26	20.72
	8H	19.53	20.38	20.00	20.82	21.29	19.10	19.94	19.56	20.39	20.85
	12H	19.67	20.43	20.15	20.90	21.37	19.21	19.97	19.70	20.45	20.92
8H	4H	19.02	19.87	19.48	20.31	20.78	18.65	19.49	19.11	19.94	20.40
	6H	19.74	20.44	20.23	20.93	21.40	19.36	20.06	19.85	20.55	21.02
	8H	20.00	20.63	20.51	21.13	21.62	19.60	20.23	20.11	20.74	21.23
	12H	20.20	20.75	20.70	21.24	21.81	19.78	20.34	20.29	20.83	21.39
12H	4H	19.05	19.81	19.53	20.28	20.75	18.68	19.44	19.16	19.92	20.39
	6H	19.78	20.41	20.29	20.92	21.41	19.41	20.05	19.92	20.55	21.04
	8H	20.10	20.65	20.60	21.14	21.71	19.72	20.28	20.22	20.77	21.33