

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930442

Luminaire Tested: DFN2DS-PN2F0-030DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930442
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-030DS850-RLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2827.9 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930442

CATALOG NUMBER: DFN2DS-PN2F0-030DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930442

CATALOG NUMBER: DFN2DS-PN2F0-030DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2978	2978	2978
5°	2989	2941	2957
10°	2967	2893	2868
15°	2932	2807	2726
20°	2885	2684	2550
25°	2837	2546	2379
30°	2770	2402	2160
35°	2705	2247	1967
40°	2639	2086	1745
45°	2562	1906	1543
50°	2482	1723	1346
55°	2401	1527	1156
60°	2307	1321	960
65°	2200	1110	874
70°	2073	914	804
75°	1916	833	750
80°	1691	745	684
85°	1330	586	586

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2562 cd/sqm

TEST NUMBER: P930442

CATALOG NUMBER: DFN2DS-PN2F0-030DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.9	4.6
10°-20°	353.8	12.5
20°-30°	496.7	17.6
30°-40°	541.4	19.1
40°-50°	497.6	17.6
50°-60°	390.8	13.8
60°-70°	254.4	9.0
70°-80°	130.9	4.6
80°-90°	33.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	979.3	34.6
0°-40°	1520.7	53.8
0°-60°	2409.2	85.2
0°-90°	2827.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2827.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1375	1369	1353	1364	1360	130
15°	1308	1294	1252	1228	1216	369
25°	1187	1147	1065	1014	995	546
35°	1023	959	850	772	744	640
45°	836	753	622	534	504	646
55°	636	539	404	330	306	568
65°	429	328	216	174	170	426
75°	229	142	100	91	90	242
85°	54	27	24	24	24	64
90°	0	0	0	0	0	

TEST NUMBER: P930442

CATALOG NUMBER: DFN2DS-PN2F0-030DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1375.0	1375.0	1375.0	1375.0	1375.0
2.5°	1381.3	1375.0	1361.3	1373.8	1371.4
5°	1375.0	1368.8	1352.6	1363.8	1360.1
7.5°	1363.8	1356.4	1339.0	1343.9	1337.7
10°	1348.9	1340.2	1315.4	1311.5	1304.2
12.5°	1330.2	1319.0	1285.4	1278.0	1264.3
15°	1307.8	1294.1	1251.8	1228.2	1215.8
17.5°	1281.7	1261.8	1209.5	1182.2	1162.2
20°	1251.8	1226.9	1164.7	1133.7	1106.2
22.5°	1219.6	1190.8	1118.6	1076.4	1057.8
25°	1187.2	1147.3	1065.2	1014.2	995.4
27.5°	1148.6	1106.2	1015.4	957.0	928.2
30°	1107.6	1060.2	960.6	897.3	863.6
32.5°	1067.6	1010.4	908.5	833.7	802.6
35°	1022.9	959.4	849.9	771.5	744.1
37.5°	979.4	910.8	795.2	709.2	678.3
40°	933.3	858.7	737.9	649.5	617.3
42.5°	886.0	806.5	680.7	588.5	557.5
45°	836.3	752.8	622.3	533.8	503.9
47.5°	788.9	700.7	566.3	477.8	450.5
50°	736.7	648.3	511.5	425.5	399.5
52.5°	685.6	592.3	459.2	377.1	353.4
55°	635.8	538.8	404.3	329.8	306.2
57.5°	584.9	485.3	356.0	286.2	266.3
60°	532.5	433.1	304.9	241.4	221.6
62.5°	481.6	382.1	261.3	201.6	191.7
65°	429.3	328.5	216.5	174.2	170.5
67.5°	379.6	278.7	174.2	153.0	149.3
70°	327.3	230.2	144.3	131.9	126.9
72.5°	277.5	185.3	120.7	110.8	108.2
75°	228.9	141.8	99.6	90.8	89.6
77.5°	180.4	100.7	78.4	73.4	70.9
80°	135.6	72.2	59.7	54.8	54.8
82.5°	94.5	48.6	41.0	38.6	38.6
85°	53.5	27.3	23.6	23.6	23.6
87.5°	20.0	9.9	9.9	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930442

CATALOG NUMBER: DFN2DS-PN2F0-030DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.03	16.55	15.39	16.86	17.18	10.99	12.51	11.35	12.82	13.14
	3H	16.79	18.16	17.17	18.48	18.85	12.25	13.62	12.63	13.94	14.31
	4H	17.46	18.74	17.86	19.09	19.47	12.75	14.03	13.15	14.38	14.76
	6H	17.95	19.13	18.36	19.50	19.89	13.13	14.32	13.55	14.68	15.08
	8H	18.11	19.24	18.54	19.63	20.03	13.26	14.39	13.69	14.78	15.18
	12H	18.21	19.29	18.65	19.68	20.10	13.34	14.42	13.77	14.80	15.23
4H	2H	15.13	16.41	15.53	16.76	17.14	11.68	12.96	12.08	13.31	13.69
	3H	17.06	18.13	17.47	18.53	18.93	13.13	14.19	13.54	14.59	14.99
	4H	17.81	18.77	18.25	19.18	19.62	13.72	14.68	14.16	15.10	15.53
	6H	18.40	19.24	18.86	19.68	20.14	14.21	15.04	14.67	15.49	15.95
	8H	18.62	19.40	19.08	19.84	20.31	14.37	15.15	14.84	15.60	16.06
	12H	18.77	19.47	19.25	19.95	20.42	14.49	15.19	14.97	15.66	16.14
8H	4H	17.84	18.61	18.30	19.06	19.53	14.08	14.86	14.54	15.30	15.77
	6H	18.47	19.12	18.97	19.61	20.09	14.67	15.31	15.16	15.80	16.28
	8H	18.72	19.30	19.24	19.81	20.30	14.89	15.46	15.40	15.97	16.46
	12H	18.93	19.44	19.44	19.93	20.50	15.07	15.58	15.58	16.07	16.63
12H	4H	17.82	18.52	18.30	18.99	19.47	14.12	14.82	14.60	15.29	15.77
	6H	18.45	19.03	18.97	19.54	20.03	14.73	15.31	15.24	15.82	16.30
	8H	18.74	19.25	19.25	19.74	20.31	15.00	15.51	15.51	16.00	16.57