

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930478

Luminaire Tested: DFN2DS-PN2F0-050DS850-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930478
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN2F0-050DS850-RLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4713.3 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.29' x L: 2.17' x H: 0')
CIE Type: Direct

Input Watts (W): 54
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930478

CATALOG NUMBER: DFN2DS-PN2F0-050DS850-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930478

CATALOG NUMBER: DFN2DS-PN2F0-050DS850-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4964	4964	4964
5°	4982	4901	4929
10°	4944	4821	4780
15°	4887	4679	4544
20°	4809	4474	4249
25°	4728	4243	3965
30°	4616	4004	3600
35°	4508	3746	3279
40°	4398	3477	2908
45°	4269	3176	2572
50°	4137	2872	2243
55°	4002	2545	1927
60°	3845	2201	1599
65°	3667	1850	1456
70°	3454	1523	1339
75°	3193	1388	1250
80°	2819	1241	1139
85°	2217	979	979

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4269 cd/sqm

TEST NUMBER: P930478

CATALOG NUMBER: DFN2DS-PN2F0-050DS850-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	4.6
10°-20°	589.6	12.5
20°-30°	827.8	17.6
30°-40°	902.4	19.1
40°-50°	829.4	17.6
50°-60°	651.3	13.8
60°-70°	424.0	9.0
70°-80°	218.2	4.6
80°-90°	55.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1632.2	34.6
0°-40°	2534.6	53.8
0°-60°	4015.3	85.2
0°-90°	4713.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4713.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	2292	2281	2254	2273	2267	217
15°	2180	2157	2086	2047	2026	614
25°	1979	1912	1775	1690	1659	910
35°	1705	1599	1417	1286	1240	1067
45°	1394	1255	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	716	548	361	290	284	709
75°	382	236	166	151	149	404
85°	89	46	39	39	39	107
90°	0	0	0	0	0	

TEST NUMBER: P930478

CATALOG NUMBER: DFN2DS-PN2F0-050DS850-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.7	2291.7	2291.7	2291.7	2291.7
2.5°	2302.1	2291.7	2268.9	2289.8	2285.5
5°	2291.7	2281.4	2254.4	2273.0	2266.9
7.5°	2273.0	2260.7	2231.6	2239.8	2229.4
10°	2248.2	2233.6	2192.3	2185.9	2173.5
12.5°	2217.1	2198.5	2142.4	2130.1	2107.1
15°	2179.7	2156.9	2086.5	2047.1	2026.4
17.5°	2136.2	2103.0	2015.8	1970.2	1937.0
20°	2086.5	2044.9	1941.2	1889.5	1843.7
22.5°	2032.6	1984.8	1864.5	1794.0	1763.0
25°	1978.6	1912.1	1775.3	1690.3	1659.1
27.5°	1914.4	1843.7	1692.3	1594.9	1547.2
30°	1845.9	1767.0	1601.1	1495.4	1439.3
32.5°	1779.5	1684.0	1514.1	1389.6	1337.7
35°	1704.9	1599.1	1416.6	1285.9	1240.2
37.5°	1632.2	1518.1	1325.4	1182.1	1130.4
40°	1555.5	1431.2	1229.8	1082.6	1028.7
42.5°	1476.7	1344.0	1134.5	980.9	929.2
45°	1393.8	1254.7	1037.0	889.6	839.8
47.5°	1314.9	1167.8	943.8	796.4	750.8
50°	1227.9	1080.6	852.5	709.2	665.8
52.5°	1142.7	987.1	765.3	628.5	589.1
55°	1059.8	898.0	673.9	549.6	510.3
57.5°	974.8	808.9	593.2	477.1	443.8
60°	887.6	721.7	508.0	402.5	369.2
62.5°	802.7	636.8	435.5	336.0	319.5
65°	715.5	547.5	360.9	290.4	284.1
67.5°	632.6	464.6	290.4	255.1	248.9
70°	545.5	383.7	240.5	219.8	211.5
72.5°	462.6	309.0	201.2	184.6	180.4
75°	381.6	236.3	165.9	151.4	149.4
77.5°	300.8	167.9	130.8	122.3	118.1
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.6	81.0	68.4	64.2	64.2
85°	89.2	45.6	39.4	39.4	39.4
87.5°	33.3	16.5	16.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930478

CATALOG NUMBER: DFN2DS-PN2F0-050DS850-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.80	18.32	17.17	18.64	18.95	12.76	14.28	13.13	14.60	14.91
	3H	18.57	19.93	18.94	20.26	20.62	14.03	15.39	14.41	15.72	16.08
	4H	19.23	20.51	19.63	20.86	21.24	14.53	15.81	14.93	16.16	16.54
	6H	19.72	20.90	20.13	21.27	21.66	14.91	16.09	15.32	16.46	16.85
	8H	19.89	21.01	20.31	21.40	21.80	15.03	16.16	15.46	16.55	16.95
	12H	19.99	21.07	20.42	21.45	21.88	15.12	16.19	15.55	16.58	17.00
4H	2H	16.91	18.19	17.30	18.53	18.91	13.46	14.74	13.86	15.09	15.47
	3H	18.84	19.90	19.25	20.30	20.70	14.90	15.96	15.31	16.36	16.76
	4H	19.59	20.54	20.02	20.96	21.40	15.50	16.46	15.93	16.87	17.31
	6H	20.18	21.01	20.64	21.45	21.91	15.99	16.82	16.45	17.26	17.72
	8H	20.39	21.17	20.86	21.62	22.08	16.15	16.93	16.61	17.37	17.84
	12H	20.55	21.24	21.03	21.72	22.19	16.27	16.96	16.75	17.44	17.91
8H	4H	19.61	20.39	20.08	20.83	21.30	15.85	16.63	16.32	17.08	17.54
	6H	20.25	20.89	20.75	21.38	21.86	16.44	17.08	16.94	17.57	18.05
	8H	20.50	21.08	21.01	21.59	22.07	16.66	17.24	17.17	17.75	18.24
	12H	20.70	21.21	21.21	21.71	22.27	16.84	17.35	17.35	17.84	18.41
12H	4H	19.60	20.29	20.08	20.77	21.24	15.90	16.59	16.38	17.07	17.54
	6H	20.23	20.81	20.74	21.32	21.81	16.50	17.08	17.02	17.59	18.08
	8H	20.51	21.02	21.02	21.52	22.08	16.78	17.29	17.29	17.78	18.34