

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930545

Luminaire Tested: DFN2DS-PN3F0-050DS835-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930545
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN3F0-050DS835-FLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4950.0 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.11' x L: 2.96' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930545

CATALOG NUMBER: DFN2DS-PN3F0-050DS835-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930545

CATALOG NUMBER: DFN2DS-PN3F0-050DS835-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2274	2274	2274
5°	2283	2250	2263
10°	2270	2227	2238
15°	2241	2198	2196
20°	2202	2155	2153
25°	2162	2102	2102
30°	2111	2053	2035
35°	2064	1994	1965
40°	2004	1935	1898
45°	1945	1877	1831
50°	1881	1817	1752
55°	1815	1746	1682
60°	1741	1662	1601
65°	1661	1578	1506
70°	1560	1477	1407
75°	1419	1360	1327
80°	1260	1221	1159
85°	1027	979	879

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1945 cd/sqm

TEST NUMBER: P930545

CATALOG NUMBER: DFN2DS-PN3F0-050DS835-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.1	3.7
10°-20°	515.2	10.4
20°-30°	757.2	15.3
30°-40°	879.4	17.8
40°-50°	878.3	17.7
50°-60°	765.8	15.5
60°-70°	566.1	11.4
70°-80°	320.3	6.5
80°-90°	84.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1455.5	29.4
0°-40°	2334.9	47.2
0°-60°	3979.0	80.4
0°-90°	4950.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4950.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1946	1938	1918	1932	1929	185
15°	1852	1841	1816	1824	1815	522
25°	1676	1661	1630	1633	1630	771
35°	1446	1428	1398	1386	1377	903
45°	1177	1164	1136	1115	1108	908
55°	891	879	857	834	825	796
65°	601	589	571	554	544	594
75°	314	311	301	290	294	335
85°	77	75	73	67	66	90
90°	0	0	0	0	0	

TEST NUMBER: P930545

CATALOG NUMBER: DFN2DS-PN3F0-050DS835-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1945.5	1945.5	1945.5	1945.5	1945.5
2.5°	1956.8	1947.5	1926.9	1945.5	1942.0
5°	1945.5	1938.2	1917.5	1932.4	1928.9
7.5°	1932.4	1921.3	1900.7	1915.8	1912.0
10°	1912.0	1898.9	1876.5	1891.3	1885.8
12.5°	1883.8	1872.7	1850.3	1859.6	1855.8
15°	1852.0	1840.9	1816.5	1824.1	1814.7
17.5°	1812.7	1801.6	1777.2	1786.5	1777.2
20°	1769.7	1758.6	1732.4	1737.9	1730.6
22.5°	1726.8	1709.9	1685.5	1685.5	1681.7
25°	1676.2	1661.3	1629.5	1633.1	1629.5
27.5°	1620.0	1606.9	1582.7	1577.1	1567.8
30°	1564.0	1549.0	1521.0	1515.4	1507.9
32.5°	1504.1	1493.0	1463.0	1451.7	1444.2
35°	1446.1	1427.5	1397.5	1386.2	1376.9
37.5°	1380.6	1363.8	1333.8	1320.7	1311.4
40°	1313.4	1298.3	1268.3	1251.6	1244.1
42.5°	1247.9	1232.8	1203.0	1184.1	1173.0
45°	1176.8	1163.7	1135.5	1115.1	1107.5
47.5°	1107.5	1094.4	1064.5	1043.8	1032.7
50°	1034.5	1025.2	999.0	972.8	963.4
52.5°	963.4	950.3	926.1	905.5	892.4
55°	890.6	879.3	856.8	834.4	825.1
57.5°	817.5	808.2	783.8	761.4	753.8
60°	744.5	737.2	711.0	690.3	684.8
62.5°	673.5	660.4	641.7	623.0	615.5
65°	600.6	589.3	570.6	553.8	544.4
67.5°	525.8	516.3	499.6	486.5	478.9
70°	456.5	449.0	432.1	419.0	411.7
72.5°	385.5	377.9	368.6	355.5	349.9
75°	314.2	310.6	301.1	290.0	293.8
77.5°	250.7	243.1	239.4	233.8	228.3
80°	187.2	185.2	181.4	175.9	172.1
82.5°	127.2	127.2	125.4	117.9	117.9
85°	76.6	74.8	73.0	67.3	65.5
87.5°	33.7	30.0	26.2	20.6	18.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930545

CATALOG NUMBER: DFN2DS-PN3F0-050DS835-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.14	15.75	14.50	16.06	16.38	13.69	15.30	14.06	15.62	15.93
	3H	15.89	17.34	16.26	17.67	18.03	15.40	16.85	15.77	17.18	17.54
	4H	16.53	17.90	16.93	18.25	18.63	16.04	17.41	16.44	17.76	18.13
	6H	17.00	18.27	17.41	18.64	19.03	16.50	17.77	16.91	18.13	18.53
	8H	17.15	18.36	17.57	18.75	19.14	16.64	17.85	17.07	18.24	18.64
	12H	17.24	18.40	17.67	18.78	19.21	16.72	17.88	17.15	18.27	18.69
4H	2H	14.70	16.07	15.10	16.41	16.79	14.34	15.71	14.74	16.06	16.44
	3H	16.67	17.82	17.08	18.22	18.62	16.27	17.41	16.68	17.81	18.21
	4H	17.45	18.49	17.88	18.90	19.34	17.03	18.06	17.46	18.48	18.91
	6H	18.05	18.95	18.50	19.39	19.85	17.61	18.52	18.07	18.96	19.42
	8H	18.24	19.08	18.70	19.52	19.99	17.80	18.64	18.26	19.09	19.55
	12H	18.37	19.13	18.85	19.60	20.07	17.92	18.68	18.40	19.15	19.62
8H	4H	17.72	18.57	18.18	19.01	19.48	17.35	18.20	17.81	18.64	19.10
	6H	18.44	19.14	18.93	19.63	20.10	18.06	18.76	18.55	19.25	19.72
	8H	18.70	19.33	19.21	19.83	20.32	18.30	18.94	18.81	19.44	19.93
	12H	18.90	19.45	19.40	19.94	20.51	18.48	19.04	18.99	19.53	20.09
12H	4H	17.75	18.51	18.23	18.98	19.45	17.38	18.14	17.86	18.62	19.09
	6H	18.48	19.11	18.99	19.62	20.11	18.11	18.75	18.62	19.25	19.74
	8H	18.80	19.35	19.30	19.84	20.41	18.42	18.98	18.93	19.47	20.03