

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P438503

Luminaire Tested: **ISW-SA1D-730-U-SL2**

Issue Date: 12/10/2020

Test Information

Test Method: LM-79-08
Report Number: P438503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-14)
Test Lab: INNOVATION CENTER
Issue Date: 12/10/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: ISW-SA1D-730-U-SL2
Description: IMPACT ELITE LED WEDGE LUMINAIRE
(1) 70 CRI, 3000K, 800mA LIGHTSQUARE WITH 16 LEDS AND TYPE II SPILL LIGHT
ELIMINATOR OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5142 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B1 - U0 - G2


Input Watts (W): 45.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P438503
 CATALOG NUMBER: ISW-SA1D-730-U-SL2

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 1.9 fc
 Type III - Medium - N/A

REPORT NUMBER: P438503
CATALOG NUMBER: ISW-SA1D-730-U-SL2

Luminous Intensity Polar Plot



— Vertical Plane Through 67-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P438503
 CATALOG NUMBER: ISW-SA1D-730-U-SL2


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1007.0 | 0.0 | 1007.0 |
| | % Fixture | 19.6 | 0.0 | 19.6 |
| Street Side | Lumens | 4134.9 | 0.0 | 4134.9 |
| | % Fixture | 80.4 | 0.0 | 80.4 |
| Total | Lumens | 5142.0 | 0.0 | 5142.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 101.9 | 2.0 |
| 10°-20° | 246.8 | 4.8 |
| 20°-30° | 340.1 | 6.6 |
| 30°-40° | 459.4 | 8.9 |
| 40°-50° | 681.7 | 13.3 |
| 50°-60° | 1049.2 | 20.4 |
| 60°-70° | 1297.2 | 25.2 |
| 70°-80° | 868.9 | 16.9 |
| 80°-90° | 96.8 | 1.9 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 5142.0 | 100.0 |
| 0°-180° | 5142.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P438503
 CATALOG NUMBER: ISW-SA1D-730-U-SL2

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 407.8 | 7.9 | | | |
| FM (30°-60°) | 1833.2 | 35.7 | | | |
| FH (60°-80°) | 1811.5 | 35.2 | | | G2/5000 |
| FVH (80°-90°) | 82.4 | 1.6 | | | G1/100 |
| BL (0°-30°) | 281.0 | 5.5 | B1/500 | | |
| BM (30°-60°) | 357.0 | 6.9 | B1/1000 | | |
| BH (60°-80°) | 354.7 | 6.9 | B1/500 | | G1/500 |
| BVH (80°-90°) | 14.4 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2
 Type III Medium





REPORT NUMBER: P438503

CATALOG NUMBER: ISW-SA1D-730-U-SL2

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 67° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1161.1 | 1161.1 | 1161.1 | 1161.1 | 1161.1 | 1161.1 | 1161.1 | 1161.1 | 1161.1 | 1161.1 | 1161.1 |
| 2.5° | 1097.8 | 1105.3 | 1107.1 | 1112.7 | 1120.2 | 1127.6 | 1136.9 | 1148.1 | 1149.9 | 1155.5 | 1166.7 |
| 5° | 1023.4 | 1027.1 | 1030.9 | 1042.0 | 1055.0 | 1079.2 | 1103.4 | 1125.8 | 1129.5 | 1148.1 | 1168.5 |
| 7.5° | 954.6 | 963.9 | 965.7 | 975.0 | 995.5 | 1025.3 | 1058.8 | 1097.8 | 1109.0 | 1135.1 | 1166.7 |
| 10° | 904.3 | 909.9 | 913.6 | 930.4 | 947.1 | 980.6 | 1021.5 | 1069.9 | 1081.1 | 1120.2 | 1164.8 |
| 12.5° | 863.4 | 872.7 | 878.3 | 889.4 | 915.5 | 945.3 | 986.2 | 1038.3 | 1053.2 | 1101.6 | 1157.4 |
| 15° | 841.1 | 848.5 | 850.4 | 863.4 | 883.9 | 913.6 | 952.7 | 1012.2 | 1023.4 | 1083.0 | 1157.4 |
| 17.5° | 835.5 | 837.3 | 839.2 | 846.6 | 863.4 | 887.6 | 928.5 | 989.9 | 1002.9 | 1075.5 | 1157.4 |
| 20° | 846.6 | 846.6 | 846.6 | 842.9 | 855.9 | 874.6 | 915.5 | 971.3 | 989.9 | 1068.1 | 1163.0 |
| 22.5° | 872.7 | 874.6 | 869.0 | 859.7 | 854.1 | 867.1 | 902.5 | 965.7 | 982.5 | 1066.2 | 1174.1 |
| 25° | 909.9 | 911.8 | 908.0 | 895.0 | 869.0 | 867.1 | 896.9 | 960.1 | 975.0 | 1064.3 | 1172.3 |
| 27.5° | 960.1 | 971.3 | 960.1 | 945.3 | 911.8 | 882.0 | 902.5 | 956.4 | 973.2 | 1064.3 | 1176.0 |
| 30° | 1030.9 | 1038.3 | 1032.7 | 1008.5 | 965.7 | 913.6 | 909.9 | 960.1 | 973.2 | 1062.5 | 1174.1 |
| 32.5° | 1101.6 | 1103.4 | 1109.0 | 1092.3 | 1040.2 | 960.1 | 930.4 | 963.9 | 975.0 | 1060.6 | 1168.5 |
| 35° | 1155.5 | 1166.7 | 1190.9 | 1192.7 | 1131.3 | 1027.1 | 973.2 | 978.8 | 982.5 | 1066.2 | 1163.0 |
| 37.5° | 1224.4 | 1228.1 | 1267.2 | 1296.9 | 1243.0 | 1120.2 | 1032.7 | 1006.7 | 1008.5 | 1084.8 | 1172.3 |
| 40° | 1287.6 | 1302.5 | 1356.5 | 1393.7 | 1375.1 | 1244.8 | 1114.6 | 1056.9 | 1060.6 | 1118.3 | 1194.6 |
| 42.5° | 1382.5 | 1393.7 | 1449.5 | 1501.6 | 1507.2 | 1386.3 | 1228.1 | 1142.5 | 1133.2 | 1183.4 | 1243.0 |
| 45° | 1466.3 | 1479.3 | 1550.0 | 1626.3 | 1652.3 | 1546.3 | 1369.5 | 1259.7 | 1244.8 | 1293.2 | 1332.3 |
| 47.5° | 1583.5 | 1605.8 | 1661.6 | 1749.1 | 1836.6 | 1741.7 | 1550.0 | 1419.7 | 1406.7 | 1440.2 | 1451.4 |
| 50° | 1695.1 | 1708.2 | 1754.7 | 1860.7 | 2015.2 | 1987.3 | 1771.4 | 1628.2 | 1607.7 | 1613.3 | 1639.3 |
| 52.5° | 1711.9 | 1717.5 | 1765.8 | 1877.5 | 2167.8 | 2286.9 | 2043.1 | 1862.6 | 1825.4 | 1831.0 | 1862.6 |
| 55° | 1585.4 | 1607.7 | 1643.0 | 1799.3 | 2178.9 | 2619.9 | 2424.6 | 2171.5 | 2113.8 | 2093.3 | 2119.4 |
| 57.5° | 1323.0 | 1349.0 | 1399.3 | 1561.2 | 2050.5 | 2800.4 | 3049.8 | 2539.9 | 2450.6 | 2355.7 | 2387.3 |
| 60° | 975.0 | 1002.9 | 1034.6 | 1192.7 | 1724.9 | 2828.3 | 3671.3 | 2986.5 | 2854.4 | 2618.1 | 2634.8 |
| 62.5° | 748.0 | 748.0 | 775.9 | 841.1 | 1153.7 | 2625.5 | 4036.0 | 3742.0 | 3418.2 | 2938.1 | 2917.6 |
| 65° | 604.7 | 612.2 | 640.1 | 701.5 | 729.4 | 1864.5 | 4181.1 | 4839.8 | 4495.6 | 3321.4 | 3215.4 |
| 67.5° | 500.5 | 502.4 | 534.0 | 630.8 | 638.2 | 1025.3 | 3792.2 | 5416.6 | 5334.8 | 3801.5 | 3531.7 |
| 70° | 383.3 | 385.2 | 422.4 | 548.9 | 621.5 | 679.2 | 2653.4 | 5357.1 | 5461.3 | 4311.3 | 3600.5 |
| 72.5° | 254.9 | 266.1 | 310.7 | 435.4 | 619.6 | 640.1 | 1440.2 | 4685.4 | 4836.1 | 4510.4 | 3369.8 |
| 75° | 158.2 | 160.0 | 206.5 | 301.4 | 569.4 | 638.2 | 846.6 | 3650.8 | 3836.9 | 3742.0 | 2923.2 |
| 77.5° | 96.8 | 100.5 | 122.8 | 197.2 | 441.0 | 640.1 | 602.9 | 2512.0 | 2666.4 | 2456.2 | 1723.0 |
| 80° | 59.5 | 59.5 | 70.7 | 119.1 | 286.6 | 573.1 | 519.1 | 1460.7 | 1445.8 | 908.0 | 489.4 |
| 82.5° | 22.3 | 24.2 | 37.2 | 65.1 | 145.1 | 444.7 | 455.9 | 660.6 | 608.5 | 267.9 | 174.9 |
| 85° | 3.7 | 3.7 | 7.4 | 20.5 | 39.1 | 184.2 | 253.1 | 232.6 | 195.4 | 81.9 | 72.6 |
| 87.5° | 0.0 | 0.0 | 0.0 | 1.9 | 1.9 | 3.7 | 5.6 | 5.6 | 5.6 | 5.6 | 7.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P438503
 CATALOG NUMBER: ISW-SA1D-730-U-SL2

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1161.1 | 1161.1 | 1161.1 | 1161.1 | 1161.1 | 1161.1 | 1161.1 | 1161.1 | 1161.1 | 1161.1 | 1161.1 |
| 2.5° | 1166.7 | 1170.4 | 1168.5 | 1163.0 | 1157.4 | 1153.7 | 1144.4 | 1138.8 | 1140.6 | 1140.6 | 1142.5 |
| 5° | 1170.4 | 1176.0 | 1166.7 | 1155.5 | 1135.1 | 1112.7 | 1092.3 | 1081.1 | 1066.2 | 1071.8 | 1068.1 |
| 7.5° | 1176.0 | 1179.7 | 1163.0 | 1129.5 | 1094.1 | 1056.9 | 1021.5 | 989.9 | 965.7 | 954.6 | 962.0 |
| 10° | 1172.3 | 1177.9 | 1146.2 | 1096.0 | 1042.0 | 982.5 | 928.5 | 876.4 | 842.9 | 820.6 | 826.2 |
| 12.5° | 1170.4 | 1164.8 | 1122.0 | 1047.6 | 973.2 | 891.3 | 809.4 | 746.2 | 690.3 | 668.0 | 671.7 |
| 15° | 1163.0 | 1159.2 | 1092.3 | 997.4 | 895.0 | 779.7 | 671.7 | 589.9 | 522.9 | 500.5 | 508.0 |
| 17.5° | 1166.7 | 1155.5 | 1056.9 | 936.0 | 796.4 | 655.0 | 522.9 | 442.9 | 409.4 | 401.9 | 400.1 |
| 20° | 1163.0 | 1142.5 | 1021.5 | 869.0 | 692.2 | 508.0 | 388.9 | 346.1 | 346.1 | 357.3 | 359.1 |
| 22.5° | 1166.7 | 1131.3 | 982.5 | 792.7 | 573.1 | 381.5 | 303.3 | 292.1 | 308.9 | 333.1 | 333.1 |
| 25° | 1166.7 | 1118.3 | 939.7 | 707.1 | 448.4 | 290.3 | 258.6 | 258.6 | 281.0 | 303.3 | 301.4 |
| 27.5° | 1159.2 | 1092.3 | 891.3 | 615.9 | 333.1 | 240.0 | 227.0 | 232.6 | 247.5 | 266.1 | 264.2 |
| 30° | 1140.6 | 1066.2 | 831.8 | 509.8 | 253.1 | 212.1 | 210.3 | 212.1 | 219.6 | 230.7 | 228.9 |
| 32.5° | 1123.9 | 1036.4 | 774.1 | 396.3 | 214.0 | 197.2 | 195.4 | 197.2 | 199.1 | 202.8 | 202.8 |
| 35° | 1112.7 | 1010.4 | 705.2 | 305.2 | 193.5 | 187.9 | 184.2 | 184.2 | 180.5 | 182.4 | 182.4 |
| 37.5° | 1099.7 | 986.2 | 634.5 | 238.2 | 182.4 | 178.6 | 174.9 | 169.3 | 169.3 | 165.6 | 165.6 |
| 40° | 1099.7 | 967.6 | 561.9 | 201.0 | 174.9 | 173.0 | 165.6 | 158.2 | 154.4 | 154.4 | 154.4 |
| 42.5° | 1129.5 | 967.6 | 495.0 | 184.2 | 167.5 | 165.6 | 156.3 | 148.9 | 145.1 | 145.1 | 145.1 |
| 45° | 1179.7 | 978.8 | 426.1 | 173.0 | 161.9 | 158.2 | 147.0 | 139.6 | 135.8 | 135.8 | 134.0 |
| 47.5° | 1267.2 | 1025.3 | 364.7 | 167.5 | 156.3 | 150.7 | 137.7 | 130.3 | 126.5 | 126.5 | 126.5 |
| 50° | 1414.2 | 1118.3 | 314.5 | 161.9 | 150.7 | 141.4 | 130.3 | 122.8 | 119.1 | 119.1 | 117.2 |
| 52.5° | 1617.0 | 1257.9 | 290.3 | 158.2 | 143.3 | 132.1 | 122.8 | 115.4 | 111.6 | 109.8 | 109.8 |
| 55° | 1860.7 | 1468.1 | 286.6 | 156.3 | 135.8 | 124.7 | 115.4 | 107.9 | 104.2 | 102.3 | 102.3 |
| 57.5° | 2126.8 | 1698.9 | 312.6 | 152.6 | 128.4 | 115.4 | 107.9 | 100.5 | 96.8 | 94.9 | 94.9 |
| 60° | 2383.6 | 1951.9 | 396.3 | 148.9 | 122.8 | 107.9 | 98.6 | 93.0 | 89.3 | 87.5 | 87.5 |
| 62.5° | 2681.3 | 2218.0 | 580.6 | 150.7 | 119.1 | 100.5 | 91.2 | 85.6 | 83.7 | 81.9 | 81.9 |
| 65° | 3008.8 | 2523.2 | 742.4 | 165.6 | 120.9 | 93.0 | 83.7 | 80.0 | 76.3 | 74.4 | 74.4 |
| 67.5° | 3299.1 | 2720.4 | 619.6 | 191.7 | 132.1 | 87.5 | 74.4 | 72.6 | 68.8 | 67.0 | 68.8 |
| 70° | 3234.0 | 2512.0 | 381.5 | 193.5 | 134.0 | 83.7 | 67.0 | 63.3 | 59.5 | 59.5 | 59.5 |
| 72.5° | 2949.3 | 2216.1 | 266.1 | 167.5 | 119.1 | 74.4 | 57.7 | 54.0 | 52.1 | 52.1 | 52.1 |
| 75° | 2482.2 | 1827.3 | 212.1 | 135.8 | 93.0 | 61.4 | 48.4 | 46.5 | 44.7 | 42.8 | 42.8 |
| 77.5° | 1358.3 | 993.6 | 158.2 | 104.2 | 68.8 | 46.5 | 40.9 | 37.2 | 35.4 | 35.4 | 35.4 |
| 80° | 398.2 | 340.5 | 98.6 | 74.4 | 44.7 | 33.5 | 31.6 | 27.9 | 26.1 | 26.1 | 26.1 |
| 82.5° | 167.5 | 141.4 | 59.5 | 40.9 | 29.8 | 22.3 | 20.5 | 18.6 | 16.7 | 14.9 | 16.7 |
| 85° | 65.1 | 68.8 | 37.2 | 24.2 | 16.7 | 11.2 | 9.3 | 7.4 | 7.4 | 5.6 | 7.4 |
| 87.5° | 7.4 | 9.3 | 7.4 | 5.6 | 3.7 | 1.9 | 1.9 | 1.9 | 1.9 | 1.9 | 1.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 2993 | CRI (Ra): | 71.8 | R9: | -38.3 |
| CIE u': | 0.2508 | R1: | 67.5 | R10: | 62.5 |
| CIE v': | 0.5215 | R2: | 82.9 | R11: | 63.7 |
| Duv: | 0.0000 | R3: | 94.7 | R12: | 57.8 |
| CIE x: | 0.4374 | R4: | 67.7 | R13: | 70.4 |
| CIE y: | 0.4043 | R5: | 67.9 | R14: | 97.3 |
| CIE z: | 0.1583 | R6: | 77.6 | | |
| Peak Wavelength (nm): | 593 | R7: | 76.0 | | |
| Dominant Wavelength (nm): | 582 | R8: | 40.5 | | |
| Purity: | 53 | | | | |
| Rf: | 75.7 | | | | |
| Rg: | 93.9 | | | | |



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)