

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P438720

Luminaire Tested: **ISW-SA1E-740-U-SLR**

Issue Date: 12/10/2020

Test Information

Test Method: LM-79-08
Report Number: P438720
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-074-22)
Test Lab: INNOVATION CENTER
Issue Date: 12/10/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: ISW-SA1E-740-U-SLR
Description: IMPACT ELITE LED WEDGE LUMINAIRE
(1) 70 CRI, 4000K, 1050mA LIGHTSQUARE WITH 16 LEDS AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6365 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P438720
 CATALOG NUMBER: ISW-SA1E-740-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3.3 fc
 Type IV - Short - N/A

REPORT NUMBER: P438720
CATALOG NUMBER: ISW-SA1E-740-U-SLR

Luminous Intensity Polar Plot



— Vertical Plane Through 355-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P438720
 CATALOG NUMBER: ISW-SA1E-740-U-SLR


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 1147.4 | 0.0 | 1147.4 |
| | % Fixture | 18.0 | 0.0 | 18.0 |
| Street Side | Lumens | 5217.6 | 0.0 | 5217.6 |
| | % Fixture | 82.0 | 0.0 | 82.0 |
| Total | Lumens | 6365.0 | 0.0 | 6365.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 153.8 | 2.4 |
| 10°-20° | 317.5 | 5.0 |
| 20°-30° | 452.5 | 7.1 |
| 30°-40° | 646.8 | 10.2 |
| 40°-50° | 903.2 | 14.2 |
| 50°-60° | 1256.3 | 19.7 |
| 60°-70° | 1530.4 | 24.0 |
| 70°-80° | 942.6 | 14.8 |
| 80°-90° | 161.9 | 2.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 6365.0 | 100.0 |
| 0°-180° | 6365.0 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P438720


CATALOG NUMBER: ISW-SA1E-740-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 636.4 | 10.0 | | | |
| FM (30°-60°) | 2311.3 | 36.3 | | | |
| FH (60°-80°) | 2139.8 | 33.6 | | | G2/5000 |
| FVH (80°-90°) | 130.1 | 2.0 | | | G2/225 |
| BL (0°-30°) | 287.3 | 4.5 | B1/500 | | |
| BM (30°-60°) | 495.1 | 7.8 | B1/1000 | | |
| BH (60°-80°) | 333.2 | 5.2 | B1/500 | | G1/500 |
| BVH (80°-90°) | 31.8 | 0.5 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P438720

CATALOG NUMBER: ISW-SA1E-740-U-SLR

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 |
| 2.5° | 2088.1 | 2088.1 | 2062.3 | 1997.9 | 1938.6 | 1876.7 | 1856.1 | 1799.4 | 1763.3 | 1729.8 | 1742.7 |
| 5° | 1967.0 | 1959.2 | 1912.8 | 1778.8 | 1675.7 | 1575.1 | 1513.2 | 1420.4 | 1410.1 | 1327.6 | 1322.5 |
| 7.5° | 1804.6 | 1799.4 | 1729.8 | 1577.7 | 1459.1 | 1301.9 | 1209.1 | 1129.1 | 1059.5 | 1010.6 | 995.1 |
| 10° | 1693.7 | 1675.7 | 1590.6 | 1405.0 | 1232.3 | 1118.8 | 1067.3 | 997.7 | 938.4 | 876.5 | 824.9 |
| 12.5° | 1621.5 | 1600.9 | 1515.8 | 1312.2 | 1144.6 | 1067.3 | 995.1 | 912.6 | 832.7 | 760.5 | 708.9 |
| 15° | 1634.4 | 1600.9 | 1505.5 | 1289.0 | 1113.7 | 1002.8 | 902.3 | 804.3 | 711.5 | 631.6 | 567.1 |
| 17.5° | 1727.2 | 1686.0 | 1580.3 | 1304.4 | 1064.7 | 917.7 | 781.1 | 667.7 | 554.3 | 471.8 | 420.2 |
| 20° | 1889.6 | 1830.3 | 1696.3 | 1348.3 | 1028.6 | 837.8 | 657.4 | 507.9 | 389.3 | 332.6 | 317.1 |
| 22.5° | 2088.1 | 2036.6 | 1853.5 | 1384.4 | 989.9 | 747.6 | 520.7 | 366.1 | 306.8 | 278.4 | 270.7 |
| 25° | 2294.4 | 2237.6 | 2034.0 | 1443.6 | 959.0 | 665.1 | 409.9 | 291.3 | 262.9 | 250.1 | 244.9 |
| 27.5° | 2505.8 | 2449.0 | 2211.9 | 1539.0 | 922.9 | 577.5 | 330.0 | 255.2 | 234.6 | 224.3 | 224.3 |
| 30° | 2655.3 | 2608.9 | 2371.7 | 1624.1 | 881.7 | 507.9 | 291.3 | 237.2 | 219.1 | 208.8 | 206.2 |
| 32.5° | 2822.8 | 2758.4 | 2521.2 | 1680.8 | 850.7 | 453.7 | 265.5 | 221.7 | 206.2 | 193.3 | 193.3 |
| 35° | 3011.0 | 2938.8 | 2660.4 | 1737.5 | 819.8 | 427.9 | 247.5 | 211.4 | 195.9 | 183.0 | 180.5 |
| 37.5° | 3217.3 | 3124.5 | 2802.2 | 1786.5 | 786.3 | 415.0 | 237.2 | 201.1 | 185.6 | 175.3 | 170.1 |
| 40° | 3444.1 | 3346.2 | 2990.4 | 1827.8 | 763.1 | 399.6 | 229.4 | 193.3 | 177.9 | 165.0 | 162.4 |
| 42.5° | 3634.9 | 3547.2 | 3121.9 | 1853.5 | 752.8 | 379.0 | 226.9 | 185.6 | 172.7 | 157.3 | 152.1 |
| 45° | 3732.8 | 3658.1 | 3281.7 | 1861.3 | 747.6 | 366.1 | 214.0 | 185.6 | 167.6 | 152.1 | 144.4 |
| 47.5° | 3817.9 | 3763.8 | 3397.7 | 1899.9 | 734.7 | 353.2 | 198.5 | 195.9 | 165.0 | 144.4 | 136.6 |
| 50° | 3962.3 | 3905.6 | 3578.2 | 1972.1 | 719.2 | 337.7 | 183.0 | 188.2 | 165.0 | 139.2 | 131.5 |
| 52.5° | 4135.0 | 4119.5 | 3815.3 | 2085.5 | 696.0 | 317.1 | 167.6 | 177.9 | 165.0 | 136.6 | 126.3 |
| 55° | 4387.6 | 4364.4 | 4129.8 | 2232.5 | 667.7 | 288.7 | 152.1 | 162.4 | 162.4 | 128.9 | 118.6 |
| 57.5° | 4601.6 | 4604.2 | 4418.6 | 2335.6 | 641.9 | 242.3 | 141.8 | 139.2 | 154.7 | 121.2 | 110.9 |
| 60° | 4699.6 | 4699.6 | 4511.4 | 2374.3 | 608.4 | 203.7 | 134.1 | 123.7 | 159.8 | 113.4 | 103.1 |
| 62.5° | 4761.4 | 4709.9 | 4382.5 | 2338.2 | 569.7 | 183.0 | 121.2 | 113.4 | 128.9 | 105.7 | 95.4 |
| 65° | 4743.4 | 4645.4 | 4124.7 | 2155.2 | 513.0 | 177.9 | 113.4 | 103.1 | 103.1 | 98.0 | 90.2 |
| 67.5° | 4581.0 | 4428.9 | 3745.7 | 1845.8 | 453.7 | 175.3 | 103.1 | 95.4 | 92.8 | 87.6 | 82.5 |
| 70° | 4140.2 | 4031.9 | 3294.6 | 1505.5 | 415.0 | 175.3 | 95.4 | 85.1 | 82.5 | 77.3 | 74.8 |
| 72.5° | 3384.8 | 3225.0 | 2629.5 | 1129.1 | 384.1 | 175.3 | 87.6 | 74.8 | 72.2 | 69.6 | 67.0 |
| 75° | 2312.4 | 2129.4 | 1848.4 | 693.5 | 301.6 | 152.1 | 77.3 | 61.9 | 61.9 | 59.3 | 56.7 |
| 77.5° | 1276.1 | 1234.8 | 1041.5 | 366.1 | 188.2 | 92.8 | 59.3 | 49.0 | 51.6 | 49.0 | 46.4 |
| 80° | 739.9 | 696.0 | 618.7 | 177.9 | 108.3 | 54.1 | 36.1 | 36.1 | 38.7 | 38.7 | 36.1 |
| 82.5° | 358.3 | 311.9 | 319.7 | 72.2 | 38.7 | 23.2 | 15.5 | 18.0 | 20.6 | 25.8 | 25.8 |
| 85° | 12.9 | 12.9 | 25.8 | 5.2 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 5.2 | 7.7 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P438720
 CATALOG NUMBER: ISW-SA1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 |
| 2.5° | 1701.4 | 1701.4 | 1711.7 | 1755.6 | 1719.5 | 1714.3 | 1724.6 | 1742.7 | 1750.4 | 1786.5 | 1783.9 |
| 5° | 1312.2 | 1304.4 | 1335.4 | 1376.6 | 1399.8 | 1412.7 | 1433.3 | 1479.7 | 1461.7 | 1490.0 | 1484.9 |
| 7.5° | 969.3 | 982.2 | 969.3 | 1015.7 | 1051.8 | 1105.9 | 1147.2 | 1136.9 | 1139.4 | 1116.2 | 1149.8 |
| 10° | 791.4 | 786.3 | 755.3 | 770.8 | 791.4 | 824.9 | 853.3 | 858.5 | 884.2 | 843.0 | 871.3 |
| 12.5° | 675.4 | 654.8 | 623.9 | 608.4 | 603.2 | 629.0 | 636.7 | 649.6 | 665.1 | 678.0 | 683.2 |
| 15° | 541.4 | 525.9 | 505.3 | 482.1 | 476.9 | 476.9 | 495.0 | 513.0 | 533.6 | 538.8 | 556.8 |
| 17.5° | 404.7 | 397.0 | 389.3 | 389.3 | 389.3 | 389.3 | 404.7 | 412.5 | 422.8 | 438.2 | 435.7 |
| 20° | 306.8 | 306.8 | 309.4 | 322.2 | 330.0 | 335.1 | 345.4 | 348.0 | 345.4 | 348.0 | 348.0 |
| 22.5° | 270.7 | 268.1 | 275.8 | 281.0 | 293.9 | 306.8 | 311.9 | 309.4 | 301.6 | 296.5 | 301.6 |
| 25° | 244.9 | 247.5 | 250.1 | 257.8 | 268.1 | 281.0 | 283.6 | 281.0 | 273.3 | 273.3 | 273.3 |
| 27.5° | 224.3 | 226.9 | 232.0 | 239.7 | 250.1 | 260.4 | 262.9 | 257.8 | 250.1 | 252.6 | 250.1 |
| 30° | 208.8 | 214.0 | 216.5 | 224.3 | 232.0 | 242.3 | 242.3 | 237.2 | 232.0 | 232.0 | 232.0 |
| 32.5° | 190.8 | 195.9 | 201.1 | 208.8 | 219.1 | 224.3 | 224.3 | 221.7 | 216.5 | 214.0 | 214.0 |
| 35° | 180.5 | 180.5 | 185.6 | 195.9 | 201.1 | 206.2 | 208.8 | 206.2 | 201.1 | 195.9 | 193.3 |
| 37.5° | 170.1 | 170.1 | 172.7 | 177.9 | 188.2 | 193.3 | 195.9 | 190.8 | 185.6 | 180.5 | 180.5 |
| 40° | 159.8 | 159.8 | 162.4 | 165.0 | 175.3 | 183.0 | 183.0 | 175.3 | 170.1 | 172.7 | 170.1 |
| 42.5° | 152.1 | 152.1 | 154.7 | 154.7 | 159.8 | 172.7 | 170.1 | 165.0 | 162.4 | 162.4 | 159.8 |
| 45° | 144.4 | 141.8 | 144.4 | 144.4 | 146.9 | 159.8 | 159.8 | 152.1 | 152.1 | 154.7 | 152.1 |
| 47.5° | 136.6 | 134.1 | 136.6 | 136.6 | 139.2 | 146.9 | 146.9 | 144.4 | 144.4 | 144.4 | 146.9 |
| 50° | 128.9 | 128.9 | 128.9 | 128.9 | 131.5 | 134.1 | 139.2 | 136.6 | 136.6 | 136.6 | 139.2 |
| 52.5° | 121.2 | 121.2 | 121.2 | 123.7 | 123.7 | 128.9 | 131.5 | 128.9 | 131.5 | 131.5 | 131.5 |
| 55° | 116.0 | 113.4 | 113.4 | 118.6 | 118.6 | 123.7 | 126.3 | 123.7 | 126.3 | 126.3 | 126.3 |
| 57.5° | 108.3 | 108.3 | 108.3 | 110.9 | 113.4 | 118.6 | 123.7 | 118.6 | 121.2 | 121.2 | 123.7 |
| 60° | 100.5 | 100.5 | 100.5 | 105.7 | 108.3 | 113.4 | 116.0 | 113.4 | 116.0 | 116.0 | 116.0 |
| 62.5° | 92.8 | 95.4 | 95.4 | 98.0 | 100.5 | 108.3 | 110.9 | 108.3 | 110.9 | 110.9 | 110.9 |
| 65° | 87.6 | 87.6 | 90.2 | 92.8 | 95.4 | 100.5 | 103.1 | 103.1 | 103.1 | 105.7 | 103.1 |
| 67.5° | 79.9 | 79.9 | 82.5 | 85.1 | 87.6 | 95.4 | 95.4 | 95.4 | 98.0 | 95.4 | 95.4 |
| 70° | 72.2 | 72.2 | 74.8 | 77.3 | 79.9 | 87.6 | 87.6 | 87.6 | 90.2 | 85.1 | 85.1 |
| 72.5° | 64.4 | 64.4 | 67.0 | 69.6 | 74.8 | 82.5 | 79.9 | 79.9 | 79.9 | 77.3 | 77.3 |
| 75° | 56.7 | 56.7 | 59.3 | 61.9 | 64.4 | 74.8 | 72.2 | 69.6 | 69.6 | 67.0 | 67.0 |
| 77.5° | 46.4 | 46.4 | 49.0 | 54.1 | 56.7 | 64.4 | 61.9 | 59.3 | 56.7 | 56.7 | 56.7 |
| 80° | 36.1 | 38.7 | 41.2 | 43.8 | 46.4 | 51.6 | 49.0 | 46.4 | 43.8 | 43.8 | 43.8 |
| 82.5° | 25.8 | 28.4 | 30.9 | 33.5 | 36.1 | 36.1 | 36.1 | 36.1 | 33.5 | 30.9 | 30.9 |
| 85° | 10.3 | 15.5 | 20.6 | 20.6 | 23.2 | 20.6 | 23.2 | 20.6 | 18.0 | 18.0 | 15.5 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.6 | 5.2 | 7.7 | 7.7 | 7.7 | 7.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P438720
 CATALOG NUMBER: ISW-SA1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 |
| 2.5° | 1804.6 | 1845.8 | 1869.0 | 1910.2 | 1954.1 | 2013.4 | 2062.3 | 2132.0 | 2193.8 | 2206.7 | 2222.2 |
| 5° | 1495.2 | 1549.3 | 1575.1 | 1642.1 | 1745.3 | 1809.7 | 1912.8 | 2021.1 | 2155.2 | 2196.4 | 2250.5 |
| 7.5° | 1124.0 | 1165.2 | 1232.3 | 1291.5 | 1412.7 | 1521.0 | 1660.2 | 1817.4 | 1974.7 | 2064.9 | 2152.6 |
| 10° | 855.9 | 907.4 | 979.6 | 1049.2 | 1167.8 | 1276.1 | 1441.1 | 1616.4 | 1817.4 | 1899.9 | 1992.7 |
| 12.5° | 711.5 | 752.8 | 824.9 | 920.3 | 1031.2 | 1134.3 | 1258.0 | 1448.8 | 1660.2 | 1765.9 | 1879.3 |
| 15° | 574.9 | 618.7 | 708.9 | 814.6 | 922.9 | 1038.9 | 1157.5 | 1340.5 | 1598.3 | 1706.6 | 1814.9 |
| 17.5° | 458.9 | 497.5 | 574.9 | 688.3 | 806.9 | 935.8 | 1080.2 | 1312.2 | 1611.2 | 1745.3 | 1871.6 |
| 20° | 355.8 | 389.3 | 448.6 | 551.7 | 672.8 | 824.9 | 1010.6 | 1301.9 | 1688.5 | 1876.7 | 2003.1 |
| 22.5° | 306.8 | 319.7 | 353.2 | 425.4 | 549.1 | 727.0 | 946.1 | 1309.6 | 1812.3 | 2054.6 | 2199.0 |
| 25° | 273.3 | 283.6 | 296.5 | 340.3 | 438.2 | 626.4 | 889.4 | 1325.1 | 1943.8 | 2255.7 | 2420.7 |
| 27.5° | 252.6 | 257.8 | 265.5 | 286.2 | 358.3 | 543.9 | 832.7 | 1345.7 | 2121.6 | 2459.3 | 2619.2 |
| 30° | 232.0 | 232.0 | 239.7 | 260.4 | 314.5 | 484.7 | 791.4 | 1386.9 | 2296.9 | 2634.6 | 2791.9 |
| 32.5° | 211.4 | 211.4 | 224.3 | 242.3 | 286.2 | 435.7 | 750.2 | 1399.8 | 2428.4 | 2789.3 | 2915.6 |
| 35° | 193.3 | 198.5 | 208.8 | 229.4 | 268.1 | 399.6 | 711.5 | 1376.6 | 2523.8 | 2920.8 | 3049.7 |
| 37.5° | 183.0 | 185.6 | 198.5 | 216.5 | 244.9 | 366.1 | 672.8 | 1345.7 | 2652.7 | 3096.1 | 3196.6 |
| 40° | 170.1 | 175.3 | 188.2 | 206.2 | 229.4 | 340.3 | 629.0 | 1312.2 | 2766.1 | 3292.0 | 3343.6 |
| 42.5° | 162.4 | 167.6 | 177.9 | 195.9 | 219.1 | 309.4 | 587.8 | 1286.4 | 2887.3 | 3459.6 | 3495.7 |
| 45° | 154.7 | 159.8 | 172.7 | 188.2 | 219.1 | 286.2 | 546.5 | 1268.3 | 3005.9 | 3588.5 | 3616.8 |
| 47.5° | 146.9 | 152.1 | 165.0 | 185.6 | 216.5 | 273.3 | 518.2 | 1250.3 | 3080.6 | 3699.3 | 3707.1 |
| 50° | 141.8 | 146.9 | 162.4 | 190.8 | 208.8 | 268.1 | 505.3 | 1268.3 | 3206.9 | 3787.0 | 3763.8 |
| 52.5° | 134.1 | 141.8 | 159.8 | 198.5 | 198.5 | 262.9 | 495.0 | 1332.8 | 3364.2 | 3915.9 | 3856.6 |
| 55° | 131.5 | 136.6 | 154.7 | 190.8 | 180.5 | 250.1 | 495.0 | 1381.8 | 3573.0 | 4171.1 | 4073.1 |
| 57.5° | 123.7 | 128.9 | 149.5 | 177.9 | 165.0 | 229.4 | 489.8 | 1461.7 | 3869.5 | 4452.1 | 4364.4 |
| 60° | 116.0 | 123.7 | 144.4 | 159.8 | 149.5 | 203.7 | 466.6 | 1549.3 | 4073.1 | 4604.2 | 4619.7 |
| 62.5° | 110.9 | 118.6 | 144.4 | 139.2 | 136.6 | 177.9 | 430.5 | 1603.5 | 4052.5 | 4555.2 | 4702.2 |
| 65° | 103.1 | 110.9 | 131.5 | 126.3 | 128.9 | 159.8 | 384.1 | 1577.7 | 3781.8 | 4349.0 | 4606.8 |
| 67.5° | 95.4 | 103.1 | 113.4 | 113.4 | 118.6 | 154.7 | 335.1 | 1428.2 | 3487.9 | 4098.9 | 4395.4 |
| 70° | 87.6 | 92.8 | 98.0 | 103.1 | 108.3 | 152.1 | 296.5 | 1224.5 | 3150.2 | 3859.2 | 4093.8 |
| 72.5° | 77.3 | 79.9 | 85.1 | 90.2 | 100.5 | 144.4 | 281.0 | 995.1 | 2683.6 | 3341.0 | 3704.5 |
| 75° | 67.0 | 69.6 | 74.8 | 79.9 | 87.6 | 136.6 | 257.8 | 755.3 | 2211.9 | 2639.8 | 2993.0 |
| 77.5° | 56.7 | 59.3 | 64.4 | 67.0 | 74.8 | 121.2 | 221.7 | 546.5 | 1722.1 | 1902.5 | 2188.7 |
| 80° | 43.8 | 46.4 | 51.6 | 51.6 | 61.9 | 90.2 | 172.7 | 381.5 | 1209.1 | 1348.3 | 1497.8 |
| 82.5° | 30.9 | 33.5 | 36.1 | 38.7 | 46.4 | 61.9 | 113.4 | 229.4 | 819.8 | 925.5 | 899.7 |
| 85° | 18.0 | 20.6 | 20.6 | 25.8 | 28.4 | 41.2 | 64.4 | 118.6 | 536.2 | 422.8 | 417.6 |
| 87.5° | 7.7 | 7.7 | 7.7 | 10.3 | 10.3 | 15.5 | 20.6 | 23.2 | 51.6 | 18.0 | 12.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P438720

CATALOG NUMBER: ISW-SA1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 | 2036.6 |
| 2.5° | 2245.4 | 2263.4 | 2276.3 | 2271.2 | 2263.4 | 2219.6 | 2175.8 | 2129.4 | 2088.1 | 2088.1 |
| 5° | 2338.2 | 2412.9 | 2443.9 | 2418.1 | 2361.4 | 2271.2 | 2157.7 | 2039.1 | 1982.4 | 1967.0 |
| 7.5° | 2289.2 | 2431.0 | 2505.8 | 2472.2 | 2397.5 | 2232.5 | 2059.8 | 1905.1 | 1820.0 | 1804.6 |
| 10° | 2191.2 | 2376.9 | 2461.9 | 2451.6 | 2369.1 | 2178.4 | 1969.5 | 1794.2 | 1704.0 | 1693.7 |
| 12.5° | 2077.8 | 2258.3 | 2366.5 | 2371.7 | 2317.6 | 2150.0 | 1930.9 | 1722.1 | 1642.1 | 1621.5 |
| 15° | 2008.2 | 2165.5 | 2240.2 | 2222.2 | 2237.6 | 2126.8 | 1946.3 | 1750.4 | 1652.5 | 1634.4 |
| 17.5° | 2010.8 | 2077.8 | 2095.9 | 2067.5 | 2126.8 | 2121.6 | 2034.0 | 1853.5 | 1745.3 | 1727.2 |
| 20° | 2077.8 | 2021.1 | 1964.4 | 1959.2 | 2036.6 | 2139.7 | 2173.2 | 2026.3 | 1902.5 | 1889.6 |
| 22.5° | 2193.8 | 2005.6 | 1887.0 | 1869.0 | 1967.0 | 2157.7 | 2307.3 | 2237.6 | 2121.6 | 2088.1 |
| 25° | 2322.7 | 2021.1 | 1838.1 | 1814.9 | 1902.5 | 2170.6 | 2451.6 | 2454.2 | 2325.3 | 2294.4 |
| 27.5° | 2461.9 | 2070.1 | 1838.1 | 1812.3 | 1905.1 | 2191.2 | 2547.0 | 2650.1 | 2531.5 | 2505.8 |
| 30° | 2585.7 | 2139.7 | 1856.1 | 1827.8 | 1936.0 | 2211.9 | 2611.4 | 2825.4 | 2691.4 | 2655.3 |
| 32.5° | 2660.4 | 2199.0 | 1899.9 | 1848.4 | 1990.2 | 2253.1 | 2670.7 | 2974.9 | 2871.8 | 2822.8 |
| 35° | 2719.7 | 2268.6 | 1972.1 | 1905.1 | 2070.1 | 2320.1 | 2719.7 | 3137.3 | 3039.4 | 3011.0 |
| 37.5° | 2763.5 | 2351.1 | 2046.9 | 1982.4 | 2175.8 | 2410.4 | 2789.3 | 3310.1 | 3279.1 | 3217.3 |
| 40° | 2835.7 | 2402.6 | 2180.9 | 2157.7 | 2358.8 | 2552.2 | 2871.8 | 3459.6 | 3480.2 | 3444.1 |
| 42.5° | 2900.2 | 2503.2 | 2371.7 | 2397.5 | 2593.4 | 2709.4 | 2982.7 | 3570.4 | 3681.3 | 3634.9 |
| 45° | 2951.7 | 2642.4 | 2611.4 | 2696.5 | 2864.1 | 2910.5 | 3044.5 | 3647.8 | 3763.8 | 3732.8 |
| 47.5° | 3023.9 | 2825.4 | 2931.1 | 3042.0 | 3181.2 | 3119.3 | 3109.0 | 3730.3 | 3848.9 | 3817.9 |
| 50° | 3127.0 | 3039.4 | 3250.8 | 3395.1 | 3485.4 | 3289.4 | 3188.9 | 3805.0 | 3980.3 | 3962.3 |
| 52.5° | 3232.7 | 3286.9 | 3575.6 | 3709.6 | 3768.9 | 3500.8 | 3302.3 | 3923.6 | 4135.0 | 4135.0 |
| 55° | 3428.7 | 3529.2 | 3921.0 | 4006.1 | 4086.0 | 3691.6 | 3454.4 | 4101.5 | 4374.8 | 4387.6 |
| 57.5° | 3714.8 | 3789.6 | 4184.0 | 4281.9 | 4302.6 | 3905.6 | 3694.2 | 4349.0 | 4578.4 | 4601.6 |
| 60° | 4011.3 | 4047.4 | 4444.4 | 4532.0 | 4462.4 | 4181.4 | 3975.2 | 4637.7 | 4712.5 | 4699.6 |
| 62.5° | 4338.7 | 4297.4 | 4624.8 | 4686.7 | 4668.6 | 4423.7 | 4328.4 | 4900.7 | 4810.4 | 4761.4 |
| 65° | 4599.0 | 4444.4 | 4717.6 | 4730.5 | 4740.8 | 4591.3 | 4689.3 | 5019.2 | 4851.7 | 4743.4 |
| 67.5° | 4756.3 | 4467.6 | 4529.4 | 4470.1 | 4511.4 | 4547.5 | 4934.2 | 4970.3 | 4676.4 | 4581.0 |
| 70° | 4720.2 | 4140.2 | 3861.7 | 3794.7 | 3797.3 | 4049.9 | 4776.9 | 4663.5 | 4276.8 | 4140.2 |
| 72.5° | 4387.6 | 3480.2 | 3075.5 | 2985.2 | 3003.3 | 3026.5 | 4016.4 | 4070.6 | 3457.0 | 3384.8 |
| 75° | 3694.2 | 2681.1 | 2214.4 | 2193.8 | 2168.0 | 2268.6 | 3212.1 | 2974.9 | 2294.4 | 2312.4 |
| 77.5° | 3013.6 | 1974.7 | 1626.7 | 1521.0 | 1505.5 | 1521.0 | 2191.2 | 1698.9 | 1332.8 | 1276.1 |
| 80° | 2173.2 | 1314.7 | 1214.2 | 1191.0 | 1118.8 | 899.7 | 1147.2 | 1093.0 | 752.8 | 739.9 |
| 82.5° | 1430.8 | 907.4 | 928.1 | 773.4 | 727.0 | 569.7 | 696.0 | 556.8 | 376.4 | 358.3 |
| 85° | 742.4 | 471.8 | 389.3 | 170.1 | 190.8 | 159.8 | 152.1 | 123.7 | 12.9 | 12.9 |
| 87.5° | 25.8 | 10.3 | 7.7 | 7.7 | 5.2 | 2.6 | 2.6 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/05/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K): | 3905 | CRI (Ra): | 71.2 | R9: | -29.7 |
| CIE u': | 0.2273 | R1: | 68.9 | R10: | 46.2 |
| CIE v': | 0.5024 | R2: | 77.0 | R11: | 68.8 |
| Duv: | -0.0008 | R3: | 84.0 | R12: | 45.6 |
| CIE x: | 0.3841 | R4: | 71.6 | R13: | 69.5 |
| CIE y: | 0.3774 | R5: | 68.9 | R14: | 90.7 |
| CIE z: | 0.2385 | R6: | 68.3 | | |
| Peak Wavelength (nm): | 443 | R7: | 78.7 | | |
| Dominant Wavelength (nm): | 579 | R8: | 52.2 | | |
| Purity: | 28.7 | | | | |
| Rf: | 71.7 | | | | |
| Rg: | 96.9 | | | | |



Test Conditions

Stabilization Time: 211M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.8/312%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 2.7 | 620 | 97577 | 25.4 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 4.8 | 625 | 90158 | 19.9 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 8.0 | 630 | 82240 | 14.9 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 13.3 | 635 | 74361 | 11.2 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 20.2 | 640 | 66994 | 8.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 28.5 | 645 | 60405 | 5.8 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 37.4 | 650 | 53806 | 3.9 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 44.9 | 655 | 47610 | 2.7 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 52.6 | 660 | 42018 | 1.8 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 58.4 | 665 | 36742 | 1.2 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.0 | 540 | 96845 | 63.1 | 670 | 32105 | 0.7 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.0 | 545 | 100829 | 67.1 | 675 | 27946 | 0.5 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 0.1 | 550 | 105648 | 71.8 | 680 | 24146 | 0.3 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 0.2 | 555 | 110017 | 75.1 | 685 | 21191 | 0.2 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 0.5 | 560 | 114586 | 77.9 | 690 | 18544 | 0.1 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 1.2 | 565 | 118987 | 79.1 | 695 | 16058 | 0.1 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 2.1 | 570 | 122326 | 79.5 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 2.9 | 575 | 125968 | 78.4 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 2.7 | 580 | 127613 | 75.8 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 2.0 | 585 | 129466 | 71.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 1.5 | 590 | 128813 | 66.6 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 1.3 | 595 | 126387 | 59.9 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 1.0 | 600 | 123477 | 53.2 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 1.1 | 605 | 118718 | 46.0 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 1.2 | 610 | 112091 | 38.5 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 1.7 | 615 | 105039 | 31.7 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 29.3 | 620 | 97577 | 1.2 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 43.0 | 625 | 90158 | 0.8 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 60.8 | 630 | 82240 | 0.5 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 81.1 | 635 | 74361 | 0.3 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 99.6 | 640 | 66994 | 0.2 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 113.9 | 645 | 60405 | 0.1 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 122.6 | 650 | 53806 | 0.1 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 125.0 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 123.1 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.1 | 535 | 94097 | 117.3 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 107.0 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.9 | 545 | 100829 | 96.7 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 3.0 | 550 | 105648 | 86.4 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 9.3 | 555 | 110017 | 75.2 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 23.0 | 560 | 114586 | 64.0 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 45.7 | 565 | 118987 | 53.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 75.5 | 570 | 122326 | 43.2 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 93.8 | 575 | 125968 | 34.3 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 79.3 | 580 | 127613 | 26.3 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 51.3 | 585 | 129466 | 19.8 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 35.6 | 590 | 128813 | 14.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 26.0 | 595 | 126387 | 10.1 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 19.3 | 600 | 123477 | 7.0 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 16.8 | 605 | 118718 | 4.7 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 17.7 | 610 | 112091 | 3.0 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 21.4 | 615 | 105039 | 1.9 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3927.2 M/P: 0.55

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 15.8 | 620 | 97577 | 0.1 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 22.0 | 625 | 90158 | 0.0 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 29.2 | 630 | 82240 | 0.0 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 36.6 | 635 | 74361 | 0.0 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 42.2 | 640 | 66994 | 0.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 44.9 | 645 | 60405 | 0.0 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 44.9 | 650 | 53806 | 0.0 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 42.4 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 38.6 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 33.9 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 28.3 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.6 | 545 | 100829 | 23.4 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 2.1 | 550 | 105648 | 19.0 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 5.9 | 555 | 110017 | 14.8 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 14.3 | 560 | 114586 | 11.3 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 27.3 | 565 | 118987 | 8.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 45.1 | 570 | 122326 | 6.0 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 55.3 | 575 | 125968 | 4.2 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 47.2 | 580 | 127613 | 2.9 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 30.8 | 585 | 129466 | 1.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 21.7 | 590 | 128813 | 1.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 16.1 | 595 | 126387 | 0.8 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 12.0 | 600 | 123477 | 0.5 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 10.3 | 605 | 118718 | 0.3 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 10.5 | 610 | 112091 | 0.2 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 12.1 | 615 | 105039 | 0.1 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

Summary

$R_f = 71.7$
 $R_g = 96.9$
 CIE $R_a = 71.2$
 $R_g = -29.7$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)