

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P633782

Luminaire Tested: GWS-SA2F-740-U-5NQ-W-GRSWH

Issue Date: 1/10/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P633782  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/10/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: McGRAW-EDISON  
Catalog Number: GWS-SA2F-740-U-5NQ-W-GRSWH  
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND  
TYPE V NARROW OPTICS W/ FACTORY INSTALLED GLARE SHIELD, WH  
Light Source: (32) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 14706.7 lumens  
Efficiency: N/A  
Efficacy: 118.1 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B4 - U0 - G1

Input Watts (W): 124.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 0  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P633782

CATALOG NUMBER: GWS-SA2F-740-U-5NQ-W-GRSWH

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 6.6 fc  
 Type V - Short - N/A

REPORT NUMBER: P633782

CATALOG NUMBER: GWS-SA2F-740-U-5NQ-W-GRSWH

## Luminous Intensity Polar Plot



REPORT NUMBER: P633782

CATALOG NUMBER: GWS-SA2F-740-U-5NQ-W-GRSWH


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 7353.4   | 0.0    | 7353.4  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 7353.4   | 0.0    | 7353.4  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 14706.7  | 0.0    | 14706.7 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 258.1   | 1.8       |
| 10°-20°   | 821.6   | 5.6       |
| 20°-30°   | 1520.6  | 10.3      |
| 30°-40°   | 2543.7  | 17.3      |
| 40°-50°   | 3876.2  | 26.4      |
| 50°-60°   | 4342.2  | 29.5      |
| 60°-70°   | 1027.4  | 7.0       |
| 70°-80°   | 277.0   | 1.9       |
| 80°-90°   | 39.9    | 0.3       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 14706.7 | 100.0     |
| 0°-180°   | 14706.7 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P633782


CATALOG NUMBER: GWS-SA2F-740-U-5NQ-W-GRSWH

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |        |
|------|-------------|--------|-----------|-------------------------|------|--------|
|      |             |        |           | B                       | U    | G      |
| FL   | (0°-30°)    | 1300.2 | 8.8       |                         |      |        |
| FM   | (30°-60°)   | 5381.1 | 36.6      |                         |      |        |
| FH   | (60°-80°)   | 652.2  | 4.4       |                         |      | G0/660 |
| FVH  | (80°-90°)   | 19.9   | 0.1       |                         |      | G1/100 |
| BL   | (0°-30°)    | 1300.2 | 8.8       | B3/2500                 |      |        |
| BM   | (30°-60°)   | 5381.1 | 36.6      | B4/8500                 |      |        |
| BH   | (60°-80°)   | 652.2  | 4.4       | B2/1000                 |      | G0/660 |
| BVH  | (80°-90°)   | 19.9   | 0.1       |                         |      | G1/100 |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |        |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |        |

**BUG Rating: B4-U0-G1**

Type V Short



REPORT NUMBER: P633782

CATALOG NUMBER: GWS-SA2F-740-U-5NQ-W-GRSWH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2645.8 | 2645.8 | 2645.8 | 2645.8 | 2645.8 | 2645.8 | 2645.8 | 2645.8 | 2645.8 | 2645.8 | 2645.8 |
| 2.5°  | 2640.0 | 2640.0 | 2644.6 | 2650.4 | 2651.6 | 2663.2 | 2660.9 | 2656.2 | 2653.9 | 2649.3 | 2659.7 |
| 5°    | 2669.0 | 2670.2 | 2673.7 | 2677.2 | 2674.8 | 2684.2 | 2680.7 | 2674.8 | 2671.4 | 2665.5 | 2676.0 |
| 7.5°  | 2707.4 | 2707.4 | 2710.9 | 2715.6 | 2713.2 | 2727.2 | 2720.2 | 2712.1 | 2706.2 | 2699.3 | 2708.6 |
| 10°   | 2742.3 | 2744.6 | 2748.1 | 2757.4 | 2762.1 | 2777.2 | 2772.5 | 2760.9 | 2751.6 | 2743.5 | 2753.9 |
| 12.5° | 2794.6 | 2797.0 | 2800.5 | 2813.2 | 2821.4 | 2836.5 | 2829.5 | 2813.2 | 2799.3 | 2787.7 | 2799.3 |
| 15°   | 2862.1 | 2859.8 | 2869.1 | 2885.3 | 2895.8 | 2909.8 | 2901.6 | 2873.7 | 2855.1 | 2840.0 | 2851.6 |
| 17.5° | 2930.7 | 2929.5 | 2938.8 | 2959.8 | 2974.9 | 2993.5 | 2979.5 | 2947.0 | 2927.2 | 2908.6 | 2920.2 |
| 20°   | 3005.1 | 3008.6 | 3017.9 | 3037.7 | 3059.8 | 3084.2 | 3072.6 | 3037.7 | 3015.6 | 2994.7 | 3004.0 |
| 22.5° | 3097.0 | 3098.2 | 3108.6 | 3134.2 | 3163.3 | 3186.6 | 3179.6 | 3136.6 | 3108.6 | 3086.5 | 3098.2 |
| 25°   | 3207.5 | 3206.3 | 3220.3 | 3250.5 | 3291.2 | 3314.5 | 3299.4 | 3251.7 | 3221.4 | 3195.9 | 3205.2 |
| 27.5° | 3334.3 | 3333.1 | 3354.0 | 3393.6 | 3451.7 | 3484.3 | 3452.9 | 3393.6 | 3351.7 | 3315.7 | 3323.8 |
| 30°   | 3493.6 | 3490.1 | 3513.4 | 3566.9 | 3642.4 | 3697.1 | 3650.6 | 3568.0 | 3513.4 | 3475.0 | 3483.1 |
| 32.5° | 3670.4 | 3675.0 | 3704.1 | 3776.2 | 3871.6 | 3942.5 | 3872.7 | 3780.8 | 3707.6 | 3651.8 | 3661.1 |
| 35°   | 3864.6 | 3864.6 | 3923.9 | 4013.4 | 4149.5 | 4243.7 | 4135.5 | 4003.0 | 3905.3 | 3828.5 | 3830.8 |
| 37.5° | 4080.9 | 4083.2 | 4161.1 | 4284.4 | 4462.3 | 4572.8 | 4426.3 | 4262.3 | 4143.7 | 4061.1 | 4056.5 |
| 40°   | 4344.9 | 4351.9 | 4432.1 | 4569.3 | 4769.4 | 4870.6 | 4713.5 | 4553.1 | 4432.1 | 4334.4 | 4325.1 |
| 42.5° | 4642.6 | 4644.9 | 4729.8 | 4853.1 | 5021.7 | 5082.2 | 4958.9 | 4827.5 | 4728.7 | 4640.3 | 4631.0 |
| 45°   | 4926.4 | 4920.6 | 4993.8 | 5085.7 | 5183.4 | 5189.2 | 5120.6 | 5067.1 | 4981.0 | 4905.4 | 4891.5 |
| 47.5° | 5147.3 | 5142.7 | 5209.0 | 5259.0 | 5270.6 | 5213.6 | 5235.7 | 5243.9 | 5143.9 | 5041.5 | 5014.8 |
| 50°   | 5282.2 | 5291.5 | 5354.4 | 5382.3 | 5313.6 | 5220.6 | 5304.3 | 5283.4 | 5140.4 | 5006.6 | 4963.6 |
| 52.5° | 5363.7 | 5377.6 | 5486.9 | 5557.9 | 5486.9 | 5398.5 | 5410.2 | 5286.9 | 5081.1 | 4904.3 | 4848.5 |
| 55°   | 5157.8 | 5213.6 | 5449.7 | 5763.7 | 5880.0 | 5818.4 | 5597.4 | 5279.9 | 4898.5 | 4641.4 | 4593.8 |
| 57.5° | 3822.7 | 3911.1 | 4261.2 | 4941.5 | 5648.6 | 5873.0 | 5227.6 | 4426.3 | 3848.3 | 3518.0 | 3490.1 |
| 60°   | 1951.5 | 2050.3 | 2330.6 | 3029.6 | 3939.0 | 4255.3 | 3641.3 | 2834.2 | 2252.7 | 1985.2 | 1955.0 |
| 62.5° | 796.6  | 812.9  | 904.8  | 1174.6 | 1741.0 | 2008.5 | 1764.2 | 1238.6 | 930.4  | 857.1  | 858.3  |
| 65°   | 626.8  | 630.3  | 625.7  | 642.0  | 729.2  | 809.4  | 747.8  | 657.1  | 640.8  | 648.9  | 643.1  |
| 67.5° | 546.6  | 547.8  | 544.3  | 544.3  | 547.8  | 544.3  | 551.3  | 554.7  | 557.1  | 566.4  | 560.6  |
| 70°   | 457.1  | 458.2  | 458.2  | 460.5  | 459.4  | 453.6  | 464.0  | 468.7  | 469.8  | 475.7  | 472.2  |
| 72.5° | 353.5  | 357.0  | 359.4  | 360.5  | 359.4  | 355.9  | 361.7  | 369.8  | 368.7  | 374.5  | 368.7  |
| 75°   | 239.6  | 244.2  | 246.6  | 251.2  | 250.0  | 250.0  | 257.0  | 260.5  | 257.0  | 261.7  | 257.0  |
| 77.5° | 136.1  | 139.6  | 146.5  | 151.2  | 155.8  | 159.3  | 164.0  | 166.3  | 165.1  | 167.5  | 165.1  |
| 80°   | 79.1   | 80.2   | 86.1   | 88.4   | 94.2   | 100.0  | 104.7  | 107.0  | 108.2  | 109.3  | 108.2  |
| 82.5° | 45.4   | 46.5   | 48.8   | 51.2   | 55.8   | 60.5   | 65.1   | 68.6   | 68.6   | 69.8   | 68.6   |
| 85°   | 22.1   | 22.1   | 23.3   | 24.4   | 26.7   | 30.2   | 33.7   | 37.2   | 38.4   | 38.4   | 38.4   |
| 87.5° | 3.5    | 3.5    | 4.7    | 4.7    | 5.8    | 7.0    | 9.3    | 11.6   | 12.8   | 12.8   | 12.8   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2101-121-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 03/05/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**  
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

### Spectral Parameters

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3905    | CRI (Ra): | 71.2 |      |       |
| CIE u':                   | 0.2273  | R1:       | 68.9 | R9:  | -29.7 |
| CIE v':                   | 0.5024  | R2:       | 77.0 | R10: | 46.2  |
| Duv:                      | -0.0008 | R3:       | 84.0 | R11: | 68.8  |
| CIE x:                    | 0.3841  | R4:       | 71.6 | R12: | 45.6  |
| CIE y:                    | 0.3774  | R5:       | 68.9 | R13: | 69.5  |
| CIE z:                    | 0.2385  | R6:       | 68.3 | R14: | 90.7  |
| Peak Wavelength (nm):     | 443     | R7:       | 78.7 |      |       |
| Dominant Wavelength (nm): | 579     | R8:       | 52.2 |      |       |
| Purity:                   | 28.7    |           |      |      |       |
| Rf:                       | 71.7    |           |      |      |       |
| Rg:                       | 96.9    |           |      |      |       |



### Test Conditions

Stabilization Time: 211M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/312%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-2

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

### Photopic Flux vs. Wavelength




#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2304             | 0.0              | 490       | 19043            | 2.7              | 620       | 97577            | 25.4             | 750       | 4830             | 0.0              | 880       | 3505             | 0.0              |
| 365       | 2150             | 0.0              | 495       | 26606            | 4.8              | 625       | 90158            | 19.9             | 755       | 4664             | 0.0              | 885       | 2991             | 0.0              |
| 370       | 2146             | 0.0              | 500       | 36376            | 8.0              | 630       | 82240            | 14.9             | 760       | 4006             | 0.0              | 890       | 2327             | 0.0              |
| 375       | 2332             | 0.0              | 505       | 47714            | 13.3             | 635       | 74361            | 11.2             | 765       | 3715             | 0.0              | 895       | 2775             | 0.0              |
| 380       | 2527             | 0.0              | 510       | 58741            | 20.2             | 640       | 66994            | 8.0              | 770       | 3696             | 0.0              | 900       | 2141             | 0.0              |
| 385       | 2304             | 0.0              | 515       | 68716            | 28.5             | 645       | 60405            | 5.8              | 775       | 3117             | 0.0              | 905       | 2421             | 0.0              |
| 390       | 2064             | 0.0              | 520       | 77136            | 37.4             | 650       | 53806            | 3.9              | 780       | 3062             | 0.0              | 910       | 2200             | 0.0              |
| 395       | 1856             | 0.0              | 525       | 83567            | 44.9             | 655       | 47610            | 2.7              | 785       | 2907             | 0.0              | 915       | 2716             | 0.0              |
| 400       | 1856             | 0.0              | 530       | 89283            | 52.6             | 660       | 42018            | 1.8              | 790       | 2655             | 0.0              | 920       | 2656             | 0.0              |
| 405       | 2374             | 0.0              | 535       | 94097            | 58.4             | 665       | 36742            | 1.2              | 795       | 2467             | 0.0              | 925       | 2671             | 0.0              |
| 410       | 4084             | 0.0              | 540       | 96845            | 63.1             | 670       | 32105            | 0.7              | 800       | 2609             | 0.0              | 930       | 3292             | 0.0              |
| 415       | 8543             | 0.0              | 545       | 100829           | 67.1             | 675       | 27946            | 0.5              | 805       | 2293             | 0.0              | 935       | 3188             | 0.0              |
| 420       | 18394            | 0.1              | 550       | 105648           | 71.8             | 680       | 24146            | 0.3              | 810       | 2188             | 0.0              | 940       | 1997             | 0.0              |
| 425       | 37987            | 0.2              | 555       | 110017           | 75.1             | 685       | 21191            | 0.2              | 815       | 2386             | 0.0              | 945       | 2623             | 0.0              |
| 430       | 67605            | 0.5              | 560       | 114586           | 77.9             | 690       | 18544            | 0.1              | 820       | 2712             | 0.0              | 950       | 2969             | 0.0              |
| 435       | 102160           | 1.2              | 565       | 118987           | 79.1             | 695       | 16058            | 0.1              | 825       | 2473             | 0.0              | 955       | 2277             | 0.0              |
| 440       | 135103           | 2.1              | 570       | 122326           | 79.5             | 700       | 14133            | 0.0              | 830       | 1969             | 0.0              | 960       | 4267             | 0.0              |
| 445       | 140126           | 2.9              | 575       | 125968           | 78.4             | 705       | 12309            | 0.0              | 835       | 1917             | 0.0              | 965       | 2034             | 0.0              |
| 450       | 102339           | 2.7              | 580       | 127613           | 75.8             | 710       | 11142            | 0.0              | 840       | 2248             | 0.0              | 970       | 3586             | 0.0              |
| 455       | 58751            | 2.0              | 585       | 129466           | 71.9             | 715       | 10143            | 0.0              | 845       | 2266             | 0.0              | 975       | 2505             | 0.0              |
| 460       | 36892            | 1.5              | 590       | 128813           | 66.6             | 720       | 9072             | 0.0              | 850       | 2558             | 0.0              | 980       | 2666             | 0.0              |
| 465       | 24637            | 1.3              | 595       | 126387           | 59.9             | 725       | 8130             | 0.0              | 855       | 2767             | 0.0              | 985       | 2934             | 0.0              |
| 470       | 16738            | 1.0              | 600       | 123477           | 53.2             | 730       | 7149             | 0.0              | 860       | 2826             | 0.0              | 990       | 4120             | 0.0              |
| 475       | 13456            | 1.1              | 605       | 118718           | 46.0             | 735       | 6311             | 0.0              | 865       | 2385             | 0.0              | 995       | 3858             | 0.0              |
| 480       | 13081            | 1.2              | 610       | 112091           | 38.5             | 740       | 5711             | 0.0              | 870       | 3194             | 0.0              | 1000      | 3405             | 0.0              |
| 485       | 14734            | 1.7              | 615       | 105039           | 31.7             | 745       | 5111             | 0.0              | 875       | 3189             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-2


### Scotopic Flux vs. Wavelength


**Scotopic Lumens: 10425.8**
**S/P: 1.47**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 2304                          | 0.0                            | 490               | 19043                         | 29.3                           | 620               | 97577                         | 1.2                            | 750               | 4830                          | 0.0                            | 880               | 3505                          | 0.0                            |
| 365               | 2150                          | 0.0                            | 495               | 26606                         | 43.0                           | 625               | 90158                         | 0.8                            | 755               | 4664                          | 0.0                            | 885               | 2991                          | 0.0                            |
| 370               | 2146                          | 0.0                            | 500               | 36376                         | 60.8                           | 630               | 82240                         | 0.5                            | 760               | 4006                          | 0.0                            | 890               | 2327                          | 0.0                            |
| 375               | 2332                          | 0.0                            | 505               | 47714                         | 81.1                           | 635               | 74361                         | 0.3                            | 765               | 3715                          | 0.0                            | 895               | 2775                          | 0.0                            |
| 380               | 2527                          | 0.0                            | 510               | 58741                         | 99.6                           | 640               | 66994                         | 0.2                            | 770               | 3696                          | 0.0                            | 900               | 2141                          | 0.0                            |
| 385               | 2304                          | 0.0                            | 515               | 68716                         | 113.9                          | 645               | 60405                         | 0.1                            | 775               | 3117                          | 0.0                            | 905               | 2421                          | 0.0                            |
| 390               | 2064                          | 0.0                            | 520               | 77136                         | 122.6                          | 650               | 53806                         | 0.1                            | 780               | 3062                          | 0.0                            | 910               | 2200                          | 0.0                            |
| 395               | 1856                          | 0.0                            | 525               | 83567                         | 125.0                          | 655               | 47610                         | 0.0                            | 785               | 2907                          | 0.0                            | 915               | 2716                          | 0.0                            |
| 400               | 1856                          | 0.0                            | 530               | 89283                         | 123.1                          | 660               | 42018                         | 0.0                            | 790               | 2655                          | 0.0                            | 920               | 2656                          | 0.0                            |
| 405               | 2374                          | 0.1                            | 535               | 94097                         | 117.3                          | 665               | 36742                         | 0.0                            | 795               | 2467                          | 0.0                            | 925               | 2671                          | 0.0                            |
| 410               | 4084                          | 0.2                            | 540               | 96845                         | 107.0                          | 670               | 32105                         | 0.0                            | 800               | 2609                          | 0.0                            | 930               | 3292                          | 0.0                            |
| 415               | 8543                          | 0.9                            | 545               | 100829                        | 96.7                           | 675               | 27946                         | 0.0                            | 805               | 2293                          | 0.0                            | 935               | 3188                          | 0.0                            |
| 420               | 18394                         | 3.0                            | 550               | 105648                        | 86.4                           | 680               | 24146                         | 0.0                            | 810               | 2188                          | 0.0                            | 940               | 1997                          | 0.0                            |
| 425               | 37987                         | 9.3                            | 555               | 110017                        | 75.2                           | 685               | 21191                         | 0.0                            | 815               | 2386                          | 0.0                            | 945               | 2623                          | 0.0                            |
| 430               | 67605                         | 23.0                           | 560               | 114586                        | 64.0                           | 690               | 18544                         | 0.0                            | 820               | 2712                          | 0.0                            | 950               | 2969                          | 0.0                            |
| 435               | 102160                        | 45.7                           | 565               | 118987                        | 53.4                           | 695               | 16058                         | 0.0                            | 825               | 2473                          | 0.0                            | 955               | 2277                          | 0.0                            |
| 440               | 135103                        | 75.5                           | 570               | 122326                        | 43.2                           | 700               | 14133                         | 0.0                            | 830               | 1969                          | 0.0                            | 960               | 4267                          | 0.0                            |
| 445               | 140126                        | 93.8                           | 575               | 125968                        | 34.3                           | 705               | 12309                         | 0.0                            | 835               | 1917                          | 0.0                            | 965               | 2034                          | 0.0                            |
| 450               | 102339                        | 79.3                           | 580               | 127613                        | 26.3                           | 710               | 11142                         | 0.0                            | 840               | 2248                          | 0.0                            | 970               | 3586                          | 0.0                            |
| 455               | 58751                         | 51.3                           | 585               | 129466                        | 19.8                           | 715               | 10143                         | 0.0                            | 845               | 2266                          | 0.0                            | 975               | 2505                          | 0.0                            |
| 460               | 36892                         | 35.6                           | 590               | 128813                        | 14.3                           | 720               | 9072                          | 0.0                            | 850               | 2558                          | 0.0                            | 980               | 2666                          | 0.0                            |
| 465               | 24637                         | 26.0                           | 595               | 126387                        | 10.1                           | 725               | 8130                          | 0.0                            | 855               | 2767                          | 0.0                            | 985               | 2934                          | 0.0                            |
| 470               | 16738                         | 19.3                           | 600               | 123477                        | 7.0                            | 730               | 7149                          | 0.0                            | 860               | 2826                          | 0.0                            | 990               | 4120                          | 0.0                            |
| 475               | 13456                         | 16.8                           | 605               | 118718                        | 4.7                            | 735               | 6311                          | 0.0                            | 865               | 2385                          | 0.0                            | 995               | 3858                          | 0.0                            |
| 480               | 13081                         | 17.7                           | 610               | 112091                        | 3.0                            | 740               | 5711                          | 0.0                            | 870               | 3194                          | 0.0                            | 1000              | 3405                          | 0.0                            |
| 485               | 14734                         | 21.4                           | 615               | 105039                        | 1.9                            | 745               | 5111                          | 0.0                            | 875               | 3189                          | 0.0                            |                   |                               |                                |

REPORT NUMBER: SP1-2101-121-2

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: 3927.2      M/P: 0.55**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2304             | 0.0              | 490       | 19043            | 15.8             | 620       | 97577            | 0.1              | 750       | 4830             | 0.0              | 880       | 3505             | 0.0              |
| 365       | 2150             | 0.0              | 495       | 26606            | 22.0             | 625       | 90158            | 0.0              | 755       | 4664             | 0.0              | 885       | 2991             | 0.0              |
| 370       | 2146             | 0.0              | 500       | 36376            | 29.2             | 630       | 82240            | 0.0              | 760       | 4006             | 0.0              | 890       | 2327             | 0.0              |
| 375       | 2332             | 0.0              | 505       | 47714            | 36.6             | 635       | 74361            | 0.0              | 765       | 3715             | 0.0              | 895       | 2775             | 0.0              |
| 380       | 2527             | 0.0              | 510       | 58741            | 42.2             | 640       | 66994            | 0.0              | 770       | 3696             | 0.0              | 900       | 2141             | 0.0              |
| 385       | 2304             | 0.0              | 515       | 68716            | 44.9             | 645       | 60405            | 0.0              | 775       | 3117             | 0.0              | 905       | 2421             | 0.0              |
| 390       | 2064             | 0.0              | 520       | 77136            | 44.9             | 650       | 53806            | 0.0              | 780       | 3062             | 0.0              | 910       | 2200             | 0.0              |
| 395       | 1856             | 0.0              | 525       | 83567            | 42.4             | 655       | 47610            | 0.0              | 785       | 2907             | 0.0              | 915       | 2716             | 0.0              |
| 400       | 1856             | 0.0              | 530       | 89283            | 38.6             | 660       | 42018            | 0.0              | 790       | 2655             | 0.0              | 920       | 2656             | 0.0              |
| 405       | 2374             | 0.0              | 535       | 94097            | 33.9             | 665       | 36742            | 0.0              | 795       | 2467             | 0.0              | 925       | 2671             | 0.0              |
| 410       | 4084             | 0.2              | 540       | 96845            | 28.3             | 670       | 32105            | 0.0              | 800       | 2609             | 0.0              | 930       | 3292             | 0.0              |
| 415       | 8543             | 0.6              | 545       | 100829           | 23.4             | 675       | 27946            | 0.0              | 805       | 2293             | 0.0              | 935       | 3188             | 0.0              |
| 420       | 18394            | 2.1              | 550       | 105648           | 19.0             | 680       | 24146            | 0.0              | 810       | 2188             | 0.0              | 940       | 1997             | 0.0              |
| 425       | 37987            | 5.9              | 555       | 110017           | 14.8             | 685       | 21191            | 0.0              | 815       | 2386             | 0.0              | 945       | 2623             | 0.0              |
| 430       | 67605            | 14.3             | 560       | 114586           | 11.3             | 690       | 18544            | 0.0              | 820       | 2712             | 0.0              | 950       | 2969             | 0.0              |
| 435       | 102160           | 27.3             | 565       | 118987           | 8.4              | 695       | 16058            | 0.0              | 825       | 2473             | 0.0              | 955       | 2277             | 0.0              |
| 440       | 135103           | 45.1             | 570       | 122326           | 6.0              | 700       | 14133            | 0.0              | 830       | 1969             | 0.0              | 960       | 4267             | 0.0              |
| 445       | 140126           | 55.3             | 575       | 125968           | 4.2              | 705       | 12309            | 0.0              | 835       | 1917             | 0.0              | 965       | 2034             | 0.0              |
| 450       | 102339           | 47.2             | 580       | 127613           | 2.9              | 710       | 11142            | 0.0              | 840       | 2248             | 0.0              | 970       | 3586             | 0.0              |
| 455       | 58751            | 30.8             | 585       | 129466           | 1.9              | 715       | 10143            | 0.0              | 845       | 2266             | 0.0              | 975       | 2505             | 0.0              |
| 460       | 36892            | 21.7             | 590       | 128813           | 1.3              | 720       | 9072             | 0.0              | 850       | 2558             | 0.0              | 980       | 2666             | 0.0              |
| 465       | 24637            | 16.1             | 595       | 126387           | 0.8              | 725       | 8130             | 0.0              | 855       | 2767             | 0.0              | 985       | 2934             | 0.0              |
| 470       | 16738            | 12.0             | 600       | 123477           | 0.5              | 730       | 7149             | 0.0              | 860       | 2826             | 0.0              | 990       | 4120             | 0.0              |
| 475       | 13456            | 10.3             | 605       | 118718           | 0.3              | 735       | 6311             | 0.0              | 865       | 2385             | 0.0              | 995       | 3858             | 0.0              |
| 480       | 13081            | 10.5             | 610       | 112091           | 0.2              | 740       | 5711             | 0.0              | 870       | 3194             | 0.0              | 1000      | 3405             | 0.0              |
| 485       | 14734            | 12.1             | 615       | 105039           | 0.1              | 745       | 5111             | 0.0              | 875       | 3189             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-2

TM-30-18

### Summary

$R_f = 71.7$   
 $R_g = 96.9$   
 CIE  $R_a = 71.2$   
 $R_g = -29.7$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 |            |



### Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)