

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P633460

Luminaire Tested: GWS-SA2E-827-U-AFL-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P633460
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-45)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA2E-827-U-AFL-W
Description: GALLEON WALL SLIM LUMINAIRE. (2) LIGHTSQUARES WITH 16 LEDS EACH AND AUTOMOTIVE FRONTLINE OPTICS
Light Source: (32) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10922.6 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B2 - U0 - G1


Input Watts (W): 108.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P633460
 CATALOG NUMBER: GWS-SA2E-827-U-AFL-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 8.2 fc
 Type II - Short - N/A

REPORT NUMBER: P633460
CATALOG NUMBER: GWS-SA2E-827-U-AFL-W

Luminous Intensity Polar Plot



— Vertical Plane Through 59-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P633460

CATALOG NUMBER: GWS-SA2E-827-U-AFL-W

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 1695.1 | 0.0 | 1695.1 |
| | % Fixture | 15.5 | 0.0 | 15.5 |
| Street Side | Lumens | 9227.5 | 0.0 | 9227.5 |
| | % Fixture | 84.5 | 0.0 | 84.5 |
| Total | Lumens | 10922.6 | 0.0 | 10922.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 249.0 | 2.3 |
| 10°-20° | 630.9 | 5.8 |
| 20°-30° | 1022.6 | 9.4 |
| 30°-40° | 1645.1 | 15.1 |
| 40°-50° | 2554.6 | 23.4 |
| 50°-60° | 2751.7 | 25.2 |
| 60°-70° | 1597.0 | 14.6 |
| 70°-80° | 416.9 | 3.8 |
| 80°-90° | 54.9 | 0.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 10922.6 | 100.0 |
| 0°-180° | 10922.6 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P633460


CATALOG NUMBER: GWS-SA2E-827-U-AFL-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1340.1 | 12.3 | | | |
| FM (30°-60°) | 6199.8 | 56.8 | | | |
| FH (60°-80°) | 1661.3 | 15.2 | | | G1/1800 |
| FVH (80°-90°) | 26.3 | 0.2 | | | G1/100 |
| BL (0°-30°) | 562.4 | 5.1 | B2/1000 | | |
| BM (30°-60°) | 751.6 | 6.9 | B1/1000 | | |
| BH (60°-80°) | 352.6 | 3.2 | B1/500 | | G1/500 |
| BVH (80°-90°) | 28.6 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G1

Type II Short





REPORT NUMBER: P633460
 CATALOG NUMBER: GWS-SA2E-827-U-AFL-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 59° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2681.3 | 2681.3 | 2681.3 | 2681.3 | 2681.3 | 2681.3 | 2681.3 | 2681.3 | 2681.3 | 2681.3 | 2681.3 |
| 2.5° | 3041.1 | 3015.8 | 3033.5 | 3001.9 | 2988.9 | 2954.3 | 2909.7 | 2879.7 | 2833.5 | 2773.6 | 2721.3 |
| 5° | 3343.3 | 3325.6 | 3329.5 | 3295.7 | 3265.7 | 3208.0 | 3116.5 | 3065.7 | 2987.3 | 2866.6 | 2754.3 |
| 7.5° | 3334.1 | 3354.9 | 3366.4 | 3395.6 | 3404.1 | 3398.7 | 3316.4 | 3245.7 | 3159.6 | 2978.1 | 2808.9 |
| 10° | 2988.9 | 3028.1 | 3063.4 | 3163.4 | 3284.9 | 3438.7 | 3457.9 | 3415.6 | 3328.7 | 3120.3 | 2874.3 |
| 12.5° | 2612.8 | 2642.8 | 2674.4 | 2794.3 | 2980.4 | 3288.0 | 3496.4 | 3522.5 | 3487.9 | 3261.1 | 2948.1 |
| 15° | 2428.3 | 2442.1 | 2472.1 | 2551.3 | 2699.7 | 3041.1 | 3429.5 | 3544.0 | 3606.3 | 3410.2 | 3031.1 |
| 17.5° | 2420.6 | 2426.8 | 2441.4 | 2483.7 | 2586.7 | 2850.4 | 3308.7 | 3501.0 | 3699.4 | 3567.9 | 3128.0 |
| 20° | 2579.8 | 2563.6 | 2554.4 | 2553.6 | 2604.4 | 2786.6 | 3191.9 | 3431.8 | 3743.2 | 3729.3 | 3231.8 |
| 22.5° | 2800.5 | 2805.8 | 2785.9 | 2736.6 | 2730.5 | 2832.0 | 3133.4 | 3361.8 | 3756.3 | 3872.4 | 3328.0 |
| 25° | 3113.4 | 3140.3 | 3081.1 | 2987.3 | 2941.2 | 2963.5 | 3169.6 | 3340.3 | 3754.7 | 3991.5 | 3387.9 |
| 27.5° | 3478.7 | 3499.4 | 3439.5 | 3316.4 | 3221.1 | 3167.2 | 3277.2 | 3404.1 | 3767.8 | 4094.6 | 3424.1 |
| 30° | 3894.7 | 3901.6 | 3819.3 | 3690.1 | 3550.9 | 3435.6 | 3456.4 | 3535.6 | 3834.7 | 4229.9 | 3466.4 |
| 32.5° | 4402.9 | 4432.1 | 4307.6 | 4103.0 | 3908.5 | 3760.9 | 3697.0 | 3747.8 | 3979.2 | 4389.9 | 3531.7 |
| 35° | 5048.1 | 5058.1 | 4899.7 | 4606.7 | 4331.4 | 4126.9 | 3993.1 | 4020.0 | 4199.2 | 4613.6 | 3630.1 |
| 37.5° | 5656.3 | 5666.3 | 5497.9 | 5225.7 | 4832.0 | 4552.1 | 4358.3 | 4346.0 | 4480.6 | 4929.6 | 3790.9 |
| 40° | 6042.3 | 6070.7 | 5995.4 | 5824.7 | 5448.7 | 5071.1 | 4808.2 | 4765.9 | 4849.7 | 5316.4 | 4014.6 |
| 42.5° | 6249.9 | 6262.2 | 6260.7 | 6283.0 | 6059.2 | 5684.0 | 5315.7 | 5231.1 | 5287.2 | 5734.0 | 4240.7 |
| 45° | 6251.4 | 6282.2 | 6364.5 | 6579.0 | 6589.0 | 6355.3 | 5956.9 | 5824.7 | 5773.2 | 6154.6 | 4476.7 |
| 47.5° | 5971.6 | 6004.6 | 6230.7 | 6652.8 | 6964.3 | 7017.3 | 6725.1 | 6459.8 | 6243.0 | 6516.7 | 4670.5 |
| 50° | 5124.2 | 5207.2 | 5637.8 | 6384.5 | 7038.1 | 7547.9 | 7457.9 | 7098.0 | 6660.5 | 6796.6 | 4792.0 |
| 52.5° | 4388.3 | 4385.2 | 4650.5 | 5626.3 | 6729.7 | 7781.6 | 8166.9 | 7754.7 | 7073.4 | 6974.2 | 4822.8 |
| 55° | 3213.4 | 3231.1 | 3502.5 | 4303.0 | 5907.0 | 7555.6 | 8556.7 | 8359.1 | 7547.1 | 7068.8 | 4810.5 |
| 57.5° | 1666.3 | 1753.9 | 2032.3 | 2745.9 | 4488.3 | 6777.4 | 8452.9 | 8584.4 | 8028.5 | 7135.7 | 4826.6 |
| 60° | 842.0 | 825.1 | 925.0 | 1311.0 | 2600.5 | 5293.4 | 7813.2 | 8232.2 | 8115.4 | 7188.0 | 4836.6 |
| 62.5° | 562.1 | 557.5 | 529.8 | 607.5 | 1062.7 | 3135.0 | 6660.5 | 7248.0 | 7511.7 | 7065.0 | 4709.0 |
| 65° | 486.7 | 477.5 | 426.8 | 423.7 | 516.0 | 1300.3 | 4882.0 | 5697.8 | 6208.4 | 6518.3 | 4403.7 |
| 67.5° | 438.3 | 424.5 | 372.9 | 347.6 | 370.6 | 571.3 | 2751.3 | 3821.6 | 4584.4 | 5512.5 | 3734.7 |
| 70° | 391.4 | 384.5 | 332.9 | 296.0 | 293.7 | 348.3 | 1013.5 | 1972.3 | 2805.1 | 3760.9 | 2730.5 |
| 72.5° | 350.6 | 338.3 | 294.5 | 259.1 | 241.4 | 246.8 | 439.8 | 759.7 | 1451.8 | 2346.0 | 1633.2 |
| 75° | 303.7 | 294.5 | 256.1 | 220.7 | 199.2 | 180.7 | 268.4 | 351.4 | 662.1 | 1115.0 | 771.2 |
| 77.5° | 234.5 | 228.4 | 202.2 | 175.3 | 163.0 | 134.6 | 163.0 | 221.5 | 306.0 | 469.8 | 401.4 |
| 80° | 136.1 | 139.9 | 150.7 | 136.9 | 120.0 | 96.1 | 106.1 | 127.6 | 183.8 | 254.5 | 227.6 |
| 82.5° | 68.4 | 73.0 | 97.7 | 79.2 | 71.5 | 56.1 | 63.1 | 75.4 | 96.1 | 140.7 | 89.2 |
| 85° | 5.4 | 5.4 | 17.7 | 20.0 | 24.6 | 20.0 | 25.4 | 30.8 | 43.8 | 56.1 | 30.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.3 | 3.8 | 6.9 | 13.1 | 8.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P633460
 CATALOG NUMBER: GWS-SA2E-827-U-AFL-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2681.3 | 2681.3 | 2681.3 | 2681.3 | 2681.3 | 2681.3 | 2681.3 | 2681.3 | 2681.3 | 2681.3 | 2681.3 |
| 2.5° | 2685.9 | 2646.7 | 2599.8 | 2561.3 | 2502.1 | 2470.6 | 2430.6 | 2381.4 | 2361.4 | 2352.2 | 2346.8 |
| 5° | 2691.3 | 2622.1 | 2522.1 | 2429.8 | 2327.6 | 2246.8 | 2156.9 | 2063.1 | 2009.2 | 1996.2 | 1986.9 |
| 7.5° | 2711.3 | 2614.4 | 2455.2 | 2303.0 | 2113.0 | 1936.9 | 1765.5 | 1595.5 | 1508.7 | 1475.6 | 1472.5 |
| 10° | 2739.0 | 2611.3 | 2387.5 | 2134.6 | 1813.9 | 1535.6 | 1334.9 | 1201.8 | 1145.7 | 1127.3 | 1121.1 |
| 12.5° | 2773.6 | 2609.0 | 2298.3 | 1900.8 | 1468.7 | 1205.7 | 1091.1 | 1069.6 | 1077.3 | 1075.7 | 1075.7 |
| 15° | 2817.4 | 2612.1 | 2190.7 | 1636.3 | 1188.0 | 1046.5 | 1048.8 | 1074.2 | 1098.0 | 1101.9 | 1101.9 |
| 17.5° | 2865.1 | 2609.0 | 2034.6 | 1371.0 | 1019.6 | 1008.8 | 1044.2 | 1079.6 | 1101.1 | 1104.2 | 1104.2 |
| 20° | 2916.6 | 2594.4 | 1837.8 | 1121.1 | 945.8 | 985.0 | 1023.5 | 1051.1 | 1064.2 | 1067.3 | 1067.3 |
| 22.5° | 2947.3 | 2552.9 | 1624.0 | 948.9 | 898.9 | 947.3 | 972.7 | 1001.2 | 1002.7 | 978.1 | 977.3 |
| 25° | 2942.7 | 2475.2 | 1380.2 | 838.1 | 848.9 | 891.2 | 923.5 | 903.5 | 878.9 | 865.1 | 862.7 |
| 27.5° | 2913.5 | 2358.3 | 1131.9 | 754.3 | 789.7 | 837.4 | 827.4 | 810.5 | 804.3 | 788.9 | 787.4 |
| 30° | 2876.6 | 2214.5 | 908.9 | 689.0 | 728.2 | 772.0 | 756.6 | 755.1 | 748.9 | 732.0 | 732.0 |
| 32.5° | 2841.2 | 2066.1 | 740.5 | 640.5 | 689.0 | 692.0 | 713.6 | 715.1 | 712.0 | 682.8 | 679.7 |
| 35° | 2831.2 | 1917.7 | 626.7 | 602.1 | 650.5 | 649.0 | 679.7 | 679.0 | 625.9 | 585.2 | 584.4 |
| 37.5° | 2861.2 | 1767.0 | 559.0 | 570.6 | 597.5 | 617.5 | 642.1 | 597.5 | 579.8 | 555.2 | 553.6 |
| 40° | 2925.0 | 1627.8 | 524.4 | 552.1 | 563.6 | 592.8 | 554.4 | 557.5 | 552.9 | 534.4 | 532.1 |
| 42.5° | 3009.6 | 1509.4 | 505.2 | 545.9 | 544.4 | 552.1 | 509.8 | 522.1 | 529.0 | 515.2 | 512.9 |
| 45° | 3091.1 | 1406.4 | 495.2 | 522.9 | 530.6 | 486.0 | 477.5 | 489.0 | 499.8 | 494.4 | 492.1 |
| 47.5° | 3151.1 | 1317.2 | 489.8 | 491.4 | 512.9 | 463.7 | 449.8 | 455.2 | 468.3 | 470.6 | 469.8 |
| 50° | 3169.6 | 1241.1 | 483.7 | 465.2 | 460.6 | 441.4 | 430.6 | 429.1 | 444.4 | 455.2 | 456.7 |
| 52.5° | 3134.2 | 1173.4 | 467.5 | 442.1 | 419.8 | 422.9 | 419.1 | 411.4 | 426.8 | 441.4 | 442.9 |
| 55° | 3081.9 | 1134.9 | 442.1 | 419.8 | 393.7 | 406.0 | 407.5 | 400.6 | 410.6 | 420.6 | 420.6 |
| 57.5° | 3085.7 | 1157.2 | 417.5 | 399.1 | 370.6 | 386.8 | 395.2 | 392.2 | 392.2 | 399.8 | 400.6 |
| 60° | 3111.1 | 1189.5 | 401.4 | 372.9 | 347.6 | 364.5 | 383.7 | 380.6 | 373.7 | 383.7 | 383.7 |
| 62.5° | 3038.1 | 1146.5 | 390.6 | 347.6 | 323.0 | 342.9 | 366.0 | 364.5 | 356.8 | 372.9 | 374.5 |
| 65° | 2822.8 | 1031.1 | 378.3 | 316.0 | 298.3 | 321.4 | 341.4 | 346.8 | 339.9 | 361.4 | 365.2 |
| 67.5° | 2366.0 | 867.4 | 354.5 | 286.0 | 273.7 | 295.3 | 314.5 | 322.2 | 316.8 | 342.2 | 345.3 |
| 70° | 1763.9 | 702.0 | 316.8 | 253.0 | 243.8 | 263.0 | 280.7 | 283.7 | 284.5 | 314.5 | 317.6 |
| 72.5° | 1125.0 | 545.9 | 266.8 | 216.1 | 209.2 | 223.8 | 236.8 | 249.1 | 254.5 | 283.0 | 282.2 |
| 75° | 627.5 | 406.0 | 214.5 | 183.0 | 170.7 | 182.2 | 197.6 | 212.2 | 227.6 | 269.1 | 273.7 |
| 77.5° | 361.4 | 285.3 | 169.9 | 146.9 | 132.3 | 144.6 | 157.6 | 178.4 | 224.5 | 260.7 | 256.1 |
| 80° | 203.8 | 185.3 | 128.4 | 107.7 | 98.4 | 107.7 | 117.6 | 156.9 | 176.9 | 192.2 | 194.5 |
| 82.5° | 95.3 | 103.8 | 87.7 | 66.1 | 66.1 | 72.3 | 81.5 | 121.5 | 133.8 | 109.2 | 95.3 |
| 85° | 34.6 | 46.9 | 43.1 | 33.8 | 30.0 | 29.2 | 50.7 | 69.2 | 43.1 | 38.4 | 33.1 |
| 87.5° | 9.2 | 13.1 | 12.3 | 8.5 | 4.6 | 3.8 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions


Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength




Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 CIE $R_a = 80.9$
 $R_9 = -1.5$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)