

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930641

Luminaire Tested: DFN2DS-PN4F0-040DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-PN4F0-040DS927-FLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3136.3 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.94' x L: 3.74' x H: 0')
CIE Type: Direct

Input Watts (W): 38.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930641

CATALOG NUMBER: DFN2DS-PN4F0-040DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930641

CATALOG NUMBER: DFN2DS-PN4F0-040DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	900	900	900
5°	903	890	895
10°	898	881	886
15°	887	870	869
20°	871	853	852
25°	855	832	832
30°	835	812	805
35°	817	789	777
40°	793	766	751
45°	770	743	724
50°	744	719	693
55°	718	691	665
60°	689	658	633
65°	657	624	596
70°	617	584	557
75°	562	538	525
80°	499	483	459
85°	406	388	348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 770 cd/sqm

TEST NUMBER: P930641

CATALOG NUMBER: DFN2DS-PN4F0-040DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.0	3.7
10°-20°	326.4	10.4
20°-30°	479.7	15.3
30°-40°	557.2	17.8
40°-50°	556.5	17.7
50°-60°	485.2	15.5
60°-70°	358.7	11.4
70°-80°	202.9	6.5
80°-90°	53.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	922.2	29.4
0°-40°	1479.4	47.2
0°-60°	2521.1	80.4
0°-90°	3136.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3136.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1224	1222	117
15°	1173	1166	1151	1156	1150	330
25°	1062	1053	1032	1035	1032	489
35°	916	904	886	878	872	572
45°	746	737	720	706	702	575
55°	564	557	543	529	523	504
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	48	47	46	43	42	57
90°	0	0	0	0	0	

TEST NUMBER: P930641

CATALOG NUMBER: DFN2DS-PN4F0-040DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1232.7	1232.7	1232.7	1232.7	1232.7
2.5°	1239.9	1233.9	1220.9	1232.7	1230.5
5°	1232.7	1228.0	1214.9	1224.4	1222.1
7.5°	1224.4	1217.3	1204.2	1213.8	1211.4
10°	1211.4	1203.1	1189.0	1198.4	1194.8
12.5°	1193.5	1186.5	1172.3	1178.3	1175.8
15°	1173.4	1166.4	1150.9	1155.7	1149.8
17.5°	1148.6	1141.5	1126.1	1131.9	1126.1
20°	1121.2	1114.2	1097.6	1101.1	1096.5
22.5°	1094.1	1083.4	1067.9	1067.9	1065.6
25°	1062.0	1052.6	1032.5	1034.7	1032.5
27.5°	1026.4	1018.1	1002.8	999.3	993.4
30°	991.0	981.4	963.7	960.1	955.4
32.5°	953.0	946.0	927.0	919.8	915.0
35°	916.3	904.5	885.5	878.3	872.4
37.5°	874.8	864.1	845.1	836.8	830.9
40°	832.2	822.6	803.6	793.0	788.3
42.5°	790.7	781.1	762.2	750.3	743.2
45°	745.6	737.4	719.5	706.5	701.7
47.5°	701.7	693.4	674.5	661.4	654.4
50°	655.5	649.5	633.0	616.3	610.4
52.5°	610.4	602.2	586.8	573.7	565.4
55°	564.3	557.1	542.9	528.7	522.8
57.5°	518.0	512.1	496.6	482.4	477.7
60°	471.7	467.0	450.5	437.4	433.9
62.5°	426.7	418.4	406.6	394.7	390.0
65°	380.6	373.3	361.5	350.9	345.0
67.5°	333.1	327.1	316.6	308.2	303.5
70°	289.2	284.5	273.8	265.5	260.8
72.5°	244.3	239.4	233.6	225.2	221.7
75°	199.1	196.8	190.8	183.7	186.1
77.5°	158.8	154.0	151.7	148.1	144.6
80°	118.6	117.3	114.9	111.4	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.5	47.4	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930641

CATALOG NUMBER: DFN2DS-PN4F0-040DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.92	12.53	11.28	12.84	13.15	10.47	12.08	10.84	12.40	12.71
	3H	12.67	14.12	13.04	14.45	14.81	12.17	13.63	12.55	13.96	14.32
	4H	13.31	14.68	13.71	15.03	15.41	12.82	14.19	13.22	14.53	14.91
	6H	13.78	15.05	14.19	15.41	15.81	13.28	14.55	13.69	14.91	15.30
	8H	13.92	15.14	14.35	15.52	15.92	13.42	14.63	13.85	15.02	15.42
	12H	14.01	15.17	14.44	15.56	15.98	13.50	14.66	13.93	15.04	15.47
4H	2H	11.48	12.85	11.87	13.19	13.57	11.12	12.49	11.52	12.84	13.22
	3H	13.45	14.60	13.86	15.00	15.40	13.04	14.19	13.45	14.59	14.99
	4H	14.23	15.26	14.66	15.68	16.11	13.80	14.84	14.24	15.25	15.69
	6H	14.82	15.73	15.28	16.17	16.63	14.39	15.30	14.85	15.74	16.19
	8H	15.01	15.86	15.47	16.30	16.77	14.58	15.42	15.04	15.86	16.33
	12H	15.15	15.91	15.63	16.38	16.85	14.69	15.45	15.17	15.93	16.40
8H	4H	14.50	15.35	14.96	15.79	16.26	14.13	14.97	14.59	15.42	15.88
	6H	15.22	15.92	15.71	16.41	16.88	14.83	15.54	15.33	16.03	16.50
	8H	15.47	16.11	15.98	16.61	17.10	15.08	15.71	15.59	16.22	16.71
	12H	15.67	16.23	16.18	16.72	17.28	15.26	15.82	15.77	16.31	16.87
12H	4H	14.53	15.29	15.01	15.76	16.23	14.16	14.92	14.64	15.40	15.87
	6H	15.26	15.89	15.77	16.40	16.89	14.89	15.52	15.40	16.03	16.52
	8H	15.57	16.13	16.08	16.62	17.18	15.20	15.75	15.70	16.24	16.81

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7