

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: McGRAW-EDISON

Report Number: P641422

Luminaire Tested: GWS-SA5F-827-U-T4W-W

Issue Date: 1/10/2023

Test Information

Test Method: LM-79-2019
Report Number: P641422
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2209-782-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/10/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: McGRAW-EDISON
Catalog Number: GWS-SA5F-827-U-T4W-W
Description: GALLEON WALL SLIM LUMINAIRE. (5) LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV WIDE OPTICS
Light Source: (80) 2700K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 30419.7 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B3 - U0 - G4


Input Watts (W): 310.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 0
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P641422
 CATALOG NUMBER: GWS-SA5F-827-U-T4W-W

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 4.2 fc
 Type III - Short - N/A

REPORT NUMBER: P641422
CATALOG NUMBER: GWS-SA5F-827-U-T4W-W

Luminous Intensity Polar Plot



— Vertical Plane Through 47-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P641422

CATALOG NUMBER: GWS-SA5F-827-U-T4W-W


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 6932.9 | 0.0 | 6932.9 |
| | % Fixture | 22.8 | 0.0 | 22.8 |
| Street Side | Lumens | 23486.8 | 0.0 | 23486.8 |
| | % Fixture | 77.2 | 0.0 | 77.2 |
| Total | Lumens | 30419.7 | 0.0 | 30419.7 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 308.2 | 1.0 |
| 10°-20° | 1026.8 | 3.4 |
| 20°-30° | 1745.3 | 5.7 |
| 30°-40° | 2556.6 | 8.4 |
| 40°-50° | 3895.3 | 12.8 |
| 50°-60° | 6969.6 | 22.9 |
| 60°-70° | 9300.1 | 30.6 |
| 70°-80° | 4205.7 | 13.8 |
| 80°-90° | 412.1 | 1.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 30419.7 | 100.0 |
| 0°-180° | 30419.7 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P641422


CATALOG NUMBER: GWS-SA5F-827-U-T4W-W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 1659.0 | 5.5 | | | |
| FM (30°-60°) | 10099.6 | 33.2 | | | |
| FH (60°-80°) | 11483.1 | 37.7 | | | G4/12000 |
| FVH (80°-90°) | 245.1 | 0.8 | | | G3/500 |
| BL (0°-30°) | 1421.3 | 4.7 | B3/2500 | | |
| BM (30°-60°) | 3321.9 | 10.9 | B3/5000 | | |
| BH (60°-80°) | 2022.8 | 6.6 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 167.0 | 0.5 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G4

Type III Short





REPORT NUMBER: P641422

CATALOG NUMBER: GWS-SA5F-827-U-T4W-W

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 47° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 3015.6 | 3015.6 | 3015.6 | 3015.6 | 3015.6 | 3015.6 | 3015.6 | 3015.6 | 3015.6 | 3015.6 | 3015.6 |
| 2.5° | 3215.7 | 3226.7 | 3224.5 | 3206.9 | 3195.9 | 3176.1 | 3178.3 | 3147.5 | 3101.3 | 3070.5 | 3035.4 |
| 5° | 3499.5 | 3517.0 | 3495.1 | 3466.5 | 3422.5 | 3358.7 | 3352.1 | 3281.7 | 3193.7 | 3132.1 | 3068.3 |
| 7.5° | 3745.8 | 3756.8 | 3730.4 | 3682.0 | 3618.2 | 3532.4 | 3517.0 | 3433.5 | 3323.5 | 3226.7 | 3134.3 |
| 10° | 3937.2 | 3950.4 | 3915.2 | 3851.4 | 3767.8 | 3682.0 | 3671.0 | 3585.2 | 3468.7 | 3354.3 | 3237.7 |
| 12.5° | 4099.9 | 4104.3 | 4066.9 | 3981.1 | 3891.0 | 3803.0 | 3792.0 | 3712.8 | 3605.0 | 3488.5 | 3360.9 |
| 15° | 4194.5 | 4196.7 | 4150.5 | 4055.9 | 3970.2 | 3893.2 | 3886.6 | 3818.4 | 3719.4 | 3609.4 | 3473.1 |
| 17.5° | 4187.9 | 4192.3 | 4159.3 | 4075.7 | 4000.9 | 3954.8 | 3948.2 | 3904.2 | 3827.2 | 3728.2 | 3591.8 |
| 20° | 4106.5 | 4110.9 | 4088.9 | 4033.9 | 3994.3 | 3981.1 | 3983.3 | 3970.2 | 3924.0 | 3842.6 | 3704.0 |
| 22.5° | 4042.7 | 4049.3 | 4029.5 | 3989.9 | 3985.5 | 4016.3 | 4022.9 | 4029.5 | 4007.5 | 3935.0 | 3800.8 |
| 25° | 4073.5 | 4084.5 | 4053.7 | 3998.7 | 4007.5 | 4075.7 | 4088.9 | 4110.9 | 4093.3 | 4031.7 | 3915.2 |
| 27.5° | 4286.9 | 4293.5 | 4214.3 | 4102.1 | 4075.7 | 4148.3 | 4168.1 | 4203.3 | 4190.1 | 4132.9 | 4042.7 |
| 30° | 4781.8 | 4777.4 | 4608.0 | 4333.1 | 4223.1 | 4251.7 | 4267.1 | 4317.7 | 4322.1 | 4284.7 | 4198.9 |
| 32.5° | 5479.0 | 5457.0 | 5195.3 | 4757.6 | 4438.7 | 4368.3 | 4385.9 | 4454.0 | 4504.6 | 4465.0 | 4348.5 |
| 35° | 6215.9 | 6196.1 | 5907.9 | 5395.4 | 4836.8 | 4592.6 | 4572.8 | 4625.6 | 4702.6 | 4592.6 | 4425.5 |
| 37.5° | 6917.5 | 6886.7 | 6592.0 | 5958.5 | 5327.3 | 4986.3 | 4957.7 | 4905.0 | 4858.8 | 4647.6 | 4520.0 |
| 40° | 7696.2 | 7661.0 | 7403.6 | 6686.6 | 5868.3 | 5287.7 | 5215.1 | 5006.1 | 4964.3 | 4830.2 | 4766.4 |
| 42.5° | 8527.6 | 8527.6 | 8314.2 | 7608.2 | 6521.6 | 5718.8 | 5624.2 | 5309.7 | 5353.7 | 5265.7 | 5190.9 |
| 45° | 9359.0 | 9383.2 | 9213.8 | 8536.4 | 7394.8 | 6532.6 | 6380.8 | 5934.3 | 6039.9 | 6000.3 | 5962.9 |
| 47.5° | 10067.2 | 10113.4 | 10080.4 | 9484.4 | 8463.8 | 7522.4 | 7291.4 | 6827.3 | 7053.9 | 7148.5 | 7254.0 |
| 50° | 10830.5 | 10881.1 | 10848.1 | 10612.7 | 9715.3 | 8721.1 | 8514.4 | 8034.9 | 8424.2 | 8707.9 | 9053.3 |
| 52.5° | 11963.2 | 12035.8 | 11760.9 | 11670.7 | 11235.2 | 10082.6 | 9897.9 | 9352.4 | 10058.4 | 10529.1 | 11299.0 |
| 55° | 12920.0 | 12917.8 | 12821.1 | 13027.8 | 12867.2 | 11747.7 | 11543.1 | 11048.2 | 11950.0 | 12449.3 | 13575.5 |
| 57.5° | 13364.3 | 13417.1 | 13749.3 | 14334.3 | 14655.5 | 13782.3 | 13586.5 | 13080.6 | 13980.2 | 14239.8 | 15456.1 |
| 60° | 13593.1 | 13659.1 | 14301.3 | 15458.3 | 16322.7 | 16003.8 | 15926.8 | 15282.3 | 15788.2 | 15757.4 | 17042.0 |
| 62.5° | 13272.0 | 13403.9 | 14435.5 | 15973.0 | 17512.7 | 18236.3 | 18212.1 | 17237.7 | 17325.7 | 17024.4 | 18025.1 |
| 65° | 11798.3 | 11941.2 | 13560.1 | 15715.6 | 18192.3 | 19934.3 | 19940.9 | 19008.3 | 18506.8 | 17640.2 | 17860.2 |
| 67.5° | 8437.4 | 8642.0 | 10643.5 | 14061.6 | 17952.6 | 20851.5 | 20928.5 | 19811.2 | 18784.0 | 17094.7 | 16127.0 |
| 70° | 4599.2 | 4748.8 | 6317.0 | 10221.2 | 15792.6 | 20631.6 | 20774.6 | 19424.0 | 17561.0 | 14787.4 | 12414.1 |
| 72.5° | 2089.6 | 2137.9 | 2938.6 | 5608.8 | 10788.7 | 17759.0 | 18357.3 | 17334.5 | 14422.3 | 10922.9 | 7894.1 |
| 75° | 956.8 | 978.8 | 1280.1 | 2683.4 | 5637.4 | 11884.1 | 12304.2 | 12911.2 | 10036.5 | 6897.7 | 4115.3 |
| 77.5° | 600.5 | 607.1 | 728.0 | 1227.3 | 2811.0 | 5932.1 | 6374.2 | 7687.4 | 5877.1 | 3413.7 | 1720.0 |
| 80° | 354.1 | 360.7 | 453.1 | 664.3 | 1319.7 | 2714.2 | 3134.3 | 3039.7 | 2762.6 | 1473.7 | 783.0 |
| 82.5° | 178.2 | 184.8 | 261.7 | 378.3 | 719.2 | 1080.0 | 1271.3 | 1277.9 | 1029.4 | 798.4 | 442.1 |
| 85° | 63.8 | 66.0 | 85.8 | 149.6 | 305.7 | 356.3 | 398.1 | 486.1 | 503.7 | 464.1 | 213.4 |
| 87.5° | 0.0 | 0.0 | 2.2 | 4.4 | 8.8 | 35.2 | 37.4 | 70.4 | 147.4 | 165.0 | 85.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P641422
 CATALOG NUMBER: GWS-SA5F-827-U-T4W-W

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3015.6 | 3015.6 | 3015.6 | 3015.6 | 3015.6 | 3015.6 | 3015.6 | 3015.6 | 3015.6 | 3015.6 | 3015.6 |
| 2.5° | 3024.4 | 2991.4 | 2980.4 | 2969.4 | 2951.8 | 2945.2 | 2932.0 | 2918.8 | 2918.8 | 2905.6 | 2899.0 |
| 5° | 3039.7 | 2995.8 | 2967.2 | 2954.0 | 2943.0 | 2949.6 | 2949.6 | 2954.0 | 2969.4 | 2960.6 | 2965.0 |
| 7.5° | 3094.7 | 3044.1 | 3004.6 | 2993.6 | 2993.6 | 3020.0 | 3037.6 | 3059.5 | 3088.1 | 3092.5 | 3092.5 |
| 10° | 3191.5 | 3132.1 | 3090.3 | 3083.7 | 3094.7 | 3132.1 | 3158.5 | 3184.9 | 3220.1 | 3222.3 | 3226.7 |
| 12.5° | 3297.1 | 3237.7 | 3195.9 | 3204.7 | 3215.7 | 3264.1 | 3292.7 | 3314.7 | 3349.9 | 3349.9 | 3347.7 |
| 15° | 3407.1 | 3341.1 | 3305.9 | 3323.5 | 3356.5 | 3411.5 | 3415.9 | 3418.1 | 3435.7 | 3431.3 | 3429.1 |
| 17.5° | 3521.4 | 3451.1 | 3424.7 | 3451.1 | 3486.3 | 3512.6 | 3490.7 | 3459.9 | 3453.3 | 3444.5 | 3440.1 |
| 20° | 3633.6 | 3561.0 | 3550.0 | 3569.8 | 3580.8 | 3558.8 | 3490.7 | 3433.5 | 3407.1 | 3393.9 | 3389.5 |
| 22.5° | 3730.4 | 3668.8 | 3662.2 | 3662.2 | 3607.2 | 3530.2 | 3429.1 | 3352.1 | 3316.9 | 3299.3 | 3294.9 |
| 25° | 3844.8 | 3787.6 | 3776.6 | 3717.2 | 3576.4 | 3435.7 | 3299.3 | 3228.9 | 3200.3 | 3191.5 | 3193.7 |
| 27.5° | 3978.9 | 3939.4 | 3904.2 | 3734.8 | 3488.5 | 3268.5 | 3114.5 | 3083.7 | 3072.7 | 3083.7 | 3090.3 |
| 30° | 4143.9 | 4104.3 | 4025.1 | 3712.8 | 3347.7 | 3050.7 | 2903.4 | 2901.2 | 2934.2 | 2962.8 | 2967.2 |
| 32.5° | 4278.1 | 4260.5 | 4130.7 | 3642.4 | 3149.7 | 2811.0 | 2685.6 | 2694.4 | 2753.8 | 2793.4 | 2800.0 |
| 35° | 4383.7 | 4412.3 | 4218.7 | 3525.8 | 2914.4 | 2584.4 | 2485.5 | 2489.9 | 2522.9 | 2577.8 | 2580.0 |
| 37.5° | 4533.2 | 4630.0 | 4297.9 | 3347.7 | 2643.8 | 2388.7 | 2298.5 | 2265.5 | 2261.1 | 2276.5 | 2280.9 |
| 40° | 4834.6 | 4979.7 | 4355.1 | 3088.1 | 2382.1 | 2212.7 | 2111.5 | 2047.8 | 1992.8 | 1951.0 | 1937.8 |
| 42.5° | 5289.9 | 5457.0 | 4388.1 | 2773.6 | 2148.9 | 2039.0 | 1924.6 | 1843.2 | 1746.4 | 1658.4 | 1627.7 |
| 45° | 6125.7 | 6180.7 | 4388.1 | 2439.3 | 1942.2 | 1876.2 | 1761.8 | 1665.0 | 1541.9 | 1438.5 | 1416.5 |
| 47.5° | 7463.0 | 7287.0 | 4392.5 | 2115.9 | 1759.6 | 1733.2 | 1634.3 | 1524.3 | 1387.9 | 1302.1 | 1288.9 |
| 50° | 9477.8 | 8859.7 | 4482.6 | 1847.6 | 1607.9 | 1612.3 | 1539.7 | 1418.7 | 1295.5 | 1231.7 | 1220.7 |
| 52.5° | 11760.9 | 10797.5 | 4724.6 | 1649.6 | 1480.3 | 1513.3 | 1473.7 | 1357.1 | 1247.1 | 1192.1 | 1181.1 |
| 55° | 13907.6 | 12579.1 | 4931.3 | 1508.9 | 1372.5 | 1429.7 | 1427.5 | 1319.7 | 1220.7 | 1165.8 | 1159.2 |
| 57.5° | 15733.2 | 13799.8 | 4900.6 | 1394.5 | 1280.1 | 1352.7 | 1385.7 | 1295.5 | 1203.1 | 1157.0 | 1150.4 |
| 60° | 16868.2 | 14446.5 | 4462.8 | 1288.9 | 1209.7 | 1297.7 | 1361.5 | 1288.9 | 1211.9 | 1200.9 | 1203.1 |
| 62.5° | 17360.9 | 14327.7 | 3622.6 | 1209.7 | 1163.6 | 1271.3 | 1387.9 | 1335.1 | 1293.3 | 1319.7 | 1335.1 |
| 65° | 16595.5 | 13307.2 | 2665.8 | 1150.4 | 1119.6 | 1277.9 | 1449.5 | 1407.7 | 1293.3 | 1310.9 | 1317.5 |
| 67.5° | 14470.7 | 11327.6 | 1926.8 | 1091.0 | 1064.6 | 1297.7 | 1537.5 | 1396.7 | 1218.5 | 1218.5 | 1205.3 |
| 70° | 10428.0 | 8147.1 | 1398.9 | 1031.6 | 1009.6 | 1269.1 | 1541.9 | 1321.9 | 1132.8 | 1126.2 | 1093.2 |
| 72.5° | 6275.3 | 4806.0 | 1091.0 | 965.6 | 926.0 | 1126.2 | 1445.1 | 1233.9 | 1049.2 | 994.2 | 954.6 |
| 75° | 3259.7 | 2408.5 | 915.0 | 893.0 | 794.0 | 954.6 | 1321.9 | 1097.6 | 897.4 | 849.0 | 827.0 |
| 77.5° | 1396.7 | 1126.2 | 785.2 | 796.2 | 659.9 | 802.8 | 1066.8 | 950.2 | 796.2 | 734.6 | 714.8 |
| 80° | 688.5 | 640.1 | 620.3 | 637.9 | 527.9 | 620.3 | 919.4 | 831.4 | 675.3 | 604.9 | 576.3 |
| 82.5° | 393.7 | 373.9 | 446.5 | 453.1 | 376.1 | 519.1 | 776.4 | 703.8 | 558.7 | 481.7 | 435.5 |
| 85° | 182.6 | 195.8 | 270.5 | 272.7 | 233.2 | 356.3 | 508.1 | 395.9 | 296.9 | 246.3 | 235.3 |
| 87.5° | 72.6 | 85.8 | 118.8 | 116.6 | 68.2 | 66.0 | 44.0 | 24.2 | 19.8 | 17.6 | 15.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2407-157-9

Test Date: 10/03/2024

Luminaire Tested: EMM2-HTN-SA1A-827-U-5WQ

Data applicable to all product families utilizing light square engine

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/03/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Invue
 Catalog Number: **EMM2-HTN-SA1A-827-U-5WQ**
 Description: Epic Modern Light Square 40W 5WQ Optic

Spectral Parameters

CCT (K): 2764
 CIE u': 0.2591
 CIE v': 0.5290
 Duv: 0.0020
 CIE x: 0.4581
 CIE y: 0.4156
 CIE z: 0.1263
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 583
 Purity: 62.2537
 Rf: 84.7
 Rg: 94.6

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 80.9 | | |
| R1: | 78.8 | R9: | -1.5 |
| R2: | 89.9 | R10: | 77.9 |
| R3: | 96.2 | R11: | 78.9 |
| R4: | 79.1 | R12: | 71.6 |
| R5: | 79.1 | R13: | 81.2 |
| R6: | 88.8 | R14: | 98.5 |
| R7: | 81.3 | R15: | 69.9 |
| R8: | 54.3 | | |



Test Conditions

Stabilization Time: 81M
 Operation Time: 2H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-157-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-9

Photopic Flux vs. Wavelength



Photopic Lumens: 4337.9

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 0 | 0.0 | 490 | 18018 | 2.6 | 620 | 87426 | 22.8 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 3.9 | 625 | 83013 | 18.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 5.8 | 630 | 78077 | 14.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 8.5 | 635 | 72080 | 10.7 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 11.5 | 640 | 66249 | 7.9 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 15.2 | 645 | 59973 | 5.7 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 18.7 | 650 | 53972 | 3.9 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 21.9 | 655 | 48369 | 2.7 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 24.9 | 660 | 42641 | 1.8 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 27.6 | 665 | 37602 | 1.1 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 30.0 | 670 | 32798 | 0.7 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.0 | 545 | 48553 | 32.5 | 675 | 28558 | 0.5 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.0 | 550 | 51408 | 34.9 | 680 | 24782 | 0.3 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.0 | 555 | 54711 | 37.4 | 685 | 21386 | 0.2 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 0.0 | 560 | 58847 | 40.0 | 690 | 18413 | 0.1 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 0.1 | 565 | 63386 | 42.4 | 695 | 15721 | 0.1 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 0.2 | 570 | 68196 | 44.3 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 0.6 | 575 | 73613 | 46.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 0.9 | 580 | 79207 | 47.1 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 0.9 | 585 | 84248 | 47.0 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 0.9 | 590 | 88397 | 45.7 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 1.0 | 595 | 91428 | 43.4 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 0.9 | 600 | 93452 | 40.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 1.0 | 605 | 93959 | 36.4 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 1.3 | 610 | 93079 | 32.0 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 1.8 | 615 | 90707 | 27.3 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 5286.7

S/P: 1.22

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 75.9 | 620 | 87426 | 0.4 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 93.2 | 625 | 83013 | 0.2 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 107.8 | 630 | 78077 | 0.1 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 118.7 | 635 | 72080 | 0.1 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 122.2 | 640 | 66249 | 0.1 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 120.8 | 645 | 59973 | 0.0 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 113.9 | 650 | 53972 | 0.0 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 104.1 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 92.4 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 80.5 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.1 | 540 | 46032 | 68.2 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.3 | 545 | 48553 | 57.1 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 1.1 | 550 | 51408 | 46.7 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 2.5 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 5.9 | 560 | 58847 | 29.4 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 12.5 | 565 | 63386 | 22.5 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 26.3 | 570 | 68196 | 16.9 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 55.2 | 575 | 73613 | 12.4 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 85.4 | 580 | 79207 | 9.0 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 75.1 | 585 | 84248 | 6.3 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 63.2 | 590 | 88397 | 4.4 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 63.2 | 595 | 91428 | 3.0 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 54.2 | 600 | 93452 | 2.0 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 48.8 | 605 | 93959 | 1.3 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 54.2 | 610 | 93079 | 0.9 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 63.3 | 615 | 90707 | 0.5 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

REPORT NUMBER: SP1-2407-157-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 9797

M/P: 2.26

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 0 | 0.0 | 490 | 18018 | 27.7 | 620 | 87426 | 1.1 | 750 | 2680 | 0.0 | 880 | 58 | 0.0 |
| 365 | 0 | 0.0 | 495 | 22295 | 36.0 | 625 | 83013 | 0.7 | 755 | 2287 | 0.0 | 885 | 46 | 0.0 |
| 370 | 0 | 0.0 | 500 | 26478 | 44.2 | 630 | 78077 | 0.4 | 760 | 1944 | 0.0 | 890 | 45 | 0.0 |
| 375 | 0 | 0.0 | 505 | 30524 | 51.8 | 635 | 72080 | 0.3 | 765 | 1653 | 0.0 | 895 | 41 | 0.0 |
| 380 | 0 | 0.0 | 510 | 33611 | 57.0 | 640 | 66249 | 0.2 | 770 | 1413 | 0.0 | 900 | 38 | 0.0 |
| 385 | 0 | 0.0 | 515 | 36490 | 60.5 | 645 | 59973 | 0.1 | 775 | 1198 | 0.0 | 905 | 33 | 0.0 |
| 390 | 0 | 0.0 | 520 | 38610 | 61.4 | 650 | 53972 | 0.1 | 780 | 1025 | 0.0 | 910 | 30 | 0.0 |
| 395 | 0 | 0.0 | 525 | 40511 | 60.6 | 655 | 48369 | 0.0 | 785 | 874 | 0.0 | 915 | 23 | 0.0 |
| 400 | 48 | 0.0 | 530 | 42223 | 58.2 | 660 | 42641 | 0.0 | 790 | 747 | 0.0 | 920 | 24 | 0.0 |
| 405 | 201 | 0.0 | 535 | 44137 | 55.0 | 665 | 37602 | 0.0 | 795 | 639 | 0.0 | 925 | 22 | 0.0 |
| 410 | 457 | 0.0 | 540 | 46032 | 50.9 | 670 | 32798 | 0.0 | 800 | 547 | 0.0 | 930 | 22 | 0.0 |
| 415 | 925 | 0.1 | 545 | 48553 | 46.6 | 675 | 28558 | 0.0 | 805 | 473 | 0.0 | 935 | 17 | 0.0 |
| 420 | 1816 | 0.3 | 550 | 51408 | 42.0 | 680 | 24782 | 0.0 | 810 | 401 | 0.0 | 940 | 13 | 0.0 |
| 425 | 3217 | 0.8 | 555 | 54711 | 37.4 | 685 | 21386 | 0.0 | 815 | 351 | 0.0 | 945 | 6 | 0.0 |
| 430 | 5520 | 1.9 | 560 | 58847 | 32.9 | 690 | 18413 | 0.0 | 820 | 307 | 0.0 | 950 | 10 | 0.0 |
| 435 | 9225 | 4.1 | 565 | 63386 | 28.4 | 695 | 15721 | 0.0 | 825 | 261 | 0.0 | 955 | 11 | 0.0 |
| 440 | 15522 | 8.7 | 570 | 68196 | 24.1 | 700 | 13432 | 0.0 | 830 | 228 | 0.0 | 960 | 8 | 0.0 |
| 445 | 27642 | 18.5 | 575 | 73613 | 20.0 | 705 | 11513 | 0.0 | 835 | 193 | 0.0 | 965 | 12 | 0.0 |
| 450 | 36602 | 28.3 | 580 | 79207 | 16.3 | 710 | 9780 | 0.0 | 840 | 174 | 0.0 | 970 | 3 | 0.0 |
| 455 | 28292 | 24.7 | 585 | 84248 | 12.9 | 715 | 8356 | 0.0 | 845 | 151 | 0.0 | 975 | 8 | 0.0 |
| 460 | 21166 | 20.4 | 590 | 88397 | 9.8 | 720 | 7161 | 0.0 | 850 | 123 | 0.0 | 980 | 2 | 0.0 |
| 465 | 19092 | 20.1 | 595 | 91428 | 7.3 | 725 | 6067 | 0.0 | 855 | 106 | 0.0 | 985 | 13 | 0.0 |
| 470 | 14951 | 17.2 | 600 | 93452 | 5.3 | 730 | 5164 | 0.0 | 860 | 95 | 0.0 | 990 | 16 | 0.0 |
| 475 | 12606 | 15.7 | 605 | 93959 | 3.7 | 735 | 4393 | 0.0 | 865 | 82 | 0.0 | 995 | 20 | 0.0 |
| 480 | 13323 | 18.0 | 610 | 93079 | 2.5 | 740 | 3694 | 0.0 | 870 | 77 | 0.0 | 1000 | 0 | 0.0 |
| 485 | 15164 | 21.9 | 615 | 90707 | 1.7 | 745 | 3157 | 0.0 | 875 | 65 | 0.0 | | | |

Summary

$R_f = 84.7$
 $R_g = 94.6$
 $CIE R_a = 80.9$
 $R_g = -1.5$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 84 | CES51 = 95 | CES76 = 81 |
| CES02 = 63 | CES27 = 95 | CES52 = 94 | CES77 = 84 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 81 |
| CES04 = 71 | CES29 = 87 | CES54 = 91 | CES79 = 89 |
| CES05 = 50 | CES30 = 94 | CES55 = 90 | CES80 = 89 |
| CES06 = 52 | CES31 = 89 | CES56 = 86 | CES81 = 69 |
| CES07 = 43 | CES32 = 82 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 91 | CES58 = 86 | CES83 = 93 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 77 | CES35 = 96 | CES60 = 94 | CES85 = 76 |
| CES11 = 60 | CES36 = 90 | CES61 = 89 | CES86 = 65 |
| CES12 = 66 | CES37 = 96 | CES62 = 94 | CES87 = 84 |
| CES13 = 44 | CES38 = 98 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 98 | CES64 = 82 | CES89 = 73 |
| CES15 = 72 | CES40 = 95 | CES65 = 78 | CES90 = 88 |
| CES16 = 48 | CES41 = 96 | CES66 = 81 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 80 | CES92 = 64 |
| CES18 = 57 | CES43 = 91 | CES68 = 83 | CES93 = 78 |
| CES19 = 73 | CES44 = 99 | CES69 = 88 | CES94 = 59 |
| CES20 = 67 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 89 | CES71 = 79 | CES96 = 83 |
| CES22 = 79 | CES47 = 92 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 83 | CES73 = 75 | CES98 = 83 |
| CES24 = 91 | CES49 = 90 | CES74 = 91 | CES99 = 74 |
| CES25 = 72 | CES50 = 94 | CES75 = 81 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)