

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P242267

Luminaire Tested: **S122DR-S865D840-X4F0-XX-UDD-F-W**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P242267
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DR-S865D840-X4F0-XX-UDD-F-W
Description: DEFINE 2 DIRECT RECESSED WITH SATIN FLUSH DIFFUSER
STANDARD LIGHT ENGINE
Light Source: (92) 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3407.5 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 0.15' x L: 3.88' x H: 0')
CIE Type: Direct


Input Watts (W): 34.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P242267

CATALOG NUMBER: S122DR-S865D840-X4F0-XX-UDD-F-W

Luminous Intensity Polar Plot





TEST NUMBER: P242267

CATALOG NUMBER: S122DR-S865D840-X4F0-XX-UDD-F-W

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76	83	78	74	80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48	59	52	47	57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42	53	47	42	52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37	49	42	37	47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33	45	38	33	44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27	38	32	27	37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25511	25511	25511
5°	25608	25239	25388
10°	25457	24983	25107
15°	25143	24659	24634
20°	24695	24172	24146
25°	24251	23575	23575
30°	23679	23028	22830
35°	23148	22369	22039
40°	22480	21710	21294
45°	21819	21057	20537
50°	21105	20379	19653
55°	20357	19586	18859
60°	19528	18644	17954
65°	18632	17704	16893
70°	17498	16568	15777
75°	15926	15256	14881
80°	14128	13700	12998
85°	11539	10971	9857



TEST NUMBER: P242267

CATALOG NUMBER: S122DR-S865D840-X4F0-XX-UDD-F-W

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	3.7
10°-20°	354.7	10.4
20°-30°	521.2	15.3
30°-40°	605.4	17.8
40°-50°	604.6	17.7
50°-60°	527.2	15.5
60°-70°	389.7	11.4
70°-80°	220.5	6.5
80°-90°	58.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1001.9	29.4
0°-40°	1607.3	47.2
0°-60°	2739.1	80.4
0°-90°	3407.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3407.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1339	1339	1339	1339	1339	
5°	1339	1334	1320	1330	1328	127
15°	1275	1267	1250	1256	1249	359
25°	1154	1144	1122	1124	1122	531
35°	996	983	962	954	948	622
45°	810	801	782	768	762	625
55°	613	605	590	574	568	548
65°	413	406	393	381	375	409
75°	216	214	207	200	202	231
85°	53	52	50	46	45	62
90°	0	0	0	0	0	



TEST NUMBER: P242267

CATALOG NUMBER: S122DR-S865D840-X4F0-XX-UDD-F-W

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1339.3	1339.3	1339.3	1339.3	1339.3
2.5°	1347.1	1340.6	1326.5	1339.3	1336.8
5°	1339.3	1334.2	1320.0	1330.3	1327.8
7.5°	1330.3	1322.6	1308.4	1318.7	1316.2
10°	1316.2	1307.1	1291.7	1302.0	1298.1
12.5°	1296.8	1289.1	1273.7	1280.1	1277.5
15°	1275.0	1267.2	1250.5	1255.6	1249.2
17.5°	1247.9	1240.2	1223.4	1229.9	1223.4
20°	1218.3	1210.6	1192.5	1196.4	1191.2
22.5°	1188.7	1177.1	1160.3	1160.3	1157.8
25°	1153.9	1143.6	1121.7	1124.3	1121.7
27.5°	1115.3	1106.2	1089.5	1085.6	1079.2
30°	1076.6	1066.3	1047.0	1043.1	1038.0
32.5°	1035.4	1027.7	1007.1	999.4	994.2
35°	995.5	982.6	962.0	954.3	947.8
37.5°	950.4	938.8	918.2	909.2	902.8
40°	904.1	893.8	873.1	861.6	856.4
42.5°	859.0	848.7	828.1	815.2	807.5
45°	810.0	801.0	781.7	767.5	762.4
47.5°	762.4	753.4	732.8	718.6	710.9
50°	712.2	705.7	687.7	669.7	663.2
52.5°	663.2	654.2	637.5	623.3	614.3
55°	613.0	605.3	589.8	574.4	567.9
57.5°	562.8	556.3	539.6	524.1	519.0
60°	512.6	507.4	489.4	475.2	471.3
62.5°	463.6	454.6	441.7	428.8	423.7
65°	413.4	405.7	392.8	381.2	374.8
67.5°	361.9	355.4	343.9	334.8	329.7
70°	314.2	309.1	297.5	288.5	283.3
72.5°	265.3	260.1	253.7	244.7	240.8
75°	216.4	213.8	207.3	199.6	202.2
77.5°	172.6	167.4	164.8	161.0	157.1
80°	128.8	127.5	124.9	121.1	118.5
82.5°	87.6	87.6	86.3	81.1	81.1
85°	52.8	51.5	50.2	46.4	45.1
87.5°	23.2	20.6	18.0	14.2	12.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)