

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930939

Luminaire Tested: DFN2DS-SQ3F0-060DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930939
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-060DS830-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5595.4 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 59.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930939

CATALOG NUMBER: DFN2DS-SQ3F0-060DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930939

CATALOG NUMBER: DFN2DS-SQ3F0-060DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2520	2520	2520
5°	2529	2493	2508
10°	2515	2468	2480
15°	2483	2436	2433
20°	2439	2388	2385
25°	2395	2329	2329
30°	2339	2275	2255
35°	2287	2210	2177
40°	2221	2144	2103
45°	2156	2080	2029
50°	2085	2013	1941
55°	2011	1935	1863
60°	1929	1842	1774
65°	1841	1749	1668
70°	1729	1636	1559
75°	1572	1507	1470
80°	1396	1353	1283
85°	1138	1085	973

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2156 cd/sqm

TEST NUMBER: P930939

CATALOG NUMBER: DFN2DS-SQ3F0-060DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.0	3.7
10°-20°	582.4	10.4
20°-30°	855.9	15.3
30°-40°	994.1	17.8
40°-50°	992.8	17.7
50°-60°	865.7	15.5
60°-70°	639.9	11.4
70°-80°	362.1	6.5
80°-90°	95.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1645.3	29.4
0°-40°	2639.3	47.2
0°-60°	4497.9	80.4
0°-90°	5595.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5595.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2199	2199	2199	2199	2199	
5°	2199	2191	2168	2184	2180	209
15°	2094	2081	2053	2062	2051	590
25°	1895	1878	1842	1846	1842	872
35°	1635	1614	1580	1567	1556	1021
45°	1330	1315	1284	1260	1252	1027
55°	1007	994	969	943	933	900
65°	679	666	645	626	615	671
75°	355	351	340	328	332	379
85°	87	85	82	76	74	102
90°	0	0	0	0	0	

TEST NUMBER: P930939

CATALOG NUMBER: DFN2DS-SQ3F0-060DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2199.2	2199.2	2199.2	2199.2	2199.2
2.5°	2212.0	2201.5	2178.1	2199.2	2195.1
5°	2199.2	2190.9	2167.5	2184.4	2180.4
7.5°	2184.4	2171.9	2148.5	2165.6	2161.3
10°	2161.3	2146.5	2121.1	2138.0	2131.7
12.5°	2129.5	2116.9	2091.5	2102.1	2097.8
15°	2093.5	2081.0	2053.4	2061.9	2051.4
17.5°	2049.1	2036.6	2009.0	2019.5	2009.0
20°	2000.4	1987.9	1958.2	1964.5	1956.3
22.5°	1952.0	1932.9	1905.3	1905.3	1901.1
25°	1894.7	1878.0	1842.0	1846.0	1842.0
27.5°	1831.2	1816.5	1789.0	1782.8	1772.3
30°	1768.0	1750.9	1719.3	1713.0	1704.5
32.5°	1700.2	1687.7	1653.8	1641.0	1632.5
35°	1634.7	1613.6	1579.7	1566.9	1556.4
37.5°	1560.7	1541.6	1507.8	1492.9	1482.3
40°	1484.6	1467.5	1433.7	1414.9	1406.3
42.5°	1410.6	1393.5	1359.9	1338.6	1326.0
45°	1330.3	1315.4	1283.6	1260.5	1251.9
47.5°	1251.9	1237.1	1203.3	1179.9	1167.3
50°	1169.4	1158.8	1129.3	1099.6	1089.0
52.5°	1089.0	1074.3	1046.8	1023.6	1008.8
55°	1006.7	993.9	968.6	943.2	932.7
57.5°	924.2	913.6	886.0	860.7	852.1
60°	841.6	833.3	803.7	780.4	774.0
62.5°	761.2	746.4	725.3	704.2	695.8
65°	678.9	666.2	645.1	626.0	615.4
67.5°	594.3	583.6	564.7	549.9	541.4
70°	516.0	507.5	488.4	473.6	465.3
72.5°	435.7	427.2	416.6	401.9	395.5
75°	355.1	351.2	340.3	327.8	332.1
77.5°	283.4	274.9	270.5	264.3	258.0
80°	211.6	209.3	205.1	198.8	194.5
82.5°	143.8	143.8	141.8	133.3	133.3
85°	86.6	84.6	82.5	76.0	74.0
87.5°	38.2	33.9	29.6	23.4	21.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930939

CATALOG NUMBER: DFN2DS-SQ3F0-060DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.49	16.10	14.86	16.42	16.73	14.05	15.66	14.41	15.97	16.29
	3H	16.24	17.70	16.62	18.02	18.39	15.75	17.21	16.13	17.53	17.89
	4H	16.89	18.26	17.29	18.61	18.98	16.40	17.76	16.79	18.11	18.49
	6H	17.36	18.63	17.77	18.99	19.38	16.86	18.13	17.27	18.49	18.88
	8H	17.50	18.71	17.93	19.10	19.50	17.00	18.21	17.42	18.60	19.00
	12H	17.59	18.75	18.02	19.13	19.56	17.08	18.24	17.51	18.62	19.05
4H	2H	15.05	16.42	15.45	16.77	17.15	14.70	16.07	15.10	16.42	16.79
	3H	17.03	18.18	17.44	18.57	18.97	16.62	17.77	17.03	18.17	18.57
	4H	17.81	18.84	18.24	19.26	19.69	17.38	18.42	17.81	18.83	19.27
	6H	18.40	19.31	18.86	19.75	20.20	17.97	18.87	18.42	19.32	19.77
	8H	18.59	19.44	19.05	19.88	20.35	18.15	19.00	18.61	19.44	19.91
	12H	18.72	19.48	19.20	19.96	20.43	18.27	19.03	18.75	19.51	19.98
8H	4H	18.08	18.93	18.54	19.37	19.83	17.70	18.55	18.17	18.99	19.46
	6H	18.79	19.50	19.29	19.98	20.46	18.41	19.11	18.91	19.60	20.08
	8H	19.05	19.68	19.56	20.19	20.68	18.66	19.29	19.17	19.80	20.28
	12H	19.25	19.81	19.76	20.30	20.86	18.84	19.40	19.35	19.89	20.45
12H	4H	18.10	18.86	18.59	19.34	19.81	17.74	18.50	18.22	18.98	19.45
	6H	18.84	19.47	19.35	19.98	20.46	18.47	19.10	18.98	19.61	20.09
	8H	19.15	19.71	19.66	20.20	20.76	18.77	19.33	19.28	19.82	20.38