

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930975

Luminaire Tested: DFN2DS-SQ3F0-080DS830-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-080DS830-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7460.7 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 82
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930975

CATALOG NUMBER: DFN2DS-SQ3F0-080DS830-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930975

CATALOG NUMBER: DFN2DS-SQ3F0-080DS830-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3360	3360	3360
5°	3373	3324	3344
10°	3353	3291	3307
15°	3311	3248	3245
20°	3252	3184	3180
25°	3194	3105	3105
30°	3119	3033	3007
35°	3049	2946	2903
40°	2961	2859	2805
45°	2874	2773	2705
50°	2779	2684	2588
55°	2681	2580	2484
60°	2571	2455	2365
65°	2454	2332	2225
70°	2305	2182	2078
75°	2096	2009	1960
80°	1861	1805	1711
85°	1518	1447	1298

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2874 cd/sqm

TEST NUMBER: P930975

CATALOG NUMBER: DFN2DS-SQ3F0-080DS830-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.0	3.7
10°-20°	776.5	10.4
20°-30°	1141.2	15.3
30°-40°	1325.4	17.8
40°-50°	1323.8	17.7
50°-60°	1154.3	15.5
60°-70°	853.3	11.4
70°-80°	482.8	6.5
80°-90°	127.4	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2193.7	29.4
0°-40°	3519.1	47.2
0°-60°	5997.2	80.4
0°-90°	7460.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7460.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2932	2932	2932	2932	2932	
5°	2932	2921	2890	2913	2907	278
15°	2791	2775	2738	2749	2735	786
25°	2526	2504	2456	2461	2456	1163
35°	2180	2152	2106	2089	2075	1361
45°	1774	1754	1711	1681	1669	1369
55°	1342	1325	1292	1258	1244	1200
65°	905	888	860	835	821	895
75°	474	468	454	437	443	505
85°	116	113	110	102	99	136
90°	0	0	0	0	0	



TEST NUMBER: P930975

CATALOG NUMBER: DFN2DS-SQ3F0-080DS830-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2932.3	2932.3	2932.3	2932.3	2932.3
2.5°	2949.3	2935.3	2904.2	2932.3	2926.9
5°	2932.3	2921.2	2890.2	2912.6	2907.2
7.5°	2912.6	2895.8	2864.7	2887.4	2881.8
10°	2881.8	2862.0	2828.2	2850.6	2842.3
12.5°	2839.3	2822.5	2788.7	2802.7	2797.1
15°	2791.4	2774.7	2737.8	2749.2	2735.2
17.5°	2732.2	2715.4	2678.6	2692.7	2678.6
20°	2667.3	2650.5	2611.0	2619.4	2608.3
22.5°	2602.7	2577.2	2540.4	2540.4	2534.7
25°	2526.3	2503.9	2456.1	2461.4	2456.1
27.5°	2441.7	2422.0	2385.4	2377.0	2363.0
30°	2357.4	2334.6	2292.5	2284.1	2272.7
32.5°	2267.0	2250.2	2205.0	2188.0	2176.7
35°	2179.6	2151.5	2106.3	2089.3	2075.2
37.5°	2080.9	2055.4	2010.3	1990.5	1976.5
40°	1979.5	1956.7	1911.6	1886.4	1875.1
42.5°	1880.8	1858.0	1813.2	1784.7	1768.0
45°	1773.7	1753.9	1711.4	1680.6	1669.3
47.5°	1669.3	1649.5	1604.3	1573.2	1556.5
50°	1559.2	1545.2	1505.6	1466.1	1452.1
52.5°	1452.1	1432.3	1395.9	1364.8	1345.0
55°	1342.3	1325.2	1291.5	1257.7	1243.5
57.5°	1232.2	1218.2	1181.4	1147.5	1136.1
60°	1122.1	1111.1	1071.5	1040.4	1032.1
62.5°	1015.0	995.3	967.2	939.1	927.7
65°	905.3	888.2	860.0	834.6	820.6
67.5°	792.4	778.1	752.9	733.3	721.9
70°	688.0	676.6	651.3	631.5	620.4
72.5°	580.9	569.6	555.5	535.8	527.4
75°	473.5	468.2	453.9	437.1	442.7
77.5°	377.8	366.4	360.8	352.4	344.0
80°	282.1	279.1	273.5	265.1	259.3
82.5°	191.8	191.8	189.1	177.7	177.7
85°	115.5	112.8	110.1	101.5	98.7
87.5°	50.9	45.2	39.5	31.1	28.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930975

CATALOG NUMBER: DFN2DS-SQ3F0-080DS830-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.49	17.10	15.86	17.42	17.73	15.05	16.66	15.41	16.97	17.29
	3H	17.24	18.70	17.62	19.02	19.38	16.75	18.21	17.13	18.53	18.89
	4H	17.89	19.26	18.29	19.61	19.98	17.39	18.76	17.79	19.11	19.49
	6H	18.36	19.63	18.77	19.99	20.38	17.86	19.13	18.27	19.49	19.88
	8H	18.50	19.71	18.93	20.10	20.50	18.00	19.21	18.42	19.60	20.00
	12H	18.59	19.75	19.02	20.13	20.56	18.08	19.24	18.51	19.62	20.05
4H	2H	16.05	17.42	16.45	17.77	18.15	15.70	17.07	16.10	17.42	17.79
	3H	18.03	19.17	18.44	19.57	19.97	17.62	18.77	18.03	19.17	19.57
	4H	18.80	19.84	19.24	20.25	20.69	18.38	19.42	18.81	19.83	20.27
	6H	19.40	20.31	19.86	20.75	21.20	18.97	19.87	19.42	20.31	20.77
	8H	19.59	20.44	20.05	20.88	21.35	19.15	20.00	19.61	20.44	20.91
	12H	19.72	20.48	20.20	20.96	21.43	19.27	20.03	19.75	20.51	20.98
8H	4H	19.08	19.92	19.54	20.37	20.83	18.70	19.55	19.16	19.99	20.46
	6H	19.79	20.50	20.29	20.98	21.46	19.41	20.11	19.91	20.60	21.08
	8H	20.05	20.68	20.56	21.19	21.68	19.66	20.29	20.17	20.80	21.28
	12H	20.25	20.81	20.76	21.30	21.86	19.84	20.40	20.35	20.89	21.45
12H	4H	19.10	19.86	19.58	20.34	20.81	18.74	19.50	19.22	19.98	20.45
	6H	19.84	20.47	20.35	20.98	21.46	19.47	20.10	19.98	20.61	21.09
	8H	20.15	20.71	20.66	21.20	21.76	19.77	20.33	20.28	20.82	21.38