

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931048

Luminaire Tested: DFN2DS-SQ3F0-120DS830-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931048
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-120DS830-RLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9608.4 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 131.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931048

CATALOG NUMBER: DFN2DS-SQ3F0-120DS830-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931048

CATALOG NUMBER: DFN2DS-SQ3F0-120DS830-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5353	5353	5353
5°	5374	5286	5315
10°	5332	5200	5155
15°	5271	5045	4900
20°	5186	4825	4583
25°	5099	4575	4276
30°	4979	4318	3882
35°	4862	4039	3536
40°	4743	3750	3137
45°	4604	3426	2774
50°	4462	3098	2420
55°	4316	2745	2078
60°	4147	2373	1725
65°	3955	1995	1570
70°	3725	1643	1444
75°	3443	1498	1348
80°	3040	1337	1228
85°	2389	1056	1056

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4604 cd/sqm

TEST NUMBER: P931048

CATALOG NUMBER: DFN2DS-SQ3F0-120DS830-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	437.9	4.6
10°-20°	1202.0	12.5
20°-30°	1687.6	17.6
30°-40°	1839.6	19.1
40°-50°	1690.8	17.6
50°-60°	1327.8	13.8
60°-70°	864.3	9.0
70°-80°	444.9	4.6
80°-90°	113.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3327.4	34.6
0°-40°	5167.0	53.8
0°-60°	8185.6	85.2
0°-90°	9608.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9608.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4672	4672	4672	4672	4672	
5°	4672	4651	4596	4634	4621	443
15°	4444	4397	4253	4173	4131	1252
25°	4034	3898	3619	3446	3382	1855
35°	3476	3260	2888	2622	2528	2175
45°	2841	2558	2114	1814	1712	2194
55°	2160	1831	1374	1120	1040	1930
65°	1459	1116	736	592	579	1446
75°	778	482	338	309	304	823
85°	182	93	80	80	80	218
90°	0	0	0	0	0	

TEST NUMBER: P931048

CATALOG NUMBER: DFN2DS-SQ3F0-120DS830-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4671.9	4671.9	4671.9	4671.9	4671.9
2.5°	4693.0	4671.9	4625.3	4667.9	4659.3
5°	4671.9	4650.8	4595.6	4633.8	4621.3
7.5°	4633.8	4608.6	4549.5	4566.1	4545.0
10°	4583.1	4553.5	4469.1	4456.1	4431.1
12.5°	4519.8	4481.8	4367.3	4342.2	4295.6
15°	4443.6	4397.0	4253.4	4173.1	4131.0
17.5°	4354.8	4287.0	4109.4	4016.6	3948.9
20°	4253.4	4168.6	3957.3	3851.9	3758.6
22.5°	4143.5	4046.2	3800.8	3657.2	3594.0
25°	4033.6	3898.1	3619.1	3445.9	3382.3
27.5°	3902.6	3758.6	3450.0	3251.3	3153.9
30°	3763.1	3602.1	3263.8	3048.5	2934.1
32.5°	3627.6	3432.9	3086.7	2832.8	2726.9
35°	3475.6	3259.8	2887.9	2621.5	2528.1
37.5°	3327.5	3094.8	2701.8	2409.7	2304.3
40°	3171.0	2917.6	2507.1	2207.0	2097.1
42.5°	3010.3	2739.9	2312.9	1999.8	1894.4
45°	2841.3	2557.8	2114.1	1813.6	1712.2
47.5°	2680.6	2380.6	1923.9	1623.4	1530.6
50°	2503.1	2203.0	1737.8	1445.8	1357.4
52.5°	2329.5	2012.3	1560.1	1281.1	1200.9
55°	2160.4	1830.7	1374.0	1120.5	1040.3
57.5°	1987.1	1649.0	1209.3	972.5	904.8
60°	1809.6	1471.3	1035.7	820.5	752.8
62.5°	1636.4	1298.2	887.7	685.0	651.3
65°	1458.8	1116.1	735.7	592.1	579.1
67.5°	1289.7	946.9	592.1	519.9	507.4
70°	1112.0	782.3	490.3	448.1	431.1
72.5°	942.9	629.8	410.0	376.3	367.9
75°	777.8	481.7	338.3	308.6	304.5
77.5°	613.2	342.2	266.5	249.4	240.9
80°	460.7	245.4	202.7	186.1	186.1
82.5°	321.2	165.0	139.5	130.9	130.9
85°	181.7	92.9	80.3	80.3	80.3
87.5°	67.7	33.6	33.6	29.6	29.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931048

CATALOG NUMBER: DFN2DS-SQ3F0-120DS830-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.06	18.59	17.43	18.90	19.21	13.02	14.55	13.39	14.86	15.17
	3H	18.83	20.19	19.21	20.52	20.88	14.29	15.65	14.67	15.98	16.34
	4H	19.50	20.78	19.89	21.12	21.50	14.79	16.07	15.19	16.42	16.80
	6H	19.98	21.17	20.40	21.53	21.93	15.17	16.35	15.58	16.72	17.11
	8H	20.15	21.28	20.58	21.67	22.07	15.30	16.42	15.72	16.81	17.21
	12H	20.25	21.33	20.68	21.71	22.14	15.38	16.46	15.81	16.84	17.27
4H	2H	17.17	18.45	17.57	18.80	19.18	13.72	15.00	14.12	15.35	15.73
	3H	19.10	20.16	19.51	20.56	20.96	15.16	16.23	15.57	16.63	17.03
	4H	19.85	20.81	20.28	21.22	21.66	15.76	16.72	16.19	17.13	17.57
	6H	20.44	21.27	20.90	21.72	22.18	16.25	17.08	16.71	17.52	17.98
	8H	20.66	21.43	21.12	21.88	22.35	16.41	17.19	16.88	17.63	18.10
	12H	20.81	21.50	21.29	21.98	22.45	16.53	17.22	17.01	17.70	18.17
8H	4H	19.87	20.65	20.34	21.10	21.56	16.12	16.89	16.58	17.34	17.80
	6H	20.51	21.15	21.01	21.65	22.12	16.70	17.34	17.20	17.84	18.31
	8H	20.76	21.34	21.28	21.85	22.34	16.92	17.50	17.44	18.01	18.50
	12H	20.97	21.48	21.48	21.97	22.53	17.10	17.61	17.61	18.10	18.67
12H	4H	19.86	20.55	20.34	21.03	21.50	16.16	16.85	16.64	17.33	17.80
	6H	20.49	21.07	21.01	21.58	22.07	16.77	17.34	17.28	17.85	18.34
	8H	20.78	21.29	21.29	21.78	22.34	17.04	17.55	17.55	18.04	18.61

END OF REPORT