

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930908

Luminaire Tested: DFN2DS-SQ3F0-040DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930908
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-040DS840-RLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3403.4 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 38.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930908

CATALOG NUMBER: DFN2DS-SQ3F0-040DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930908

CATALOG NUMBER: DFN2DS-SQ3F0-040DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1896	1896	1896
5°	1903	1872	1883
10°	1889	1842	1826
15°	1867	1787	1736
20°	1837	1709	1623
25°	1806	1621	1515
30°	1764	1530	1375
35°	1722	1431	1253
40°	1680	1328	1111
45°	1631	1213	983
50°	1580	1097	857
55°	1529	972	736
60°	1469	841	611
65°	1401	707	556
70°	1320	582	512
75°	1220	530	478
80°	1077	474	435
85°	847	373	373

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1631 cd/sqm

TEST NUMBER: P930908

CATALOG NUMBER: DFN2DS-SQ3F0-040DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.1	4.6
10°-20°	425.8	12.5
20°-30°	597.8	17.6
30°-40°	651.6	19.1
40°-50°	598.9	17.6
50°-60°	470.3	13.8
60°-70°	306.1	9.0
70°-80°	157.6	4.6
80°-90°	40.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1178.6	34.6
0°-40°	1830.2	53.8
0°-60°	2899.4	85.2
0°-90°	3403.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3403.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1655	1655	1655	1655	1655	
5°	1655	1647	1628	1641	1637	157
15°	1574	1558	1507	1478	1463	444
25°	1429	1381	1282	1221	1198	657
35°	1231	1155	1023	928	896	771
45°	1006	906	749	642	606	777
55°	765	648	487	397	368	684
65°	517	395	261	210	205	512
75°	276	171	120	109	108	291
85°	64	33	28	28	28	77
90°	0	0	0	0	0	

TEST NUMBER: P930908

CATALOG NUMBER: DFN2DS-SQ3F0-040DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1654.9	1654.9	1654.9	1654.9	1654.9
2.5°	1662.4	1654.9	1638.3	1653.5	1650.3
5°	1654.9	1647.3	1627.8	1641.3	1636.9
7.5°	1641.3	1632.4	1611.5	1617.3	1609.9
10°	1623.4	1612.9	1583.0	1578.4	1569.6
12.5°	1601.0	1587.5	1546.9	1538.0	1521.5
15°	1574.0	1557.5	1506.6	1478.2	1463.3
17.5°	1542.5	1518.5	1455.6	1422.7	1398.7
20°	1506.6	1476.6	1401.7	1364.4	1331.3
22.5°	1467.7	1433.2	1346.2	1295.4	1273.1
25°	1428.7	1380.8	1281.9	1220.6	1198.0
27.5°	1382.4	1331.3	1222.0	1151.7	1117.1
30°	1332.9	1275.9	1156.1	1079.8	1039.3
32.5°	1285.0	1216.0	1093.3	1003.4	965.9
35°	1231.1	1154.7	1022.9	928.5	895.5
37.5°	1178.7	1096.2	957.0	853.6	816.2
40°	1123.2	1033.4	888.1	781.8	742.8
42.5°	1066.3	970.5	819.2	708.3	671.0
45°	1006.4	906.0	748.8	642.4	606.5
47.5°	949.5	843.2	681.5	575.1	542.1
50°	886.6	780.3	615.5	512.1	480.8
52.5°	825.1	712.8	552.7	453.8	425.3
55°	765.3	648.4	486.7	396.9	368.5
57.5°	703.9	584.1	428.3	344.4	320.5
60°	640.9	521.1	366.9	290.6	266.7
62.5°	579.7	459.9	314.4	242.6	230.7
65°	516.7	395.3	260.6	209.7	205.1
67.5°	456.9	335.4	209.7	184.2	179.7
70°	393.9	277.1	173.7	158.8	152.7
72.5°	334.0	223.1	145.2	133.3	130.3
75°	275.5	170.7	119.8	109.3	107.9
77.5°	217.2	121.2	94.4	88.4	85.3
80°	163.2	86.9	71.8	66.0	66.0
82.5°	113.8	58.5	49.4	46.3	46.3
85°	64.4	32.9	28.4	28.4	28.4
87.5°	24.0	11.9	11.9	10.5	10.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930908

CATALOG NUMBER: DFN2DS-SQ3F0-040DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.46	14.98	13.82	15.29	15.61	9.42	10.94	9.78	11.25	11.57
	3H	15.22	16.59	15.60	16.92	17.28	10.68	12.05	11.06	12.38	12.74
	4H	15.89	17.17	16.29	17.52	17.90	11.18	12.47	11.58	12.81	13.19
	6H	16.38	17.56	16.79	17.93	18.32	11.57	12.75	11.98	13.12	13.51
	8H	16.54	17.67	16.97	18.06	18.46	11.69	12.82	12.12	13.21	13.61
	12H	16.65	17.73	17.08	18.11	18.54	11.77	12.85	12.20	13.23	13.66
4H	2H	13.56	14.84	13.96	15.19	15.57	10.11	11.39	10.51	11.74	12.12
	3H	15.50	16.56	15.91	16.96	17.36	11.56	12.62	11.97	13.02	13.42
	4H	16.24	17.20	16.68	17.62	18.06	12.16	13.11	12.59	13.53	13.97
	6H	16.84	17.67	17.29	18.11	18.57	12.65	13.48	13.10	13.92	14.38
	8H	17.05	17.83	17.51	18.27	18.74	12.81	13.58	13.27	14.03	14.50
	12H	17.20	17.90	17.69	18.38	18.85	12.92	13.62	13.41	14.10	14.57
8H	4H	16.27	17.05	16.73	17.49	17.96	12.51	13.29	12.97	13.73	14.20
	6H	16.91	17.55	17.40	18.04	18.52	13.10	13.74	13.59	14.23	14.71
	8H	17.16	17.73	17.67	18.24	18.73	13.32	13.89	13.83	14.40	14.89
	12H	17.36	17.87	17.87	18.36	18.93	13.50	14.01	14.01	14.50	15.06
12H	4H	16.25	16.95	16.74	17.43	17.90	12.55	13.25	13.04	13.73	14.20
	6H	16.89	17.46	17.40	17.97	18.46	13.16	13.74	13.67	14.25	14.74
	8H	17.17	17.68	17.68	18.17	18.74	13.43	13.94	13.94	14.43	15.00