

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930998

Luminaire Tested: DFN2DS-SQ3F0-090DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930998
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-090DS840-RLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7657.7 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 93.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930998

CATALOG NUMBER: DFN2DS-SQ3F0-090DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930998

CATALOG NUMBER: DFN2DS-SQ3F0-090DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4266	4266	4266
5°	4283	4213	4236
10°	4250	4144	4109
15°	4201	4021	3905
20°	4133	3846	3653
25°	4064	3647	3408
30°	3968	3442	3094
35°	3875	3219	2818
40°	3780	2989	2500
45°	3669	2730	2211
50°	3556	2469	1928
55°	3439	2187	1656
60°	3305	1892	1375
65°	3152	1590	1251
70°	2969	1309	1151
75°	2744	1194	1074
80°	2423	1066	979
85°	1902	841	841

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3669 cd/sqm

TEST NUMBER: P930998

CATALOG NUMBER: DFN2DS-SQ3F0-090DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.0	4.6
10°-20°	958.0	12.5
20°-30°	1345.0	17.6
30°-40°	1466.1	19.1
40°-50°	1347.5	17.6
50°-60°	1058.3	13.8
60°-70°	688.8	9.0
70°-80°	354.6	4.6
80°-90°	90.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2651.9	34.6
0°-40°	4118.0	53.8
0°-60°	6523.8	85.2
0°-90°	7657.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7657.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3723	3723	3723	3723	3723	
5°	3723	3707	3663	3693	3683	353
15°	3541	3504	3390	3326	3292	998
25°	3215	3107	2884	2746	2696	1478
35°	2770	2598	2302	2089	2015	1734
45°	2264	2038	1685	1445	1365	1749
55°	1722	1459	1095	893	829	1539
65°	1163	890	586	472	462	1153
75°	620	384	270	246	243	656
85°	145	74	64	64	64	174
90°	0	0	0	0	0	

TEST NUMBER: P930998

CATALOG NUMBER: DFN2DS-SQ3F0-090DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3723.4	3723.4	3723.4	3723.4	3723.4
2.5°	3740.2	3723.4	3686.2	3720.2	3713.4
5°	3723.4	3706.6	3662.7	3693.0	3683.0
7.5°	3693.0	3673.0	3625.8	3639.0	3622.2
10°	3652.6	3629.0	3561.9	3551.4	3531.4
12.5°	3602.2	3571.9	3480.7	3460.7	3423.4
15°	3541.4	3504.3	3389.9	3325.8	3292.3
17.5°	3470.7	3416.7	3275.1	3201.1	3147.1
20°	3389.9	3322.3	3153.9	3069.9	2995.5
22.5°	3302.3	3224.7	3029.1	2914.7	2864.4
25°	3214.7	3106.7	2884.4	2746.3	2695.6
27.5°	3110.3	2995.5	2749.5	2591.2	2513.6
30°	2999.1	2870.8	2601.2	2429.6	2338.4
32.5°	2891.1	2735.9	2460.0	2257.7	2173.3
35°	2770.0	2598.0	2301.6	2089.3	2014.9
37.5°	2651.9	2466.5	2153.3	1920.5	1836.5
40°	2527.2	2325.2	1998.1	1759.0	1671.4
42.5°	2399.2	2183.7	1843.2	1593.8	1509.7
45°	2264.5	2038.5	1684.9	1445.3	1364.6
47.5°	2136.4	1897.3	1533.3	1293.8	1219.8
50°	1994.9	1755.7	1385.0	1152.3	1081.8
52.5°	1856.6	1603.8	1243.4	1021.0	957.1
55°	1721.7	1459.0	1095.0	893.1	829.0
57.5°	1583.8	1314.2	963.9	775.1	721.1
60°	1442.1	1172.6	825.5	653.9	599.9
62.5°	1304.2	1034.6	707.5	545.9	519.1
65°	1162.6	889.5	586.3	471.9	461.6
67.5°	1027.8	754.7	471.9	414.3	404.3
70°	886.3	623.5	390.8	357.2	343.5
72.5°	751.5	501.9	326.7	299.9	293.2
75°	619.9	384.0	269.6	245.9	242.7
77.5°	488.7	272.8	212.3	198.8	192.0
80°	367.2	195.6	161.6	148.3	148.3
82.5°	256.0	131.5	111.2	104.4	104.4
85°	144.7	74.0	64.0	64.0	64.0
87.5°	54.0	26.8	26.8	23.6	23.6
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930998

CATALOG NUMBER: DFN2DS-SQ3F0-090DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.28	17.80	16.64	18.11	18.42	12.24	13.76	12.60	14.07	14.39
	3H	18.04	19.41	18.42	19.73	20.10	13.50	14.87	13.88	15.19	15.56
	4H	18.71	19.99	19.11	20.34	20.71	14.00	15.28	14.40	15.63	16.01
	6H	19.20	20.38	19.61	20.75	21.14	14.38	15.57	14.80	15.93	16.32
	8H	19.36	20.49	19.79	20.88	21.28	14.51	15.63	14.93	16.02	16.43
	12H	19.46	20.54	19.89	20.92	21.35	14.59	15.67	15.02	16.05	16.48
4H	2H	16.38	17.66	16.78	18.01	18.39	12.93	14.21	13.33	14.56	14.94
	3H	18.31	19.38	18.72	19.78	20.18	14.37	15.44	14.78	15.84	16.24
	4H	19.06	20.02	19.49	20.43	20.87	14.97	15.93	15.41	16.35	16.78
	6H	19.65	20.49	20.11	20.93	21.39	15.46	16.29	15.92	16.74	17.20
	8H	19.87	20.65	20.33	21.09	21.56	15.62	16.40	16.09	16.85	17.31
	12H	20.02	20.72	20.50	21.19	21.67	15.74	16.44	16.22	16.91	17.38
8H	4H	19.09	19.86	19.55	20.31	20.77	15.33	16.10	15.79	16.55	17.02
	6H	19.72	20.37	20.22	20.86	21.33	15.91	16.56	16.41	17.05	17.52
	8H	19.97	20.55	20.49	21.06	21.55	16.13	16.71	16.65	17.22	17.71
	12H	20.18	20.69	20.69	21.18	21.74	16.31	16.82	16.82	17.32	17.88
12H	4H	19.07	19.77	19.55	20.24	20.71	15.37	16.07	15.85	16.54	17.01
	6H	19.70	20.28	20.22	20.79	21.28	15.98	16.55	16.49	17.06	17.55
	8H	19.99	20.50	20.50	20.99	21.56	16.25	16.76	16.76	17.25	17.82