

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930945

Luminaire Tested: DFN2DS-SQ3F0-060DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930945
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-060DS850-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6587.4 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 59.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930945

CATALOG NUMBER: DFN2DS-SQ3F0-060DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930945

CATALOG NUMBER: DFN2DS-SQ3F0-060DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2967	2967	2967
5°	2978	2935	2952
10°	2960	2905	2920
15°	2924	2868	2865
20°	2872	2811	2808
25°	2820	2742	2742
30°	2754	2678	2655
35°	2692	2601	2563
40°	2614	2525	2476
45°	2538	2449	2388
50°	2454	2370	2285
55°	2368	2278	2193
60°	2271	2168	2088
65°	2167	2059	1964
70°	2035	1926	1835
75°	1851	1774	1731
80°	1644	1593	1511
85°	1340	1277	1146

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2538 cd/sqm

TEST NUMBER: P930945

CATALOG NUMBER: DFN2DS-SQ3F0-060DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.7	3.7
10°-20°	685.6	10.4
20°-30°	1007.6	15.3
30°-40°	1170.3	17.8
40°-50°	1168.8	17.7
50°-60°	1019.2	15.5
60°-70°	753.4	11.4
70°-80°	426.3	6.5
80°-90°	112.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1937.0	29.4
0°-40°	3107.2	47.2
0°-60°	5295.3	80.4
0°-90°	6587.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6587.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2589	2589	2589	2589	2589	
5°	2589	2579	2552	2572	2567	246
15°	2465	2450	2417	2428	2415	694
25°	2231	2211	2168	2173	2168	1026
35°	1925	1900	1860	1845	1832	1202
45°	1566	1549	1511	1484	1474	1209
55°	1185	1170	1140	1110	1098	1060
65°	799	784	759	737	724	790
75°	418	413	401	386	391	446
85°	102	100	97	90	87	120
90°	0	0	0	0	0	

TEST NUMBER: P930945

CATALOG NUMBER: DFN2DS-SQ3F0-060DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2589.1	2589.1	2589.1	2589.1	2589.1
2.5°	2604.2	2591.7	2564.2	2589.1	2584.3
5°	2589.1	2579.3	2551.8	2571.7	2566.9
7.5°	2571.7	2556.9	2529.4	2549.5	2544.5
10°	2544.5	2527.1	2497.1	2517.0	2509.6
12.5°	2507.0	2492.1	2462.3	2474.7	2469.7
15°	2464.6	2449.9	2417.4	2427.5	2415.1
17.5°	2412.4	2397.7	2365.2	2377.5	2365.2
20°	2355.1	2340.3	2305.4	2312.8	2303.1
22.5°	2298.1	2275.6	2243.1	2243.1	2238.1
25°	2230.6	2210.9	2168.5	2173.3	2168.5
27.5°	2155.9	2138.5	2106.2	2098.9	2086.5
30°	2081.5	2061.3	2024.1	2016.7	2006.6
32.5°	2001.6	1986.9	1947.0	1931.9	1921.9
35°	1924.6	1899.7	1859.8	1844.7	1832.3
37.5°	1837.4	1814.9	1775.1	1757.5	1745.1
40°	1747.8	1727.7	1687.9	1665.7	1655.6
42.5°	1660.6	1640.5	1601.0	1575.9	1561.0
45°	1566.1	1548.6	1511.1	1484.0	1473.9
47.5°	1473.9	1456.4	1416.6	1389.1	1374.3
50°	1376.7	1364.3	1329.5	1294.5	1282.1
52.5°	1282.1	1264.7	1232.4	1205.0	1187.6
55°	1185.2	1170.1	1140.3	1110.4	1098.0
57.5°	1088.0	1075.6	1043.1	1013.3	1003.2
60°	990.8	981.0	946.2	918.7	911.3
62.5°	896.2	878.8	853.9	829.1	819.1
65°	799.3	784.3	759.4	736.9	724.5
67.5°	699.7	687.0	664.8	647.4	637.3
70°	607.5	597.5	575.0	557.6	547.8
72.5°	512.9	502.9	490.5	473.1	465.7
75°	418.1	413.4	400.7	385.9	390.9
77.5°	333.6	323.6	318.5	311.2	303.8
80°	249.1	246.4	241.4	234.0	229.0
82.5°	169.3	169.3	166.9	156.9	156.9
85°	101.9	99.6	97.1	89.5	87.2
87.5°	44.9	39.9	34.8	27.5	24.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930945

CATALOG NUMBER: DFN2DS-SQ3F0-060DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.06	16.67	15.43	16.99	17.30	14.62	16.23	14.98	16.54	16.86
	3H	16.81	18.27	17.19	18.59	18.95	16.32	17.77	16.70	18.10	18.46
	4H	17.46	18.83	17.86	19.17	19.55	16.96	18.33	17.36	18.68	19.06
	6H	17.93	19.19	18.34	19.56	19.95	17.42	18.69	17.84	19.06	19.45
	8H	18.07	19.28	18.49	19.67	20.07	17.57	18.78	17.99	19.17	19.57
	12H	18.16	19.32	18.59	19.70	20.13	17.65	18.81	18.08	19.19	19.62
4H	2H	15.62	16.99	16.02	17.34	17.71	15.27	16.64	15.67	16.99	17.36
	3H	17.60	18.74	18.01	19.14	19.54	17.19	18.34	17.60	18.73	19.13
	4H	18.37	19.41	18.80	19.82	20.26	17.95	18.98	18.38	19.40	19.83
	6H	18.97	19.87	19.42	20.31	20.77	18.54	19.44	18.99	19.88	20.34
	8H	19.16	20.01	19.62	20.45	20.91	18.72	19.57	19.18	20.01	20.48
	12H	19.29	20.05	19.77	20.53	21.00	18.84	19.60	19.32	20.07	20.54
8H	4H	18.65	19.49	19.11	19.94	20.40	18.27	19.12	18.73	19.56	20.03
	6H	19.36	20.06	19.85	20.55	21.03	18.98	19.68	19.47	20.17	20.65
	8H	19.62	20.25	20.13	20.76	21.24	19.23	19.86	19.74	20.37	20.85
	12H	19.82	20.38	20.33	20.87	21.43	19.41	19.96	19.91	20.45	21.02
12H	4H	18.67	19.43	19.15	19.91	20.38	18.31	19.07	18.79	19.54	20.01
	6H	19.41	20.04	19.92	20.54	21.03	19.04	19.67	19.55	20.18	20.66
	8H	19.72	20.28	20.23	20.77	21.33	19.34	19.90	19.85	20.39	20.95