

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P892210

Luminaire Tested: **0540N**

Issue Date: 10/24/2024

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P892210  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P222643)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 10/24/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: 0540N  
Description: Define Patient, Downlight with Narrow 25deg

Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 695.0 lumens  
Efficiency: N/A  
Efficacy: 95.2 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P892210  
CATALOG NUMBER: 0540N

### Luminous Intensity Polar Plot





TEST NUMBER: P892210  
 CATALOG NUMBER: 0540N

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	97
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	95	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	92	92
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	90	90	90
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	88	88	88
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	86	86	86
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84	84	84	84
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	82	82	82
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	80	80	80
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79	79	79	79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2034360
5°	1878396
10°	1271419
15°	432585
20°	158879
25°	84217
30°	43298
35°	20177
40°	6634
45°	3349
50°	1535
55°	602
60°	691
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P892210  
 CATALOG NUMBER: 0540N

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	322.6	46.4
10°-20°	271.3	39.0
20°-30°	74.4	10.7
30°-40°	21.7	3.1
40°-50°	4.0	0.6
50°-60°	0.9	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	668.3	96.2
0°-40°	690.0	99.3
0°-60°	694.9	100.0
0°-90°	695.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	695.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4123	
5°	3793	323
15°	847	271
25°	155	74
35°	34	22
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P892210  
CATALOG NUMBER: 0540N

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4123.3
1°	4099.4
2°	4056.9
3°	3996.0
4°	3912.5
5°	3792.7
6°	3629.1
7°	3424.4
8°	3174.5
9°	2879.4
10°	2537.8
11°	2163.4
12°	1773.8
13°	1402.1
14°	1085.1
15°	846.9
17.5°	477.8
20°	302.6
22.5°	215.6
25°	154.7
27.5°	109.5
30°	76.0
32.5°	53.4
35°	33.5
37.5°	13.7
40°	10.3
42.5°	7.5
45°	4.8
47.5°	2.7
50°	2.0
52.5°	1.4
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P892210  
CATALOG NUMBER: 0540N

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)