

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930999

Luminaire Tested: DFN2DS-SQ3F0-090DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930999
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-090DS850-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9881.2 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 93.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930999

CATALOG NUMBER: DFN2DS-SQ3F0-090DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930999

CATALOG NUMBER: DFN2DS-SQ3F0-090DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4450	4450	4450
5°	4467	4403	4429
10°	4441	4358	4380
15°	4386	4301	4297
20°	4307	4217	4212
25°	4230	4112	4112
30°	4131	4017	3982
35°	4038	3902	3845
40°	3921	3787	3715
45°	3806	3673	3583
50°	3681	3555	3428
55°	3551	3417	3290
60°	3406	3252	3133
65°	3250	3088	2947
70°	3053	2890	2753
75°	2777	2661	2596
80°	2465	2389	2267
85°	2010	1917	1720

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3806 cd/sqm

TEST NUMBER: P930999

CATALOG NUMBER: DFN2DS-SQ3F0-090DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.5	3.7
10°-20°	1028.5	10.4
20°-30°	1511.4	15.3
30°-40°	1755.4	17.8
40°-50°	1753.3	17.7
50°-60°	1528.8	15.5
60°-70°	1130.1	11.4
70°-80°	639.4	6.5
80°-90°	168.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2905.4	29.4
0°-40°	4660.9	47.2
0°-60°	7942.9	80.4
0°-90°	9881.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9881.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3884	3884	3884	3884	3884	
5°	3884	3869	3828	3858	3850	369
15°	3697	3675	3626	3641	3622	1041
25°	3346	3316	3253	3260	3253	1540
35°	2887	2850	2790	2767	2748	1803
45°	2349	2323	2267	2226	2211	1813
55°	1778	1755	1710	1666	1647	1589
65°	1199	1176	1139	1106	1087	1185
75°	627	620	601	579	586	670
85°	153	149	146	134	131	180
90°	0	0	0	0	0	

TEST NUMBER: P930999

CATALOG NUMBER: DFN2DS-SQ3F0-090DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3883.6	3883.6	3883.6	3883.6	3883.6
2.5°	3906.2	3887.6	3846.5	3883.6	3876.5
5°	3883.6	3869.0	3827.8	3857.5	3850.3
7.5°	3857.5	3835.4	3794.1	3824.3	3816.7
10°	3816.7	3790.6	3745.8	3775.5	3764.4
12.5°	3760.4	3738.2	3693.5	3712.0	3704.6
15°	3697.1	3674.9	3626.1	3641.2	3622.5
17.5°	3618.6	3596.4	3547.7	3566.3	3547.7
20°	3532.6	3510.4	3458.1	3469.2	3454.5
22.5°	3447.0	3413.4	3364.6	3364.6	3357.1
25°	3346.0	3316.2	3252.9	3260.0	3252.9
27.5°	3233.8	3207.7	3159.4	3148.3	3129.7
30°	3122.2	3092.0	3036.1	3025.0	3010.0
32.5°	3002.5	2980.3	2920.4	2897.9	2882.8
35°	2886.8	2849.6	2789.7	2767.2	2748.5
37.5°	2756.1	2722.4	2662.5	2636.4	2617.8
40°	2621.7	2591.6	2531.7	2498.5	2483.5
42.5°	2490.9	2460.9	2401.4	2363.8	2341.7
45°	2349.1	2323.0	2266.7	2225.9	2210.9
47.5°	2210.9	2184.7	2124.8	2083.7	2061.5
50°	2065.1	2046.4	1994.1	1941.9	1923.2
52.5°	1923.2	1897.1	1848.7	1807.6	1781.4
55°	1777.8	1755.2	1710.4	1665.7	1647.1
57.5°	1632.0	1613.4	1564.7	1519.9	1504.8
60°	1486.2	1471.5	1419.2	1378.0	1367.0
62.5°	1344.3	1318.2	1280.9	1243.7	1228.7
65°	1198.9	1176.3	1139.1	1105.5	1086.8
67.5°	1049.6	1030.6	997.2	971.2	956.1
70°	911.3	896.2	862.6	836.4	821.8
72.5°	769.4	754.3	735.7	709.6	698.6
75°	627.3	620.0	601.1	578.9	586.4
77.5°	500.4	485.4	477.9	466.8	455.7
80°	373.6	369.6	362.1	351.0	343.6
82.5°	254.0	254.0	250.4	235.3	235.3
85°	152.9	149.4	145.8	134.3	130.8
87.5°	67.3	59.8	52.3	41.3	37.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930999

CATALOG NUMBER: DFN2DS-SQ3F0-090DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.47	18.08	16.83	18.39	18.71	16.03	17.64	16.39	17.95	18.26
	3H	18.22	19.67	18.60	20.00	20.36	17.73	19.18	18.11	19.51	19.87
	4H	18.87	20.23	19.26	20.58	20.96	18.37	19.74	18.77	20.09	20.46
	6H	19.33	20.60	19.75	20.97	21.36	18.83	20.10	19.24	20.47	20.86
	8H	19.48	20.69	19.90	21.08	21.48	18.98	20.19	19.40	20.58	20.97
	12H	19.57	20.73	20.00	21.11	21.54	19.06	20.22	19.49	20.60	21.03
4H	2H	17.03	18.40	17.43	18.75	19.12	16.68	18.05	17.08	18.39	18.77
	3H	19.01	20.15	19.41	20.55	20.95	18.60	19.74	19.01	20.14	20.54
	4H	19.78	20.82	20.21	21.23	21.67	19.36	20.39	19.79	20.81	21.24
	6H	20.38	21.28	20.83	21.72	22.18	19.95	20.85	20.40	21.29	21.75
	8H	20.57	21.41	21.03	21.86	22.32	20.13	20.98	20.59	21.42	21.88
	12H	20.70	21.46	21.18	21.94	22.40	20.25	21.01	20.73	21.48	21.95
8H	4H	20.05	20.90	20.52	21.34	21.81	19.68	20.53	20.14	20.97	21.44
	6H	20.77	21.47	21.26	21.96	22.44	20.39	21.09	20.88	21.58	22.05
	8H	21.03	21.66	21.54	22.17	22.65	20.64	21.27	21.15	21.77	22.26
	12H	21.23	21.79	21.74	22.28	22.84	20.82	21.37	21.32	21.86	22.42
12H	4H	20.08	20.84	20.56	21.32	21.79	19.72	20.48	20.20	20.95	21.42
	6H	20.81	21.45	21.32	21.95	22.44	20.45	21.08	20.96	21.58	22.07
	8H	21.13	21.69	21.64	22.18	22.74	20.75	21.31	21.26	21.80	22.36

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7