

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930947

Luminaire Tested: DFN2DS-SQ3F0-060DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930947
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-060DS927-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4704.5 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 59.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930947

CATALOG NUMBER: DFN2DS-SQ3F0-060DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930947

CATALOG NUMBER: DFN2DS-SQ3F0-060DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2119	2119	2119
5°	2127	2096	2109
10°	2114	2075	2085
15°	2088	2048	2046
20°	2051	2008	2005
25°	2014	1958	1958
30°	1967	1913	1896
35°	1922	1858	1830
40°	1867	1803	1769
45°	1812	1749	1706
50°	1753	1692	1632
55°	1691	1627	1567
60°	1622	1548	1491
65°	1548	1471	1403
70°	1454	1376	1311
75°	1322	1267	1236
80°	1174	1138	1079
85°	957	912	819

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1812 cd/sqm

TEST NUMBER: P930947

CATALOG NUMBER: DFN2DS-SQ3F0-060DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.0	3.7
10°-20°	489.7	10.4
20°-30°	719.6	15.3
30°-40°	835.8	17.8
40°-50°	834.7	17.7
50°-60°	727.9	15.5
60°-70°	538.1	11.4
70°-80°	304.4	6.5
80°-90°	80.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1383.3	29.4
0°-40°	2219.1	47.2
0°-60°	3781.7	80.4
0°-90°	4704.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4704.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1849	1849	1849	1849	1849	
5°	1849	1842	1822	1837	1833	176
15°	1760	1750	1726	1734	1725	496
25°	1593	1579	1549	1552	1549	733
35°	1374	1357	1328	1317	1308	858
45°	1118	1106	1079	1060	1053	863
55°	846	836	814	793	784	757
65°	571	560	542	526	517	564
75°	299	295	286	276	279	319
85°	73	71	69	64	62	86
90°	0	0	0	0	0	



TEST NUMBER: P930947

CATALOG NUMBER: DFN2DS-SQ3F0-060DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1849.0	1849.0	1849.0	1849.0	1849.0
2.5°	1859.8	1850.9	1831.3	1849.0	1845.6
5°	1849.0	1842.0	1822.4	1836.6	1833.2
7.5°	1836.6	1826.0	1806.4	1820.7	1817.2
10°	1817.2	1804.7	1783.3	1797.5	1792.2
12.5°	1790.4	1779.8	1758.5	1767.3	1763.8
15°	1760.1	1749.6	1726.4	1733.6	1724.7
17.5°	1722.8	1712.3	1689.1	1697.9	1689.1
20°	1681.9	1671.4	1646.4	1651.7	1644.7
22.5°	1641.2	1625.1	1601.9	1601.9	1598.3
25°	1593.0	1578.9	1548.7	1552.1	1548.7
27.5°	1539.6	1527.2	1504.2	1498.9	1490.1
30°	1486.5	1472.1	1445.6	1440.3	1433.0
32.5°	1429.5	1418.9	1390.4	1379.7	1372.5
35°	1374.4	1356.7	1328.2	1317.4	1308.5
37.5°	1312.2	1296.1	1267.7	1255.2	1246.3
40°	1248.2	1233.9	1205.4	1189.6	1182.4
42.5°	1185.9	1171.6	1143.3	1125.4	1114.8
45°	1118.5	1105.9	1079.2	1059.8	1052.6
47.5°	1052.6	1040.1	1011.7	992.1	981.4
50°	983.2	974.3	949.4	924.5	915.6
52.5°	915.6	903.2	880.1	860.6	848.2
55°	846.4	835.6	814.3	793.0	784.2
57.5°	777.0	768.2	745.0	723.7	716.4
60°	707.6	700.6	675.7	656.1	650.8
62.5°	640.0	627.6	609.8	592.1	585.0
65°	570.8	560.1	542.4	526.3	517.4
67.5°	499.7	490.6	474.8	462.4	455.2
70°	433.9	426.7	410.7	398.2	391.2
72.5°	366.3	359.2	350.3	337.9	332.6
75°	298.6	295.3	286.1	275.6	279.2
77.5°	238.2	231.1	227.5	222.2	216.9
80°	177.9	176.0	172.4	167.1	163.5
82.5°	120.9	120.9	119.2	112.1	112.1
85°	72.8	71.1	69.4	63.9	62.3
87.5°	32.1	28.5	24.9	19.6	17.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930947

CATALOG NUMBER: DFN2DS-SQ3F0-060DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.89	15.50	14.26	15.82	16.13	13.45	15.06	13.81	15.37	15.69
	3H	15.64	17.10	16.02	17.42	17.78	15.15	16.60	15.53	16.93	17.29
	4H	16.29	17.66	16.69	18.00	18.38	15.79	17.16	16.19	17.51	17.89
	6H	16.76	18.03	17.17	18.39	18.78	16.26	17.52	16.67	17.89	18.28
	8H	16.90	18.11	17.32	18.50	18.90	16.40	17.61	16.82	18.00	18.40
	12H	16.99	18.15	17.42	18.53	18.96	16.48	17.64	16.91	18.02	18.45
4H	2H	14.45	15.82	14.85	16.17	16.54	14.10	15.47	14.50	15.82	16.19
	3H	16.43	17.57	16.84	17.97	18.37	16.02	17.17	16.43	17.56	17.96
	4H	17.20	18.24	17.63	18.65	19.09	16.78	17.82	17.21	18.23	18.67
	6H	17.80	18.70	18.25	19.15	19.60	17.37	18.27	17.82	18.71	19.17
	8H	17.99	18.84	18.45	19.28	19.74	17.55	18.40	18.01	18.84	19.31
	12H	18.12	18.88	18.60	19.36	19.83	17.67	18.43	18.15	18.90	19.37
8H	4H	17.48	18.32	17.94	18.77	19.23	17.10	17.95	17.56	18.39	18.86
	6H	18.19	18.89	18.68	19.38	19.86	17.81	18.51	18.30	19.00	19.48
	8H	18.45	19.08	18.96	19.59	20.07	18.06	18.69	18.57	19.20	19.68
	12H	18.65	19.21	19.16	19.70	20.26	18.24	18.79	18.74	19.29	19.85
12H	4H	17.50	18.26	17.98	18.74	19.21	17.14	17.90	17.62	18.37	18.84
	6H	18.24	18.87	18.75	19.37	19.86	17.87	18.50	18.38	19.01	19.49
	8H	18.55	19.11	19.06	19.60	20.16	18.17	18.73	18.68	19.22	19.78