

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930949

Luminaire Tested: DFN2DS-SQ3F0-060DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930949
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-060DS930-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4841.1 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 59.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930949

CATALOG NUMBER: DFN2DS-SQ3F0-060DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930949

CATALOG NUMBER: DFN2DS-SQ3F0-060DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2180	2180	2180
5°	2188	2157	2170
10°	2176	2135	2146
15°	2149	2107	2105
20°	2110	2066	2064
25°	2072	2015	2015
30°	2024	1968	1951
35°	1978	1912	1883
40°	1921	1855	1820
45°	1865	1799	1755
50°	1803	1742	1680
55°	1740	1674	1612
60°	1669	1594	1535
65°	1593	1513	1443
70°	1496	1416	1349
75°	1360	1304	1272
80°	1208	1171	1111
85°	985	939	843

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1865 cd/sqm

TEST NUMBER: P930949

CATALOG NUMBER: DFN2DS-SQ3F0-060DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.1	3.7
10°-20°	503.9	10.4
20°-30°	740.5	15.3
30°-40°	860.0	17.8
40°-50°	859.0	17.7
50°-60°	749.0	15.5
60°-70°	553.7	11.4
70°-80°	313.3	6.5
80°-90°	82.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1423.5	29.4
0°-40°	2283.5	47.2
0°-60°	3891.5	80.4
0°-90°	4841.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4841.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1903	1896	1875	1890	1886	181
15°	1811	1800	1776	1784	1775	510
25°	1639	1625	1594	1597	1594	754
35°	1414	1396	1367	1356	1346	883
45°	1151	1138	1110	1091	1083	888
55°	871	860	838	816	807	779
65°	587	576	558	542	532	581
75°	307	304	294	284	287	328
85°	75	73	71	66	64	88
90°	0	0	0	0	0	

TEST NUMBER: P930949

CATALOG NUMBER: DFN2DS-SQ3F0-060DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1913.8	1904.7	1884.4	1902.7	1899.2
5°	1902.7	1895.5	1875.3	1889.9	1886.4
7.5°	1889.9	1879.1	1858.9	1873.6	1869.9
10°	1869.9	1857.1	1835.1	1849.7	1844.3
12.5°	1842.4	1831.5	1809.5	1818.7	1815.0
15°	1811.3	1800.4	1776.5	1784.0	1774.8
17.5°	1772.9	1762.0	1738.2	1747.2	1738.2
20°	1730.7	1719.9	1694.2	1699.7	1692.5
22.5°	1688.8	1672.3	1648.4	1648.4	1644.8
25°	1639.3	1624.8	1593.7	1597.2	1593.7
27.5°	1584.4	1571.6	1547.8	1542.5	1533.3
30°	1529.7	1514.8	1487.5	1482.1	1474.7
32.5°	1471.0	1460.2	1430.8	1419.7	1412.4
35°	1414.4	1396.1	1366.8	1355.7	1346.5
37.5°	1350.3	1333.7	1304.5	1291.6	1282.5
40°	1284.4	1269.7	1240.4	1224.1	1216.7
42.5°	1220.4	1205.6	1176.5	1158.1	1147.2
45°	1150.9	1138.1	1110.5	1090.6	1083.1
47.5°	1083.1	1070.3	1041.1	1020.9	1009.9
50°	1011.7	1002.6	977.0	951.3	942.2
52.5°	942.2	929.4	905.7	885.6	872.8
55°	871.0	859.9	838.0	816.1	806.9
57.5°	799.6	790.5	766.6	744.7	737.2
60°	728.1	720.9	695.4	675.1	669.7
62.5°	658.6	645.8	627.6	609.3	602.0
65°	587.4	576.4	558.1	541.6	532.4
67.5°	514.2	504.9	488.6	475.8	468.4
70°	446.5	439.1	422.6	409.8	402.6
72.5°	376.9	369.6	360.5	347.7	342.2
75°	307.3	303.8	294.5	283.6	287.3
77.5°	245.2	237.8	234.1	228.7	223.2
80°	183.0	181.1	177.4	172.0	168.3
82.5°	124.5	124.5	122.7	115.3	115.3
85°	74.9	73.2	71.4	65.8	64.1
87.5°	33.0	29.3	25.6	20.2	18.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930949

CATALOG NUMBER: DFN2DS-SQ3F0-060DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.99	15.60	14.36	15.92	16.23	13.55	15.16	13.91	15.47	15.79
	3H	15.74	17.20	16.12	17.52	17.88	15.25	16.70	15.63	17.03	17.39
	4H	16.39	17.76	16.79	18.10	18.48	15.89	17.26	16.29	17.61	17.99
	6H	16.86	18.12	17.27	18.49	18.88	16.35	17.62	16.77	17.99	18.38
	8H	17.00	18.21	17.42	18.60	19.00	16.50	17.71	16.92	18.10	18.50
	12H	17.09	18.25	17.52	18.63	19.06	16.58	17.74	17.01	18.12	18.55
4H	2H	14.55	15.92	14.95	16.27	16.64	14.20	15.57	14.60	15.92	16.29
	3H	16.53	17.67	16.94	18.07	18.47	16.12	17.27	16.53	17.66	18.06
	4H	17.30	18.34	17.73	18.75	19.19	16.88	17.91	17.31	18.33	18.76
	6H	17.90	18.80	18.35	19.24	19.70	17.47	18.37	17.92	18.81	19.27
	8H	18.09	18.94	18.55	19.38	19.84	17.65	18.50	18.11	18.94	19.40
	12H	18.22	18.98	18.70	19.46	19.93	17.77	18.53	18.25	19.00	19.47
8H	4H	17.58	18.42	18.04	18.87	19.33	17.20	18.05	17.66	18.49	18.96
	6H	18.29	18.99	18.78	19.48	19.96	17.91	18.61	18.40	19.10	19.58
	8H	18.55	19.18	19.06	19.69	20.17	18.16	18.79	18.67	19.30	19.78
	12H	18.75	19.31	19.26	19.80	20.36	18.34	18.89	18.84	19.38	19.95
12H	4H	17.60	18.36	18.08	18.84	19.31	17.24	18.00	17.72	18.47	18.94
	6H	18.34	18.97	18.85	19.47	19.96	17.97	18.60	18.48	19.11	19.59
	8H	18.65	19.21	19.16	19.70	20.26	18.27	18.83	18.78	19.32	19.88