

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930967

Luminaire Tested: DFN2DS-SQ3F0-070DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930967
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-070DS930-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5648.0 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 71.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930967

CATALOG NUMBER: DFN2DS-SQ3F0-070DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930967

CATALOG NUMBER: DFN2DS-SQ3F0-070DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2543	2543	2543
5°	2553	2516	2531
10°	2538	2491	2503
15°	2507	2459	2456
20°	2462	2410	2408
25°	2418	2351	2351
30°	2361	2296	2276
35°	2308	2230	2197
40°	2241	2164	2123
45°	2176	2099	2048
50°	2104	2032	1960
55°	2030	1953	1881
60°	1947	1859	1790
65°	1858	1765	1684
70°	1745	1652	1574
75°	1587	1521	1484
80°	1409	1366	1295
85°	1149	1096	982

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2176 cd/sqm

TEST NUMBER: P930967

CATALOG NUMBER: DFN2DS-SQ3F0-070DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.9	3.7
10°-20°	587.9	10.4
20°-30°	863.9	15.3
30°-40°	1003.4	17.8
40°-50°	1002.1	17.7
50°-60°	873.8	15.5
60°-70°	646.0	11.4
70°-80°	365.5	6.5
80°-90°	96.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1660.7	29.4
0°-40°	2664.1	47.2
0°-60°	4540.1	80.4
0°-90°	5648.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5648.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2220	2220	2220	2220	2220	
5°	2220	2212	2188	2205	2201	211
15°	2113	2100	2073	2081	2071	595
25°	1913	1896	1859	1863	1859	880
35°	1650	1629	1594	1582	1571	1030
45°	1343	1328	1296	1272	1264	1036
55°	1016	1003	978	952	941	908
65°	685	672	651	632	621	678
75°	358	354	344	331	335	383
85°	87	85	83	77	75	103
90°	0	0	0	0	0	

TEST NUMBER: P930967

CATALOG NUMBER: DFN2DS-SQ3F0-070DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2219.8	2219.8	2219.8	2219.8	2219.8
2.5°	2232.8	2222.1	2198.5	2219.8	2215.7
5°	2219.8	2211.5	2187.9	2204.9	2200.8
7.5°	2204.9	2192.2	2168.6	2185.9	2181.6
10°	2181.6	2166.6	2141.0	2158.0	2151.7
12.5°	2149.4	2136.8	2111.2	2121.8	2117.5
15°	2113.2	2100.5	2072.6	2081.3	2070.6
17.5°	2068.3	2055.7	2027.8	2038.5	2027.8
20°	2019.2	2006.5	1976.6	1983.0	1974.6
22.5°	1970.3	1951.0	1923.2	1923.2	1918.8
25°	1912.6	1895.5	1859.3	1863.4	1859.3
27.5°	1848.4	1833.5	1805.9	1799.5	1788.8
30°	1784.6	1767.3	1735.5	1729.1	1720.5
32.5°	1716.1	1703.5	1669.3	1656.4	1647.8
35°	1650.0	1628.8	1594.5	1581.7	1571.0
37.5°	1575.3	1556.1	1521.8	1506.9	1496.3
40°	1498.5	1481.3	1447.1	1428.1	1419.5
42.5°	1423.8	1406.6	1372.6	1351.1	1338.4
45°	1342.7	1327.8	1295.6	1272.3	1263.7
47.5°	1263.7	1248.7	1214.5	1191.0	1178.3
50°	1180.4	1169.7	1139.8	1109.9	1099.3
52.5°	1099.3	1084.4	1056.7	1033.2	1018.2
55°	1016.1	1003.3	977.7	952.1	941.4
57.5°	932.8	922.2	894.3	868.7	860.2
60°	849.5	841.1	811.3	787.7	781.3
62.5°	768.4	753.5	732.2	710.9	702.3
65°	685.3	672.4	651.1	631.9	621.2
67.5°	599.9	589.1	570.0	555.1	546.5
70°	520.9	512.3	493.0	478.1	469.7
72.5°	439.8	431.2	420.5	405.6	399.3
75°	358.5	354.4	343.5	330.9	335.2
77.5°	286.1	277.4	273.1	266.7	260.5
80°	213.5	211.3	207.0	200.7	196.3
82.5°	145.2	145.2	143.1	134.6	134.6
85°	87.4	85.4	83.4	76.8	74.7
87.5°	38.5	34.2	29.9	23.6	21.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930967

CATALOG NUMBER: DFN2DS-SQ3F0-070DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.53	16.14	14.89	16.45	16.77	14.08	15.69	14.45	16.01	16.32
	3H	16.28	17.73	16.65	18.06	18.42	15.79	17.24	16.16	17.57	17.93
	4H	16.92	18.29	17.32	18.64	19.02	16.43	17.80	16.83	18.14	18.52
	6H	17.39	18.66	17.80	19.02	19.42	16.89	18.16	17.30	18.52	18.91
	8H	17.53	18.75	17.96	19.13	19.53	17.03	18.24	17.46	18.63	19.03
	12H	17.63	18.79	18.05	19.17	19.60	17.11	18.27	17.54	18.65	19.08
4H	2H	15.09	16.46	15.48	16.80	17.18	14.73	16.10	15.13	16.45	16.83
	3H	17.06	18.21	17.47	18.61	19.01	16.65	17.80	17.06	18.20	18.60
	4H	17.84	18.87	18.27	19.29	19.72	17.41	18.45	17.85	18.86	19.30
	6H	18.43	19.34	18.89	19.78	20.24	18.00	18.91	18.46	19.35	19.80
	8H	18.62	19.47	19.08	19.91	20.38	18.19	19.03	18.65	19.48	19.94
	12H	18.76	19.52	19.24	19.99	20.46	18.30	19.06	18.78	19.54	20.01
8H	4H	18.11	18.96	18.57	19.40	19.87	17.74	18.58	18.20	19.03	19.49
	6H	18.83	19.53	19.32	20.02	20.49	18.44	19.15	18.94	19.64	20.11
	8H	19.08	19.72	19.59	20.22	20.71	18.69	19.32	19.20	19.83	20.32
	12H	19.28	19.84	19.79	20.33	20.89	18.87	19.43	19.38	19.92	20.48
12H	4H	18.14	18.90	18.62	19.37	19.84	17.77	18.53	18.25	19.01	19.48
	6H	18.87	19.50	19.38	20.01	20.50	18.50	19.13	19.01	19.64	20.13
	8H	19.19	19.74	19.69	20.23	20.79	18.81	19.37	19.31	19.86	20.42