

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930985

Luminaire Tested: DFN2DS-SQ3F0-080DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930985
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-080DS930-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6454.8 lumens
Efficiency: N/A
Efficacy: 78.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 82
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930985

CATALOG NUMBER: DFN2DS-SQ3F0-080DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930985

CATALOG NUMBER: DFN2DS-SQ3F0-080DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2907	2907	2907
5°	2918	2876	2893
10°	2901	2847	2861
15°	2865	2810	2807
20°	2814	2754	2752
25°	2763	2686	2686
30°	2698	2624	2602
35°	2638	2549	2511
40°	2562	2474	2427
45°	2487	2399	2340
50°	2405	2322	2239
55°	2320	2232	2149
60°	2225	2125	2046
65°	2123	2017	1925
70°	1994	1888	1798
75°	1814	1738	1696
80°	1611	1561	1481
85°	1313	1253	1123

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2487 cd/sqm

TEST NUMBER: P930985

CATALOG NUMBER: DFN2DS-SQ3F0-080DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.8	3.7
10°-20°	671.8	10.4
20°-30°	987.3	15.3
30°-40°	1146.7	17.8
40°-50°	1145.3	17.7
50°-60°	998.7	15.5
60°-70°	738.2	11.4
70°-80°	417.7	6.5
80°-90°	110.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1898.0	29.4
0°-40°	3044.7	47.2
0°-60°	5188.6	80.4
0°-90°	6454.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6454.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2537	2537	2537	2537	2537	
5°	2537	2527	2500	2520	2515	241
15°	2415	2401	2369	2379	2366	680
25°	2186	2166	2125	2130	2125	1006
35°	1886	1862	1822	1808	1795	1178
45°	1535	1517	1481	1454	1444	1184
55°	1161	1146	1117	1088	1076	1038
65°	783	768	744	722	710	774
75°	410	405	393	378	383	437
85°	100	98	95	88	85	117
90°	0	0	0	0	0	

TEST NUMBER: P930985

CATALOG NUMBER: DFN2DS-SQ3F0-080DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2536.9	2536.9	2536.9	2536.9	2536.9
2.5°	2551.7	2539.5	2512.6	2536.9	2532.3
5°	2536.9	2527.4	2500.5	2519.9	2515.3
7.5°	2519.9	2505.4	2478.5	2498.1	2493.2
10°	2493.2	2476.1	2446.9	2466.3	2459.1
12.5°	2456.5	2442.0	2412.7	2424.9	2420.0
15°	2415.1	2400.6	2368.7	2378.6	2366.4
17.5°	2363.8	2349.3	2317.5	2329.7	2317.5
20°	2307.7	2293.2	2259.0	2266.3	2256.7
22.5°	2251.8	2229.8	2197.9	2197.9	2193.0
25°	2185.7	2166.4	2124.9	2129.6	2124.9
27.5°	2112.5	2095.4	2063.8	2056.6	2044.4
30°	2039.5	2019.8	1983.4	1976.1	1966.3
32.5°	1961.4	1946.9	1907.8	1893.0	1883.2
35°	1885.7	1861.5	1822.3	1807.6	1795.4
37.5°	1800.3	1778.3	1739.3	1722.2	1710.0
40°	1712.6	1692.9	1653.9	1632.1	1622.3
42.5°	1627.2	1607.5	1568.7	1544.1	1529.7
45°	1534.6	1517.4	1480.7	1454.0	1444.3
47.5°	1444.3	1427.1	1388.0	1361.1	1346.6
50°	1349.0	1336.8	1302.6	1268.5	1256.3
52.5°	1256.3	1239.2	1207.7	1180.8	1163.7
55°	1161.3	1146.5	1117.4	1088.1	1075.9
57.5°	1066.1	1054.0	1022.1	992.8	983.0
60°	970.8	961.3	927.1	900.2	892.9
62.5°	878.2	861.1	836.8	812.5	802.6
65°	783.2	768.5	744.1	722.1	709.9
67.5°	685.6	673.2	651.4	634.4	624.5
70°	595.3	585.4	563.5	546.4	536.8
72.5°	502.6	492.8	480.6	463.6	456.3
75°	409.7	405.1	392.7	378.2	383.0
77.5°	326.9	317.0	312.1	304.9	297.6
80°	244.1	241.5	236.6	229.3	224.4
82.5°	165.9	165.9	163.6	153.7	153.7
85°	99.9	97.6	95.3	87.8	85.4
87.5°	44.0	39.1	34.1	26.9	24.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930985

CATALOG NUMBER: DFN2DS-SQ3F0-080DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.99	16.60	15.36	16.92	17.23	14.55	16.16	14.91	16.47	16.78
	3H	16.74	18.19	17.12	18.52	18.88	16.25	17.70	16.63	18.03	18.39
	4H	17.39	18.76	17.78	19.10	19.48	16.89	18.26	17.29	18.61	18.98
	6H	17.86	19.12	18.27	19.49	19.88	17.35	18.62	17.77	18.99	19.38
	8H	18.00	19.21	18.42	19.60	20.00	17.50	18.71	17.92	19.10	19.49
	12H	18.09	19.25	18.52	19.63	20.06	17.58	18.74	18.01	19.12	19.55
4H	2H	15.55	16.92	15.95	17.27	17.64	15.20	16.57	15.60	16.91	17.29
	3H	17.53	18.67	17.94	19.07	19.47	17.12	18.26	17.53	18.66	19.06
	4H	18.30	19.34	18.73	19.75	20.19	17.88	18.91	18.31	19.33	19.76
	6H	18.90	19.80	19.35	20.24	20.70	18.47	19.37	18.92	19.81	20.27
	8H	19.09	19.93	19.55	20.38	20.84	18.65	19.50	19.11	19.94	20.40
	12H	19.22	19.98	19.70	20.46	20.93	18.77	19.53	19.25	20.00	20.47
8H	4H	18.58	19.42	19.04	19.86	20.33	18.20	19.05	18.66	19.49	19.96
	6H	19.29	19.99	19.78	20.48	20.96	18.91	19.61	19.40	20.10	20.57
	8H	19.55	20.18	20.06	20.69	21.17	19.16	19.79	19.67	20.29	20.78
	12H	19.75	20.31	20.26	20.80	21.36	19.34	19.89	19.84	20.38	20.95
12H	4H	18.60	19.36	19.08	19.84	20.31	18.24	19.00	18.72	19.47	19.94
	6H	19.33	19.97	19.84	20.47	20.96	18.97	19.60	19.48	20.11	20.59
	8H	19.65	20.21	20.16	20.70	21.26	19.27	19.83	19.78	20.32	20.88