

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931004

Luminaire Tested: DFN2DS-SQ3F0-090DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931004
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-090DS930-RLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6234.7 lumens
Efficiency: N/A
Efficacy: 66.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 93.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931004

CATALOG NUMBER: DFN2DS-SQ3F0-090DS930-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931004

CATALOG NUMBER: DFN2DS-SQ3F0-090DS930-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92	90	88	86
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82	79	76	74
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74	69	66	64
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66	62	57	55
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60	55	51	49
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55	50	45	43
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51	45	41	39
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47	41	37	35
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44	38	34	32
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3474	3474	3474
5°	3487	3430	3449
10°	3460	3374	3345
15°	3420	3274	3180
20°	3365	3131	2974
25°	3309	2969	2775
30°	3231	2802	2519
35°	3155	2621	2295
40°	3078	2433	2035
45°	2988	2223	1800
50°	2895	2010	1570
55°	2800	1781	1348
60°	2691	1540	1119
65°	2566	1294	1019
70°	2417	1066	937
75°	2234	972	875
80°	1972	868	797
85°	1549	685	685

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2988 cd/sqm

TEST NUMBER: P931004

CATALOG NUMBER: DFN2DS-SQ3F0-090DS930-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.1	4.6
10°-20°	780.0	12.5
20°-30°	1095.0	17.6
30°-40°	1193.7	19.1
40°-50°	1097.1	17.6
50°-60°	861.6	13.8
60°-70°	560.8	9.0
70°-80°	288.7	4.6
80°-90°	73.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2159.1	34.6
0°-40°	3352.8	53.8
0°-60°	5311.5	85.2
0°-90°	6234.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6234.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3032	3032	3032	3032	3032	
5°	3032	3018	2982	3007	2999	287
15°	2883	2853	2760	2708	2680	813
25°	2617	2529	2348	2236	2195	1204
35°	2255	2115	1874	1701	1640	1412
45°	1844	1660	1372	1177	1111	1424
55°	1402	1188	892	727	675	1253
65°	946	724	477	384	376	938
75°	505	313	220	200	198	534
85°	118	60	52	52	52	141
90°	0	0	0	0	0	

TEST NUMBER: P931004

CATALOG NUMBER: DFN2DS-SQ3F0-090DS930-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3031.6	3031.6	3031.6	3031.6	3031.6
2.5°	3045.2	3031.6	3001.2	3028.9	3023.4
5°	3031.6	3017.9	2982.1	3006.8	2998.6
7.5°	3006.8	2990.5	2952.1	2962.9	2949.2
10°	2973.9	2954.7	2900.0	2891.5	2875.2
12.5°	2932.9	2908.2	2833.9	2817.6	2787.3
15°	2883.4	2853.2	2760.0	2707.8	2680.5
17.5°	2825.8	2781.8	2666.5	2606.3	2562.4
20°	2760.0	2705.0	2567.8	2499.4	2438.9
22.5°	2688.7	2625.5	2466.3	2373.1	2332.1
25°	2617.4	2529.4	2348.4	2236.0	2194.7
27.5°	2532.4	2438.9	2238.6	2109.7	2046.5
30°	2441.8	2337.3	2117.9	1978.2	1903.9
32.5°	2353.9	2227.6	2002.9	1838.2	1769.4
35°	2255.3	2115.3	1873.9	1701.1	1640.5
37.5°	2159.2	2008.2	1753.1	1563.7	1495.3
40°	2057.6	1893.2	1626.8	1432.1	1360.8
42.5°	1953.4	1777.9	1500.7	1297.6	1229.2
45°	1843.7	1659.7	1371.8	1176.8	1111.0
47.5°	1739.5	1544.8	1248.4	1053.4	993.2
50°	1624.2	1429.4	1127.6	938.1	880.8
52.5°	1511.6	1305.8	1012.4	831.3	779.2
55°	1401.8	1187.9	891.5	727.1	675.0
57.5°	1289.5	1070.0	784.8	631.1	587.1
60°	1174.2	954.7	672.1	532.4	488.4
62.5°	1061.9	842.4	576.0	444.5	422.7
65°	946.5	724.2	477.3	384.2	375.8
67.5°	836.8	614.4	384.2	337.3	329.2
70°	721.6	507.7	318.2	290.8	279.7
72.5°	611.8	408.6	266.0	244.2	238.7
75°	504.7	312.6	219.5	200.2	197.6
77.5°	397.9	222.1	172.9	161.9	156.3
80°	298.9	159.3	131.5	120.8	120.8
82.5°	208.4	107.1	90.5	85.0	85.0
85°	117.8	60.2	52.1	52.1	52.1
87.5°	43.9	21.8	21.8	19.2	19.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931004

CATALOG NUMBER: DFN2DS-SQ3F0-090DS930-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.56	17.08	15.93	17.40	17.71	11.52	13.04	11.89	13.36	13.67
	3H	17.33	18.69	17.70	19.02	19.38	12.79	14.15	13.16	14.48	14.84
	4H	17.99	19.27	18.39	19.62	20.00	13.29	14.57	13.69	14.92	15.30
	6H	18.48	19.66	18.89	20.03	20.42	13.67	14.85	14.08	15.22	15.61
	8H	18.65	19.77	19.07	20.16	20.56	13.79	14.92	14.22	15.31	15.71
	12H	18.75	19.83	19.18	20.21	20.64	13.88	14.95	14.31	15.34	15.76
4H	2H	15.66	16.95	16.06	17.29	17.67	12.22	13.50	12.62	13.85	14.22
	3H	17.60	18.66	18.01	19.06	19.46	13.66	14.72	14.07	15.12	15.52
	4H	18.35	19.30	18.78	19.72	20.16	14.26	15.22	14.69	15.63	16.07
	6H	18.94	19.77	19.40	20.21	20.67	14.75	15.58	15.20	16.02	16.48
	8H	19.15	19.93	19.62	20.38	20.84	14.91	15.69	15.37	16.13	16.60
	12H	19.31	20.00	19.79	20.48	20.95	15.03	15.72	15.51	16.20	16.67
8H	4H	18.37	19.15	18.83	19.59	20.06	14.61	15.39	15.08	15.83	16.30
	6H	19.01	19.65	19.51	20.14	20.62	15.20	15.84	15.70	16.33	16.81
	8H	19.26	19.84	19.77	20.35	20.83	15.42	16.00	15.93	16.51	17.00
	12H	19.46	19.97	19.97	20.47	21.03	15.60	16.11	16.11	16.60	17.17
12H	4H	18.36	19.05	18.84	19.53	20.00	14.66	15.35	15.14	15.83	16.30
	6H	18.99	19.57	19.50	20.08	20.57	15.26	15.84	15.78	16.35	16.84
	8H	19.27	19.78	19.78	20.28	20.84	15.54	16.05	16.05	16.54	17.10