

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930915

Luminaire Tested: DFN2DS-SQ3F0-040DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-040DS935-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3405.6 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 38.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930915

CATALOG NUMBER: DFN2DS-SQ3F0-040DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930915

CATALOG NUMBER: DFN2DS-SQ3F0-040DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1534	1534	1534
5°	1540	1517	1526
10°	1531	1502	1509
15°	1511	1483	1481
20°	1485	1453	1452
25°	1458	1417	1417
30°	1424	1384	1373
35°	1392	1345	1325
40°	1352	1305	1280
45°	1312	1266	1235
50°	1269	1225	1181
55°	1224	1178	1134
60°	1174	1121	1080
65°	1120	1064	1016
70°	1052	996	949
75°	957	917	895
80°	849	823	781
85°	693	660	593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1312 cd/sqm

TEST NUMBER: P930915

CATALOG NUMBER: DFN2DS-SQ3F0-040DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.0	3.7
10°-20°	354.5	10.4
20°-30°	520.9	15.3
30°-40°	605.0	17.8
40°-50°	604.3	17.7
50°-60°	526.9	15.5
60°-70°	389.5	11.4
70°-80°	220.4	6.5
80°-90°	58.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1001.4	29.4
0°-40°	1606.4	47.2
0°-60°	2737.6	80.4
0°-90°	3405.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3405.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1338	1338	1338	1338	1338	
5°	1338	1333	1319	1330	1327	127
15°	1274	1266	1250	1255	1248	359
25°	1153	1143	1121	1124	1121	531
35°	995	982	962	954	947	621
45°	810	801	781	767	762	625
55°	613	605	590	574	568	548
65°	413	405	393	381	375	409
75°	216	214	207	200	202	231
85°	53	52	50	46	45	62
90°	0	0	0	0	0	

TEST NUMBER: P930915

CATALOG NUMBER: DFN2DS-SQ3F0-040DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1338.5	1338.5	1338.5	1338.5	1338.5
2.5°	1346.3	1339.9	1325.7	1338.5	1336.1
5°	1338.5	1333.4	1319.2	1329.5	1327.1
7.5°	1329.5	1321.8	1307.6	1318.0	1315.5
10°	1315.5	1306.4	1291.0	1301.3	1297.4
12.5°	1296.0	1288.4	1273.0	1279.4	1276.8
15°	1274.2	1266.5	1249.8	1254.9	1248.5
17.5°	1247.2	1239.5	1222.7	1229.1	1222.7
20°	1217.5	1209.8	1191.9	1195.7	1190.7
22.5°	1188.0	1176.4	1159.6	1159.6	1157.0
25°	1153.2	1142.9	1121.1	1123.6	1121.1
27.5°	1114.6	1105.5	1088.9	1085.1	1078.7
30°	1076.0	1065.7	1046.4	1042.6	1037.4
32.5°	1034.8	1027.2	1006.5	998.8	993.6
35°	994.9	982.1	961.5	953.7	947.3
37.5°	949.9	938.3	917.6	908.7	902.2
40°	903.6	893.2	872.6	861.1	856.0
42.5°	858.5	848.1	827.7	814.7	807.0
45°	809.6	800.7	781.2	767.2	762.0
47.5°	762.0	752.9	732.4	718.2	710.5
50°	711.7	705.3	687.3	669.3	662.8
52.5°	662.8	653.9	637.2	623.0	614.0
55°	612.8	604.9	589.5	574.0	567.7
57.5°	562.4	556.1	539.2	523.8	518.7
60°	512.2	507.1	489.2	475.0	471.1
62.5°	463.4	454.3	441.5	428.6	423.5
65°	413.2	405.4	392.6	381.0	374.6
67.5°	361.7	355.2	343.7	334.7	329.6
70°	314.1	308.9	297.3	288.3	283.2
72.5°	265.2	260.0	253.6	244.6	240.7
75°	216.2	213.7	207.2	199.5	202.1
77.5°	172.4	167.3	164.7	160.8	157.0
80°	128.7	127.4	124.8	121.0	118.4
82.5°	87.5	87.5	86.3	81.1	81.1
85°	52.7	51.5	50.2	46.3	45.1
87.5°	23.2	20.6	18.1	14.2	12.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930915

CATALOG NUMBER: DFN2DS-SQ3F0-040DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.77	14.38	13.13	14.69	15.01	12.32	13.93	12.69	14.25	14.56
	3H	14.52	15.97	14.90	16.30	16.66	14.03	15.48	14.40	15.81	16.17
	4H	15.16	16.53	15.56	16.88	17.26	14.67	16.04	15.07	16.39	16.76
	6H	15.63	16.90	16.04	17.27	17.66	15.13	16.40	15.54	16.77	17.16
	8H	15.78	16.99	16.20	17.38	17.78	15.27	16.48	15.70	16.87	17.27
	12H	15.87	17.03	16.30	17.41	17.84	15.36	16.52	15.78	16.90	17.33
4H	2H	13.33	14.70	13.73	15.05	15.42	12.98	14.35	13.37	14.69	15.07
	3H	15.30	16.45	15.71	16.85	17.25	14.90	16.04	15.31	16.44	16.84
	4H	16.08	17.12	16.51	17.53	17.97	15.66	16.69	16.09	17.11	17.54
	6H	16.68	17.58	17.13	18.02	18.48	16.24	17.15	16.70	17.59	18.05
	8H	16.87	17.71	17.33	18.16	18.62	16.43	17.27	16.89	17.72	18.18
	12H	17.00	17.76	17.48	18.23	18.70	16.55	17.31	17.03	17.78	18.25
8H	4H	16.35	17.20	16.81	17.64	18.11	15.98	16.83	16.44	17.27	17.73
	6H	17.07	17.77	17.56	18.26	18.73	16.69	17.39	17.18	17.88	18.35
	8H	17.33	17.96	17.84	18.46	18.95	16.94	17.57	17.45	18.07	18.56
	12H	17.53	18.08	18.03	18.58	19.14	17.11	17.67	17.62	18.16	18.72
12H	4H	16.38	17.14	16.86	17.62	18.09	16.02	16.78	16.50	17.25	17.72
	6H	17.11	17.75	17.62	18.25	18.74	16.74	17.38	17.25	17.88	18.37
	8H	17.43	17.98	17.93	18.48	19.04	17.05	17.61	17.56	18.10	18.66