

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333893

Luminaire Tested: **S122RDS-S865D840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333893
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-24)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDS-S865D840-4F0-1E-UDD-F
Description: DEFINE 2 REGRESSED DIRECT LED LUMINAIRE, FLUSH SATIN WHITE DIFFUSER
PENDANT/SURFACE/WALL MOUNT, 865 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2926.7 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 34.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333893

CATALOG NUMBER: S122RDS-S865D840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333893

CATALOG NUMBER: S122RDS-S865D840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88					86				
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76					74				
3	93	83	76	70	90	82	75	69	79	73	68	76	71	67	74	69	66					64				
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	62	57					55				
5	79	67	59	53	77	66	58	52	64	57	52	62	56	51	60	55	51					49				
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45					43				
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41					39				
8	64	51	43	38	62	51	43	37	49	42	37	48	42	37	47	41	37					35				
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	44	38	34					32				
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31					29				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22976	22976	22976
5°	23063	22689	22814
10°	22887	22317	22127
15°	22624	21656	21031
20°	22261	20711	19672
25°	21887	19639	18355
30°	21369	18535	16662
35°	20865	17337	15179
40°	20358	16096	13464
45°	19760	14703	11910
50°	19150	13295	10384
55°	18525	11781	8918
60°	17799	10188	7401
65°	16974	8562	6739
70°	15989	7053	6203
75°	14785	6425	5783
80°	13054	5746	5272
85°	10263	4539	4539



TEST NUMBER: P333893

CATALOG NUMBER: S122RDS-S865D840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.4	4.6
10°-20°	366.1	12.5
20°-30°	514.0	17.6
30°-40°	560.3	19.1
40°-50°	515.0	17.6
50°-60°	404.4	13.8
60°-70°	263.3	9.0
70°-80°	135.5	4.6
80°-90°	34.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1013.5	34.6
0°-40°	1573.9	53.8
0°-60°	2493.3	85.2
0°-90°	2926.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2926.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1423	1423	1423	1423	1423	
5°	1423	1417	1400	1412	1408	135
15°	1354	1339	1296	1271	1258	381
25°	1229	1187	1102	1050	1030	565
35°	1059	993	880	798	770	663
45°	865	779	644	552	522	668
55°	658	558	418	341	317	588
65°	444	340	224	180	176	440
75°	237	147	103	94	93	251
85°	55	28	24	24	24	66
90°	0	0	0	0	0	



TEST NUMBER: P333893

CATALOG NUMBER: S122RDS-S865D840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1423.0	1423.0	1423.0	1423.0	1423.0
2.5°	1429.5	1423.0	1408.9	1421.8	1419.2
5°	1423.0	1416.6	1399.9	1411.5	1407.6
7.5°	1411.5	1403.7	1385.7	1390.8	1384.4
10°	1396.0	1387.0	1361.2	1357.4	1349.6
12.5°	1376.7	1365.1	1330.3	1322.6	1308.4
15°	1353.5	1339.3	1295.6	1271.1	1258.2
17.5°	1326.5	1305.9	1251.8	1223.4	1202.8
20°	1295.6	1269.8	1205.4	1173.2	1144.9
22.5°	1262.1	1232.4	1157.8	1114.0	1094.7
25°	1228.6	1187.4	1102.4	1049.6	1030.3
27.5°	1188.7	1144.9	1050.9	990.3	960.7
30°	1146.2	1097.2	994.2	928.5	893.7
32.5°	1105.0	1045.7	940.1	862.8	830.6
35°	1058.6	992.9	879.6	798.5	770.1
37.5°	1013.5	942.7	822.9	734.1	701.9
40°	965.9	888.6	763.7	672.2	638.8
42.5°	916.9	834.5	704.4	609.1	576.9
45°	865.4	779.1	643.9	552.5	521.6
47.5°	816.5	725.0	586.0	494.5	466.2
50°	762.4	671.0	529.3	440.4	413.4
52.5°	709.6	613.0	475.2	390.2	365.7
55°	658.1	557.6	418.5	341.3	316.8
57.5°	605.3	502.3	368.3	296.2	275.6
60°	551.2	448.2	315.5	249.8	229.2
62.5°	498.4	395.4	270.4	208.6	198.3
65°	444.3	340.0	224.1	180.3	176.4
67.5°	392.8	288.5	180.3	158.4	154.5
70°	338.7	238.2	149.4	136.5	131.4
72.5°	287.2	191.9	124.9	114.6	112.0
75°	237.0	146.8	103.0	94.0	92.7
77.5°	186.7	104.3	81.1	76.0	73.4
80°	140.4	74.7	61.8	56.7	56.7
82.5°	97.9	50.2	42.5	39.9	39.9
85°	55.4	28.3	24.5	24.5	24.5
87.5°	20.6	10.3	10.3	9.0	9.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)