

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930953

Luminaire Tested: DFN2DS-SQ3F0-060DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930953
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-060DS940-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5298.4 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 59.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930953

CATALOG NUMBER: DFN2DS-SQ3F0-060DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930953

CATALOG NUMBER: DFN2DS-SQ3F0-060DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2386	2386	2386
5°	2395	2361	2375
10°	2381	2337	2348
15°	2352	2306	2304
20°	2310	2261	2259
25°	2268	2205	2205
30°	2215	2154	2135
35°	2165	2092	2061
40°	2103	2031	1992
45°	2041	1969	1921
50°	1974	1906	1838
55°	1904	1832	1764
60°	1826	1744	1680
65°	1743	1656	1580
70°	1637	1549	1476
75°	1489	1427	1392
80°	1322	1281	1215
85°	1078	1027	922

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2041 cd/sqm

TEST NUMBER: P930953

CATALOG NUMBER: DFN2DS-SQ3F0-060DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.0	3.7
10°-20°	551.5	10.4
20°-30°	810.5	15.3
30°-40°	941.3	17.8
40°-50°	940.1	17.7
50°-60°	819.8	15.5
60°-70°	606.0	11.4
70°-80°	342.9	6.5
80°-90°	90.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1558.0	29.4
0°-40°	2499.3	47.2
0°-60°	4259.1	80.4
0°-90°	5298.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5298.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2082	2082	2082	2082	2082	
5°	2082	2075	2052	2068	2065	198
15°	1982	1970	1944	1952	1942	558
25°	1794	1778	1744	1748	1744	826
35°	1548	1528	1496	1484	1474	967
45°	1260	1246	1215	1194	1186	972
55°	953	941	917	893	883	852
65°	643	631	611	593	583	636
75°	336	332	322	310	314	359
85°	82	80	78	72	70	96
90°	0	0	0	0	0	



TEST NUMBER: P930953

CATALOG NUMBER: DFN2DS-SQ3F0-060DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2082.5	2082.5	2082.5	2082.5	2082.5
2.5°	2094.6	2084.6	2062.5	2082.5	2078.6
5°	2082.5	2074.6	2052.5	2068.5	2064.6
7.5°	2068.5	2056.6	2034.5	2050.6	2046.6
10°	2046.6	2032.6	2008.5	2024.5	2018.5
12.5°	2016.5	2004.5	1980.5	1990.5	1986.5
15°	1982.4	1970.5	1944.4	1952.5	1942.5
17.5°	1940.4	1928.5	1902.4	1912.3	1902.4
20°	1894.3	1882.4	1854.3	1860.3	1852.4
22.5°	1848.4	1830.3	1804.2	1804.2	1800.1
25°	1794.2	1778.3	1744.2	1748.1	1744.2
27.5°	1734.0	1720.0	1694.1	1688.2	1678.2
30°	1674.2	1658.0	1628.1	1622.1	1614.0
32.5°	1610.0	1598.1	1566.0	1553.9	1545.8
35°	1548.0	1528.0	1495.9	1483.8	1473.8
37.5°	1477.9	1459.8	1427.7	1413.6	1403.7
40°	1405.8	1389.6	1357.6	1339.8	1331.7
42.5°	1335.7	1319.5	1287.7	1267.5	1255.6
45°	1259.7	1245.6	1215.4	1193.6	1185.5
47.5°	1185.5	1171.5	1139.4	1117.3	1105.4
50°	1107.3	1097.3	1069.3	1041.2	1031.2
52.5°	1031.2	1017.2	991.3	969.2	955.2
55°	953.3	941.1	917.2	893.2	883.2
57.5°	875.1	865.2	839.0	815.0	806.9
60°	796.9	789.1	761.1	738.9	733.0
62.5°	720.8	706.8	686.8	666.9	658.8
65°	642.9	630.8	610.8	592.7	582.7
67.5°	562.8	552.6	534.8	520.7	512.6
70°	488.6	480.6	462.5	448.5	440.6
72.5°	412.6	404.5	394.5	380.5	374.6
75°	336.3	332.5	322.3	310.4	314.4
77.5°	268.3	260.3	256.2	250.3	244.3
80°	200.3	198.2	194.2	188.2	184.2
82.5°	136.2	136.2	134.2	126.2	126.2
85°	82.0	80.1	78.1	72.0	70.1
87.5°	36.1	32.1	28.0	22.1	20.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930953

CATALOG NUMBER: DFN2DS-SQ3F0-060DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.30	15.92	14.67	16.23	16.54	13.86	15.47	14.22	15.78	16.10
	3H	16.05	17.51	16.43	17.84	18.20	15.56	17.02	15.94	17.34	17.70
	4H	16.70	18.07	17.10	18.42	18.79	16.21	17.57	16.60	17.92	18.30
	6H	17.17	18.44	17.58	18.80	19.19	16.67	17.94	17.08	18.30	18.69
	8H	17.31	18.52	17.74	18.91	19.31	16.81	18.02	17.23	18.41	18.81
	12H	17.40	18.56	17.83	18.94	19.37	16.89	18.05	17.32	18.43	18.86
4H	2H	14.86	16.23	15.26	16.58	16.96	14.51	15.88	14.91	16.23	16.60
	3H	16.84	17.99	17.25	18.38	18.78	16.43	17.58	16.84	17.98	18.38
	4H	17.62	18.65	18.05	19.07	19.50	17.19	18.23	17.62	18.64	19.08
	6H	18.21	19.12	18.67	19.56	20.01	17.78	18.68	18.23	19.13	19.58
	8H	18.40	19.25	18.86	19.69	20.16	17.96	18.81	18.42	19.25	19.72
	12H	18.53	19.29	19.01	19.77	20.24	18.08	18.84	18.56	19.32	19.79
8H	4H	17.89	18.74	18.35	19.18	19.64	17.52	18.36	17.98	18.80	19.27
	6H	18.60	19.31	19.10	19.80	20.27	18.22	18.93	18.72	19.41	19.89
	8H	18.86	19.49	19.37	20.00	20.49	18.47	19.10	18.98	19.61	20.09
	12H	19.06	19.62	19.57	20.11	20.67	18.65	19.21	19.16	19.70	20.26
12H	4H	17.92	18.68	18.40	19.15	19.62	17.55	18.31	18.03	18.79	19.26
	6H	18.65	19.28	19.16	19.79	20.27	18.28	18.91	18.79	19.42	19.91
	8H	18.96	19.52	19.47	20.01	20.57	18.58	19.14	19.09	19.63	20.19