

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930971

Luminaire Tested: DFN2DS-SQ3F0-070DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930971
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-070DS940-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6181.6 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 71.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930971

CATALOG NUMBER: DFN2DS-SQ3F0-070DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930971

CATALOG NUMBER: DFN2DS-SQ3F0-070DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2784	2784	2784
5°	2794	2754	2771
10°	2778	2726	2740
15°	2744	2691	2688
20°	2695	2638	2635
25°	2646	2573	2573
30°	2584	2513	2491
35°	2526	2441	2405
40°	2453	2369	2324
45°	2381	2298	2241
50°	2303	2224	2145
55°	2222	2137	2058
60°	2131	2035	1960
65°	2034	1932	1843
70°	1910	1808	1722
75°	1737	1665	1624
80°	1542	1495	1418
85°	1258	1200	1075

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2381 cd/sqm

TEST NUMBER: P930971

CATALOG NUMBER: DFN2DS-SQ3F0-070DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.7	3.7
10°-20°	643.4	10.4
20°-30°	945.5	15.3
30°-40°	1098.2	17.8
40°-50°	1096.8	17.7
50°-60°	956.4	15.5
60°-70°	707.0	11.4
70°-80°	400.0	6.5
80°-90°	105.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1817.6	29.4
0°-40°	2915.8	47.2
0°-60°	4969.0	80.4
0°-90°	6181.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6181.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2430	2430	2430	2430	2430	
5°	2430	2420	2395	2413	2409	231
15°	2313	2299	2268	2278	2266	651
25°	2093	2075	2035	2040	2035	963
35°	1806	1783	1745	1731	1719	1128
45°	1470	1453	1418	1392	1383	1134
55°	1112	1098	1070	1042	1030	994
65°	750	736	713	692	680	742
75°	392	388	376	362	367	419
85°	96	94	91	84	82	112
90°	0	0	0	0	0	

TEST NUMBER: P930971

CATALOG NUMBER: DFN2DS-SQ3F0-070DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2429.5	2429.5	2429.5	2429.5	2429.5
2.5°	2443.7	2432.0	2406.3	2429.5	2425.1
5°	2429.5	2420.4	2394.7	2413.2	2408.8
7.5°	2413.2	2399.3	2373.5	2392.4	2387.7
10°	2387.7	2371.3	2343.3	2361.9	2355.0
12.5°	2352.5	2338.6	2310.6	2322.2	2317.5
15°	2312.9	2299.0	2268.4	2277.9	2266.2
17.5°	2263.7	2249.9	2219.4	2231.1	2219.4
20°	2209.9	2196.1	2163.4	2170.3	2161.1
22.5°	2156.4	2135.4	2104.9	2104.9	2100.1
25°	2093.3	2074.6	2035.0	2039.5	2035.0
27.5°	2023.1	2006.7	1976.5	1969.5	1957.9
30°	1953.2	1934.3	1899.4	1892.5	1883.0
32.5°	1878.3	1864.5	1827.0	1812.9	1803.4
35°	1805.9	1782.7	1745.2	1731.1	1719.4
37.5°	1724.1	1703.1	1665.6	1649.3	1637.6
40°	1640.1	1621.3	1583.8	1563.1	1553.6
42.5°	1558.3	1539.5	1502.3	1478.8	1464.8
45°	1469.6	1453.2	1418.0	1392.5	1383.0
47.5°	1383.0	1366.7	1329.3	1303.5	1289.7
50°	1291.9	1280.2	1247.5	1214.8	1203.1
52.5°	1203.1	1186.8	1156.6	1130.8	1114.4
55°	1112.1	1098.1	1070.0	1042.0	1030.3
57.5°	1021.0	1009.3	978.8	950.8	941.4
60°	929.7	920.5	887.9	862.1	855.2
62.5°	841.0	824.7	801.4	778.1	768.6
65°	750.1	735.9	712.6	691.6	679.9
67.5°	656.6	644.7	623.9	607.5	598.1
70°	570.1	560.7	539.6	523.2	514.1
72.5°	481.3	472.0	460.3	443.9	437.0
75°	392.4	387.9	376.0	362.2	366.9
77.5°	313.1	303.6	298.9	292.0	285.1
80°	233.7	231.3	226.6	219.6	214.9
82.5°	158.9	158.9	156.6	147.3	147.3
85°	95.7	93.5	91.3	84.0	81.8
87.5°	42.1	37.5	32.7	25.8	23.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930971

CATALOG NUMBER: DFN2DS-SQ3F0-070DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.84	16.45	15.20	16.76	17.08	14.40	16.01	14.76	16.32	16.63
	3H	16.59	18.04	16.97	18.37	18.73	16.10	17.55	16.48	17.88	18.24
	4H	17.24	18.61	17.63	18.95	19.33	16.74	18.11	17.14	18.46	18.83
	6H	17.71	18.97	18.12	19.34	19.73	17.20	18.47	17.62	18.84	19.23
	8H	17.85	19.06	18.27	19.45	19.85	17.35	18.56	17.77	18.95	19.34
	12H	17.94	19.10	18.37	19.48	19.91	17.43	18.59	17.86	18.97	19.40
4H	2H	15.40	16.77	15.80	17.12	17.49	15.05	16.42	15.45	16.76	17.14
	3H	17.38	18.52	17.78	18.92	19.32	16.97	18.11	17.38	18.51	18.91
	4H	18.15	19.19	18.58	19.60	20.04	17.73	18.76	18.16	19.18	19.61
	6H	18.75	19.65	19.20	20.09	20.55	18.32	19.22	18.77	19.66	20.12
	8H	18.94	19.78	19.40	20.23	20.69	18.50	19.35	18.96	19.79	20.25
	12H	19.07	19.83	19.55	20.31	20.77	18.62	19.38	19.10	19.85	20.32
8H	4H	18.43	19.27	18.89	19.71	20.18	18.05	18.90	18.51	19.34	19.81
	6H	19.14	19.84	19.63	20.33	20.81	18.76	19.46	19.25	19.95	20.42
	8H	19.40	20.03	19.91	20.54	21.02	19.01	19.64	19.52	20.14	20.63
	12H	19.60	20.16	20.11	20.65	21.21	19.19	19.74	19.69	20.23	20.80
12H	4H	18.45	19.21	18.93	19.69	20.16	18.09	18.85	18.57	19.32	19.79
	6H	19.18	19.82	19.69	20.32	20.81	18.82	19.45	19.33	19.95	20.44
	8H	19.50	20.06	20.01	20.55	21.11	19.12	19.68	19.63	20.17	20.73