

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930920

Luminaire Tested: DFN2DS-SQ3F0-040DS950-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930920
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-040DS950-RLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3213.0 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 38.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930920

CATALOG NUMBER: DFN2DS-SQ3F0-040DS950-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P930920

CATALOG NUMBER: DFN2DS-SQ3F0-040DS950-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1790	1790	1790
5°	1797	1768	1777
10°	1783	1739	1724
15°	1763	1687	1639
20°	1734	1614	1532
25°	1705	1530	1430
30°	1665	1444	1298
35°	1626	1351	1183
40°	1586	1254	1049
45°	1540	1146	928
50°	1492	1036	809
55°	1443	918	695
60°	1387	794	577
65°	1323	667	525
70°	1246	549	483
75°	1151	501	451
80°	1016	447	411
85°	799	352	352

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1540 cd/sqm

TEST NUMBER: P930920

CATALOG NUMBER: DFN2DS-SQ3F0-040DS950-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.4	4.6
10°-20°	401.9	12.5
20°-30°	564.3	17.6
30°-40°	615.1	19.1
40°-50°	565.4	17.6
50°-60°	444.0	13.8
60°-70°	289.0	9.0
70°-80°	148.8	4.6
80°-90°	38.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1112.7	34.6
0°-40°	1727.8	53.8
0°-60°	2737.2	85.2
0°-90°	3213.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3213.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1562	1562	1562	1562	1562	
5°	1562	1555	1537	1550	1545	148
15°	1486	1470	1422	1396	1381	419
25°	1349	1304	1210	1152	1131	620
35°	1162	1090	966	877	845	727
45°	950	855	707	606	573	734
55°	722	612	460	375	348	646
65°	488	373	246	198	194	484
75°	260	161	113	103	102	275
85°	61	31	27	27	27	73
90°	0	0	0	0	0	

TEST NUMBER: P930920

CATALOG NUMBER: DFN2DS-SQ3F0-040DS950-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1562.3	1562.3	1562.3	1562.3	1562.3
2.5°	1569.4	1562.3	1546.7	1561.0	1558.0
5°	1562.3	1555.2	1536.8	1549.5	1545.4
7.5°	1549.5	1541.1	1521.4	1526.8	1519.8
10°	1532.6	1522.7	1494.4	1490.1	1481.8
12.5°	1511.4	1498.7	1460.4	1452.0	1436.4
15°	1485.9	1470.3	1422.3	1395.5	1381.4
17.5°	1456.2	1433.6	1374.1	1343.1	1320.4
20°	1422.3	1394.0	1323.3	1288.0	1256.8
22.5°	1385.6	1353.1	1270.9	1222.9	1201.9
25°	1348.8	1303.5	1210.2	1152.3	1131.0
27.5°	1305.0	1256.8	1153.7	1087.2	1054.6
30°	1258.4	1204.5	1091.4	1019.4	981.2
32.5°	1213.1	1148.0	1032.1	947.3	911.8
35°	1162.3	1090.1	965.7	876.6	845.4
37.5°	1112.7	1034.9	903.4	805.8	770.6
40°	1060.4	975.6	838.4	738.0	701.3
42.5°	1006.6	916.2	773.4	668.7	633.4
45°	950.1	855.3	707.0	606.5	572.6
47.5°	896.4	796.1	643.4	542.9	511.8
50°	837.0	736.6	581.1	483.5	453.9
52.5°	779.0	672.9	521.7	428.4	401.5
55°	722.5	612.2	459.5	374.7	347.9
57.5°	664.5	551.4	404.4	325.2	302.6
60°	605.1	492.0	346.3	274.3	251.7
62.5°	547.2	434.1	296.8	229.1	217.8
65°	487.8	373.2	246.0	198.0	193.6
67.5°	431.3	316.7	198.0	173.9	169.6
70°	371.9	261.6	164.0	149.9	144.1
72.5°	315.3	210.6	137.1	125.9	123.0
75°	260.1	161.1	113.1	103.2	101.9
77.5°	205.1	114.4	89.1	83.4	80.5
80°	154.0	82.0	67.8	62.3	62.3
82.5°	107.4	55.2	46.7	43.8	43.8
85°	60.8	31.1	26.8	26.8	26.8
87.5°	22.7	11.2	11.2	9.9	9.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930920

CATALOG NUMBER: DFN2DS-SQ3F0-040DS950-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.26	14.78	13.62	15.09	15.41	9.22	10.74	9.58	11.05	11.37
	3H	15.02	16.39	15.40	16.72	17.08	10.48	11.85	10.86	12.18	12.54
	4H	15.69	16.97	16.09	17.32	17.70	10.99	12.27	11.39	12.61	12.99
	6H	16.18	17.36	16.59	17.73	18.12	11.37	12.55	11.78	12.92	13.31
	8H	16.34	17.47	16.77	17.86	18.26	11.49	12.62	11.92	13.01	13.41
	12H	16.45	17.53	16.88	17.91	18.34	11.57	12.65	12.00	13.03	13.46
4H	2H	13.36	14.64	13.76	14.99	15.37	9.91	11.19	10.31	11.54	11.92
	3H	15.30	16.36	15.71	16.76	17.16	11.36	12.42	11.77	12.82	13.22
	4H	16.04	17.00	16.48	17.42	17.86	11.96	12.91	12.39	13.33	13.77
	6H	16.64	17.47	17.09	17.91	18.37	12.45	13.28	12.90	13.72	14.18
	8H	16.85	17.63	17.31	18.07	18.54	12.61	13.38	13.07	13.83	14.30
	12H	17.00	17.70	17.49	18.18	18.65	12.72	13.42	13.21	13.90	14.37
8H	4H	16.07	16.85	16.53	17.29	17.76	12.31	13.09	12.77	13.53	14.00
	6H	16.71	17.35	17.20	17.84	18.32	12.90	13.54	13.39	14.03	14.51
	8H	16.96	17.53	17.47	18.04	18.53	13.12	13.69	13.63	14.20	14.69
	12H	17.16	17.67	17.67	18.16	18.73	13.30	13.81	13.81	14.30	14.86
12H	4H	16.05	16.75	16.54	17.23	17.70	12.35	13.05	12.84	13.53	14.00
	6H	16.69	17.26	17.20	17.77	18.26	12.96	13.54	13.47	14.05	14.54
	8H	16.97	17.48	17.48	17.97	18.54	13.23	13.74	13.74	14.24	14.80