

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P930991

Luminaire Tested: DFN2DS-SQ3F0-080DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P930991
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-080DS950-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7484.4 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 82
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P930991

CATALOG NUMBER: DFN2DS-SQ3F0-080DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P930991

CATALOG NUMBER: DFN2DS-SQ3F0-080DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3370	3370	3370
5°	3383	3335	3354
10°	3363	3301	3317
15°	3322	3258	3255
20°	3263	3194	3191
25°	3204	3115	3115
30°	3129	3043	3016
35°	3058	2956	2912
40°	2970	2868	2813
45°	2883	2782	2714
50°	2788	2692	2597
55°	2690	2588	2492
60°	2580	2463	2372
65°	2462	2339	2232
70°	2312	2189	2085
75°	2103	2016	1966
80°	1867	1810	1717
85°	1524	1453	1302

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2883 cd/sqm

TEST NUMBER: P930991

CATALOG NUMBER: DFN2DS-SQ3F0-080DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.9	3.7
10°-20°	779.0	10.4
20°-30°	1144.8	15.3
30°-40°	1329.6	17.8
40°-50°	1328.0	17.7
50°-60°	1158.0	15.5
60°-70°	856.0	11.4
70°-80°	484.3	6.5
80°-90°	127.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2200.7	29.4
0°-40°	3530.3	47.2
0°-60°	6016.3	80.4
0°-90°	7484.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7484.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2942	2942	2942	2942	2942	
5°	2942	2930	2899	2922	2916	279
15°	2800	2784	2746	2758	2744	789
25°	2534	2512	2464	2469	2464	1166
35°	2186	2158	2113	2096	2082	1365
45°	1779	1760	1717	1686	1675	1373
55°	1346	1329	1296	1262	1248	1204
65°	908	891	863	837	823	898
75°	475	470	455	438	444	507
85°	116	113	110	102	99	136
90°	0	0	0	0	0	

TEST NUMBER: P930991

CATALOG NUMBER: DFN2DS-SQ3F0-080DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2941.6	2941.6	2941.6	2941.6	2941.6
2.5°	2958.7	2944.6	2913.4	2941.6	2936.2
5°	2941.6	2930.5	2899.4	2921.8	2916.5
7.5°	2921.8	2905.0	2873.8	2896.6	2890.9
10°	2890.9	2871.1	2837.2	2859.7	2851.3
12.5°	2848.3	2831.5	2797.6	2811.7	2806.0
15°	2800.3	2783.5	2746.5	2758.0	2743.9
17.5°	2740.9	2724.1	2687.1	2701.3	2687.1
20°	2675.8	2658.9	2619.4	2627.8	2616.6
22.5°	2610.9	2585.4	2548.5	2548.5	2542.8
25°	2534.4	2511.9	2463.9	2469.3	2463.9
27.5°	2449.4	2429.7	2393.0	2384.6	2370.5
30°	2364.9	2342.0	2299.8	2291.3	2279.9
32.5°	2274.2	2257.4	2212.1	2195.0	2183.6
35°	2186.5	2158.4	2113.0	2095.9	2081.8
37.5°	2087.5	2062.0	2016.7	1996.9	1982.8
40°	1985.8	1963.0	1917.7	1892.5	1881.0
42.5°	1886.8	1863.9	1818.9	1790.4	1773.7
45°	1779.3	1759.5	1716.9	1686.0	1674.6
47.5°	1674.6	1654.8	1609.4	1578.2	1561.4
50°	1564.2	1550.1	1510.4	1470.8	1456.7
52.5°	1456.7	1436.9	1400.3	1369.1	1349.3
55°	1346.5	1329.4	1295.6	1261.7	1247.5
57.5°	1236.2	1222.1	1185.1	1151.2	1139.8
60°	1125.7	1114.6	1074.9	1043.8	1035.3
62.5°	1018.2	998.5	970.2	942.1	930.6
65°	908.1	891.0	862.8	837.3	823.2
67.5°	794.9	780.6	755.3	735.6	724.2
70°	690.2	678.8	653.4	633.5	622.4
72.5°	582.8	571.4	557.3	537.5	529.1
75°	475.1	469.7	455.3	438.5	444.2
77.5°	379.0	367.6	361.9	353.5	345.1
80°	283.0	280.0	274.3	265.9	260.2
82.5°	192.4	192.4	189.7	178.2	178.2
85°	115.9	113.1	110.5	101.8	99.0
87.5°	51.0	45.4	39.6	31.2	28.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P930991

CATALOG NUMBER: DFN2DS-SQ3F0-080DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.50	17.12	15.87	17.43	17.74	15.06	16.67	15.42	16.98	17.30
	3H	17.25	18.71	17.63	19.04	19.40	16.76	18.22	17.14	18.54	18.90
	4H	17.90	19.27	18.30	19.62	19.99	17.41	18.77	17.80	19.12	19.50
	6H	18.37	19.64	18.78	20.00	20.39	17.87	19.14	18.28	19.50	19.89
	8H	18.51	19.72	18.94	20.11	20.51	18.01	19.22	18.43	19.61	20.01
	12H	18.60	19.76	19.03	20.14	20.57	18.09	19.25	18.52	19.63	20.06
4H	2H	16.06	17.43	16.46	17.78	18.16	15.71	17.08	16.11	17.43	17.80
	3H	18.04	19.19	18.45	19.58	19.98	17.63	18.78	18.04	19.18	19.58
	4H	18.82	19.85	19.25	20.27	20.70	18.39	19.43	18.82	19.84	20.28
	6H	19.41	20.32	19.87	20.76	21.21	18.98	19.89	19.43	20.33	20.78
	8H	19.60	20.45	20.06	20.89	21.36	19.16	20.01	19.62	20.45	20.92
	12H	19.73	20.49	20.21	20.97	21.44	19.28	20.04	19.76	20.52	20.99
8H	4H	19.09	19.94	19.55	20.38	20.84	18.72	19.56	19.18	20.00	20.47
	6H	19.80	20.51	20.30	21.00	21.47	19.42	20.13	19.92	20.61	21.09
	8H	20.06	20.69	20.57	21.20	21.69	19.67	20.30	20.18	20.81	21.29
	12H	20.26	20.82	20.77	21.31	21.87	19.85	20.41	20.36	20.90	21.46
12H	4H	19.12	19.88	19.60	20.35	20.82	18.75	19.51	19.23	19.99	20.46
	6H	19.85	20.48	20.36	20.99	21.47	19.48	20.11	19.99	20.62	21.11
	8H	20.16	20.72	20.67	21.21	21.77	19.79	20.34	20.29	20.83	21.39