

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931009

Luminaire Tested: DFN2DS-SQ3F0-090DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ3F0-090DS950-FLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8420.0 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.06' x L: 3.06' x H: 0')
CIE Type: Direct

Input Watts (W): 93.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931009

CATALOG NUMBER: DFN2DS-SQ3F0-090DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931009

CATALOG NUMBER: DFN2DS-SQ3F0-090DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3792	3792	3792
5°	3806	3752	3774
10°	3784	3714	3732
15°	3737	3665	3662
20°	3670	3593	3589
25°	3605	3504	3504
30°	3520	3423	3394
35°	3441	3325	3276
40°	3341	3227	3165
45°	3244	3130	3053
50°	3137	3029	2921
55°	3026	2912	2804
60°	2902	2771	2669
65°	2770	2631	2511
70°	2601	2462	2346
75°	2366	2268	2212
80°	2101	2036	1932
85°	1713	1634	1465

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3244 cd/sqm

TEST NUMBER: P931009

CATALOG NUMBER: DFN2DS-SQ3F0-090DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.5	3.7
10°-20°	876.4	10.4
20°-30°	1287.9	15.3
30°-40°	1495.9	17.8
40°-50°	1494.0	17.7
50°-60°	1302.7	15.5
60°-70°	963.0	11.4
70°-80°	544.8	6.5
80°-90°	143.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2475.8	29.4
0°-40°	3971.6	47.2
0°-60°	6768.3	80.4
0°-90°	8420.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8420.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3309	3309	3309	3309	3309	
5°	3309	3297	3262	3287	3281	314
15°	3150	3131	3090	3103	3087	887
25°	2851	2826	2772	2778	2772	1312
35°	2460	2428	2377	2358	2342	1536
45°	2002	1980	1932	1897	1884	1545
55°	1515	1496	1458	1419	1404	1354
65°	1022	1002	971	942	926	1010
75°	534	528	512	493	500	571
85°	130	127	124	114	111	153
90°	0	0	0	0	0	

TEST NUMBER: P931009

CATALOG NUMBER: DFN2DS-SQ3F0-090DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3309.3	3309.3	3309.3	3309.3	3309.3
2.5°	3328.6	3312.7	3277.6	3309.3	3303.2
5°	3309.3	3296.8	3261.8	3287.1	3280.9
7.5°	3287.1	3268.2	3233.0	3258.7	3252.3
10°	3252.3	3230.0	3191.8	3217.2	3207.7
12.5°	3204.3	3185.4	3147.3	3163.1	3156.8
15°	3150.3	3131.4	3089.9	3102.7	3086.8
17.5°	3083.4	3064.5	3023.1	3038.9	3023.1
20°	3010.2	2991.3	2946.7	2956.1	2943.7
22.5°	2937.2	2908.6	2867.0	2867.0	2860.6
25°	2851.2	2825.8	2771.9	2777.9	2771.9
27.5°	2755.6	2733.3	2692.2	2682.8	2666.9
30°	2660.5	2634.8	2587.1	2577.7	2564.9
32.5°	2558.5	2539.6	2488.6	2469.4	2456.5
35°	2459.9	2428.2	2377.1	2358.0	2342.1
37.5°	2348.5	2319.8	2268.8	2246.5	2230.7
40°	2234.0	2208.4	2157.3	2129.0	2116.2
42.5°	2122.6	2097.0	2046.3	2014.3	1995.4
45°	2001.7	1979.5	1931.5	1896.7	1884.0
47.5°	1884.0	1861.6	1810.6	1775.6	1756.7
50°	1759.7	1743.8	1699.2	1654.7	1638.8
52.5°	1638.8	1616.5	1575.3	1540.3	1518.0
55°	1514.9	1495.7	1457.5	1419.4	1403.5
57.5°	1390.7	1374.8	1333.3	1295.1	1282.3
60°	1266.4	1253.9	1209.3	1174.3	1164.8
62.5°	1145.5	1123.2	1091.5	1059.8	1047.0
65°	1021.6	1002.4	970.6	942.0	926.1
67.5°	894.3	878.2	849.7	827.5	814.7
70°	776.5	763.7	735.0	712.7	700.2
72.5°	655.6	642.8	626.9	604.7	595.3
75°	534.5	528.3	512.2	493.3	499.7
77.5°	426.4	413.6	407.2	397.8	388.3
80°	318.4	315.0	308.5	299.1	292.8
82.5°	216.4	216.4	213.4	200.5	200.5
85°	130.3	127.3	124.3	114.4	111.4
87.5°	57.4	50.9	44.6	35.2	31.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931009

CATALOG NUMBER: DFN2DS-SQ3F0-090DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.91	17.52	16.28	17.84	18.15	15.47	17.08	15.83	17.39	17.71
	3H	17.66	19.12	18.04	19.44	19.81	17.17	18.63	17.55	18.95	19.31
	4H	18.31	19.68	18.71	20.03	20.40	17.81	19.18	18.21	19.53	19.91
	6H	18.78	20.05	19.19	20.41	20.80	18.28	19.55	18.69	19.91	20.30
	8H	18.92	20.13	19.35	20.52	20.92	18.42	19.63	18.84	20.02	20.42
	12H	19.01	20.17	19.44	20.55	20.98	18.50	19.66	18.93	20.04	20.47
4H	2H	16.47	17.84	16.87	18.19	18.57	16.12	17.49	16.52	17.84	18.21
	3H	18.45	19.60	18.86	19.99	20.39	18.04	19.19	18.45	19.59	19.99
	4H	19.23	20.26	19.66	20.67	21.11	18.80	19.84	19.23	20.25	20.69
	6H	19.82	20.73	20.28	21.17	21.62	19.39	20.29	19.84	20.74	21.19
	8H	20.01	20.86	20.47	21.30	21.77	19.57	20.42	20.03	20.86	21.33
	12H	20.14	20.90	20.62	21.38	21.85	19.69	20.45	20.17	20.93	21.40
8H	4H	19.50	20.35	19.96	20.79	21.25	19.12	19.97	19.59	20.41	20.88
	6H	20.21	20.92	20.71	21.40	21.88	19.83	20.53	20.33	21.02	21.50
	8H	20.47	21.10	20.98	21.61	22.10	20.08	20.71	20.59	21.22	21.70
	12H	20.67	21.23	21.18	21.72	22.28	20.26	20.82	20.77	21.31	21.87
12H	4H	19.52	20.28	20.00	20.76	21.23	19.16	19.92	19.64	20.40	20.87
	6H	20.26	20.89	20.77	21.40	21.88	19.89	20.52	20.40	21.03	21.51
	8H	20.57	21.13	21.08	21.62	22.18	20.19	20.75	20.70	21.24	21.80