

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333992

Luminaire Tested: **S123DS-S775D835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333992
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-11)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DS-S775D835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT LED LUMINAIRE, FLUSH SATIN WHITE DIFFUSER
PENDANT/SURFACE/WALL MOUNT, 775 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3026.8 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 26.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333992

CATALOG NUMBER: S123DS-S775D835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333992

CATALOG NUMBER: S123DS-S775D835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92		94	91	89		90	88	86	84
2	99	91	84	79	97	89	83	78	86	80	76		82	78	74		79	76	72	70
3	91	80	72	66	88	79	71	65	76	69	64		73	67	63		70	66	62	59
4	83	71	62	56	81	70	62	55	67	60	55		65	59	54		63	58	53	51
5	76	64	55	48	74	63	54	48	60	53	47		58	52	47		57	51	46	44
6	71	57	49	42	69	56	48	42	55	47	42		53	46	41		51	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37		48	42	37		47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33		44	38	33		43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30		41	34	30		40	34	30	28
10	54	40	33	27	52	40	32	27	39	32	27		38	32	27		37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12518	12518	12518
5°	12577	12404	12491
10°	12493	12296	12373
15°	12347	12158	12180
20°	12176	11959	11970
25°	11948	11722	11699
30°	11696	11460	11373
35°	11432	11182	11038
40°	11157	10876	10707
45°	10854	10595	10336
50°	10550	10248	9964
55°	10153	9890	9590
60°	9752	9472	9171
65°	9398	9016	8736
70°	8875	8497	8120
75°	8110	7819	7486
80°	7314	7005	6943
85°	6422	6175	5928



TEST NUMBER: P333992

CATALOG NUMBER: S123DS-S775D835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.6	3.6
10°-20°	309.6	10.2
20°-30°	457.2	15.1
30°-40°	534.0	17.6
40°-50°	536.8	17.7
50°-60°	471.6	15.6
60°-70°	351.2	11.6
70°-80°	199.9	6.6
80°-90°	56.8	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	876.5	29.0
0°-40°	1410.5	46.6
0°-60°	2418.9	79.9
0°-90°	3026.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3026.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1163	1163	1163	1163	1163	
5°	1164	1159	1148	1158	1156	110
15°	1108	1104	1091	1099	1093	312
25°	1006	1000	987	988	985	463
35°	870	864	851	845	840	544
45°	713	709	696	684	679	550
55°	541	540	527	516	511	485
65°	369	364	354	346	343	364
75°	195	191	188	183	180	208
85°	52	50	50	48	48	59
90°	0	0	0	0	0	



TEST NUMBER: P333992

CATALOG NUMBER: S123DS-S775D835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1163	1163	1163	1163	1163
2.5°	1168	1164	1153	1163	1162
5°	1164	1159	1148	1158	1156
7.5°	1155	1150	1139	1148	1147
10°	1143	1138	1125	1134	1132
12.5°	1127	1123	1111	1117	1116
15°	1108	1104	1091	1099	1093
17.5°	1087	1082	1069	1075	1073
20°	1063	1057	1044	1048	1045
22.5°	1036	1030	1017	1020	1016
25°	1006	1000	987	988	985
27.5°	975	969	955	956	953
30°	941	936	922	922	915
32.5°	907	900	890	883	880
35°	870	864	851	845	840
37.5°	833	825	812	805	802
40°	794	788	774	766	762
42.5°	755	748	734	726	722
45°	713	709	696	684	679
47.5°	672	666	654	642	638
50°	630	625	612	601	595
52.5°	586	583	569	560	554
55°	541	540	527	516	511
57.5°	499	495	485	475	469
60°	453	452	440	431	426
62.5°	412	409	397	388	385
65°	369	364	354	346	343
67.5°	323	319	311	304	300
70°	282	276	270	263	258
72.5°	239	235	228	222	220
75°	195	191	188	183	180
77.5°	156	154	150	146	146
80°	118	115	113	112	112
82.5°	81	81	81	79	78
85°	52	50	50	48	48
87.5°	26	23	22	21	21
90°	0	0	0	0	0

(END OF REPORT)