

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P334012

Luminaire Tested: **S123DS-S775D935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P334012  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DS-S775D935-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT LED LUMINAIRE, FLUSH SATIN WHITE DIFFUSER  
PENDANT/SURFACE/WALL MOUNT, 775 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2606.0 lumens  
Efficiency: N/A  
Efficacy: 99.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 26.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P334012

CATALOG NUMBER: S123DS-S775D935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P334012

CATALOG NUMBER: S123DS-S775D935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	70
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	59
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	51
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	44
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	28
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10778	10778	10778
5°	10829	10680	10754
10°	10756	10587	10653
15°	10631	10467	10487
20°	10483	10297	10306
25°	10288	10093	10073
30°	10070	9866	9792
35°	9843	9628	9503
40°	9605	9364	9219
45°	9345	9123	8899
50°	9083	8823	8579
55°	8741	8514	8257
60°	8396	8155	7896
65°	8092	7763	7521
70°	7641	7317	6990
75°	6983	6733	6446
80°	6298	6031	5976
85°	5533	5311	5101



TEST NUMBER: P334012

CATALOG NUMBER: S123DS-S775D935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.4	3.6
10°-20°	266.5	10.2
20°-30°	393.7	15.1
30°-40°	459.8	17.6
40°-50°	462.2	17.7
50°-60°	406.0	15.6
60°-70°	302.4	11.6
70°-80°	172.1	6.6
80°-90°	48.9	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	754.6	29.0
0°-40°	1214.4	46.6
0°-60°	2082.6	79.9
0°-90°	2606.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2606.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1001	1001	1001	1001	1001	
5°	1002	998	988	997	995	95
15°	954	950	939	946	941	269
25°	866	861	850	851	848	399
35°	749	744	733	728	723	469
45°	614	610	599	589	585	474
55°	466	465	454	444	440	417
65°	318	313	305	298	295	313
75°	168	164	162	158	155	179
85°	45	43	43	41	41	51
90°	0	0	0	0	0	



TEST NUMBER: P334012

CATALOG NUMBER: S123DS-S775D935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1001.3	1001.3	1001.3	1001.3	1001.3
2.5°	1005.6	1002.2	992.7	1001.3	1000.5
5°	1002.2	997.9	988.4	997.0	995.3
7.5°	994.5	990.1	980.7	988.4	987.6
10°	984.1	979.8	968.6	976.4	974.7
12.5°	970.3	966.9	956.6	961.7	960.9
15°	954.0	950.5	939.3	946.2	941.1
17.5°	935.9	931.6	920.4	925.6	923.9
20°	915.2	910.1	898.9	902.3	899.7
22.5°	892.0	886.8	875.6	878.2	874.8
25°	866.2	861.0	849.8	850.7	848.1
27.5°	839.5	834.3	822.3	823.1	820.5
30°	810.2	805.9	793.8	793.8	787.8
32.5°	780.9	774.9	766.3	760.3	757.7
35°	749.1	743.9	732.7	727.5	723.2
37.5°	717.2	710.3	699.1	693.1	690.5
40°	683.6	678.5	666.4	659.5	656.1
42.5°	650.1	644.0	632.0	625.1	621.6
45°	613.9	610.4	599.3	588.9	584.6
47.5°	578.6	573.4	563.1	552.8	549.3
50°	542.4	538.1	526.9	517.5	512.3
52.5°	504.5	502.0	489.9	482.2	477.0
55°	465.8	464.9	453.7	444.3	440.0
57.5°	429.6	426.2	417.6	409.0	403.8
60°	390.0	389.2	378.8	371.1	366.8
62.5°	354.7	352.1	341.8	334.1	331.5
65°	317.7	313.4	304.8	297.9	295.3
67.5°	278.1	274.7	267.8	261.7	258.3
70°	242.8	237.6	232.5	226.4	222.1
72.5°	205.8	202.3	196.3	191.1	189.4
75°	167.9	164.5	161.9	157.6	155.0
77.5°	134.3	132.6	129.1	125.7	125.7
80°	101.6	99.0	97.3	96.4	96.4
82.5°	69.7	69.7	69.7	68.0	67.2
85°	44.8	43.0	43.0	41.3	41.3
87.5°	22.4	19.8	18.9	18.1	18.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)