

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931089

Luminaire Tested: DFN2DS-SQ4F0-070DS850-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931089
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-070DS850-FLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7685.4 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 69.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931089

CATALOG NUMBER: DFN2DS-SQ4F0-070DS850-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931089

CATALOG NUMBER: DFN2DS-SQ4F0-070DS850-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2119	2119	2119
5°	2128	2097	2109
10°	2115	2076	2086
15°	2089	2049	2047
20°	2052	2008	2006
25°	2015	1959	1959
30°	1968	1913	1897
35°	1923	1859	1831
40°	1868	1804	1769
45°	1813	1749	1706
50°	1753	1693	1633
55°	1692	1628	1567
60°	1622	1549	1492
65°	1548	1471	1403
70°	1454	1376	1311
75°	1322	1267	1237
80°	1174	1138	1080
85°	958	914	819

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1813 cd/sqm

TEST NUMBER: P931089

CATALOG NUMBER: DFN2DS-SQ4F0-070DS850-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.3	3.7
10°-20°	799.9	10.4
20°-30°	1175.6	15.3
30°-40°	1365.3	17.8
40°-50°	1363.6	17.7
50°-60°	1189.1	15.5
60°-70°	879.0	11.4
70°-80°	497.3	6.5
80°-90°	131.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2259.8	29.4
0°-40°	3625.1	47.2
0°-60°	6177.8	80.4
0°-90°	7685.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7685.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3021	3021	3021	3021	3021	
5°	3021	3009	2977	3000	2995	287
15°	2876	2858	2820	2832	2818	810
25°	2602	2579	2530	2536	2530	1198
35°	2245	2216	2170	2152	2138	1402
45°	1827	1807	1763	1731	1720	1410
55°	1383	1365	1330	1296	1281	1236
65°	933	915	886	860	845	922
75°	488	482	467	450	456	521
85°	119	116	114	104	102	140
90°	0	0	0	0	0	

TEST NUMBER: P931089

CATALOG NUMBER: DFN2DS-SQ4F0-070DS850-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3020.6	3020.6	3020.6	3020.6	3020.6
2.5°	3038.2	3023.7	2991.6	3020.6	3015.0
5°	3020.6	3009.3	2977.2	3000.3	2994.7
7.5°	3000.3	2983.0	2950.9	2974.4	2968.6
10°	2968.6	2948.2	2913.3	2936.5	2927.9
12.5°	2924.8	2907.6	2872.8	2887.2	2881.3
15°	2875.5	2858.2	2820.3	2832.1	2817.5
17.5°	2814.4	2797.2	2759.3	2773.8	2759.3
20°	2747.5	2730.4	2689.7	2698.3	2686.9
22.5°	2681.0	2654.8	2616.9	2616.9	2611.0
25°	2602.5	2579.3	2530.1	2535.6	2530.1
27.5°	2515.2	2494.9	2457.3	2448.7	2434.1
30°	2428.4	2404.9	2361.5	2352.9	2341.1
32.5°	2335.2	2318.0	2271.5	2253.9	2242.2
35°	2245.3	2216.3	2169.8	2152.2	2137.7
37.5°	2143.6	2117.4	2070.8	2050.5	2036.0
40°	2039.1	2015.7	1969.1	1943.3	1931.5
42.5°	1937.4	1914.0	1867.8	1838.5	1821.2
45°	1827.1	1806.8	1763.0	1731.3	1719.5
47.5°	1719.5	1699.2	1652.6	1620.6	1603.4
50°	1606.2	1591.6	1550.9	1510.3	1495.8
52.5°	1495.8	1475.5	1437.9	1405.9	1385.5
55°	1382.7	1365.2	1330.4	1295.5	1281.0
57.5°	1269.4	1254.8	1216.9	1182.1	1170.4
60°	1155.9	1144.5	1103.9	1071.8	1063.2
62.5°	1045.6	1025.3	996.3	967.4	955.6
65°	932.6	914.9	886.0	859.8	845.3
67.5°	816.3	801.6	775.6	755.3	743.6
70°	708.8	697.1	670.8	650.5	639.1
72.5°	598.4	586.8	572.2	551.9	543.3
75°	487.8	482.3	467.4	450.3	456.1
77.5°	389.3	377.5	371.6	363.0	354.4
80°	290.6	287.6	281.7	273.0	267.2
82.5°	197.5	197.5	194.7	183.1	183.1
85°	119.0	116.2	113.5	104.5	101.7
87.5°	52.3	46.6	40.7	32.1	28.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931089

CATALOG NUMBER: DFN2DS-SQ4F0-070DS850-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.89	15.50	14.26	15.82	16.13	13.45	15.06	13.81	15.37	15.69
	3H	15.64	17.10	16.02	17.42	17.78	15.15	16.61	15.53	16.93	17.29
	4H	16.29	17.66	16.69	18.01	18.38	15.79	17.16	16.19	17.51	17.89
	6H	16.76	18.03	17.17	18.39	18.78	16.26	17.53	16.67	17.89	18.28
	8H	16.90	18.11	17.33	18.50	18.90	16.40	17.61	16.82	18.00	18.40
	12H	16.99	18.15	17.42	18.53	18.96	16.48	17.64	16.91	18.02	18.45
4H	2H	14.45	15.82	14.85	16.17	16.55	14.10	15.47	14.50	15.82	16.19
	3H	16.43	17.57	16.84	17.97	18.37	16.02	17.17	16.43	17.57	17.97
	4H	17.20	18.24	17.64	18.65	19.09	16.78	17.82	17.21	18.23	18.67
	6H	17.80	18.71	18.26	19.15	19.60	17.37	18.27	17.82	18.71	19.17
	8H	17.99	18.84	18.45	19.28	19.74	17.55	18.40	18.01	18.84	19.31
	12H	18.12	18.88	18.60	19.36	19.83	17.67	18.43	18.15	18.91	19.38
8H	4H	17.48	18.32	17.94	18.77	19.23	17.10	17.95	17.56	18.39	18.86
	6H	18.19	18.90	18.69	19.38	19.86	17.81	18.51	18.30	19.00	19.48
	8H	18.45	19.08	18.96	19.59	20.08	18.06	18.69	18.57	19.20	19.68
	12H	18.65	19.21	19.16	19.70	20.26	18.24	18.80	18.75	19.29	19.85
12H	4H	17.50	18.26	17.98	18.74	19.21	17.14	17.90	17.62	18.37	18.84
	6H	18.24	18.87	18.75	19.38	19.86	17.87	18.50	18.38	19.01	19.49
	8H	18.55	19.11	19.06	19.60	20.16	18.17	18.73	18.68	19.22	19.78