

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931150

Luminaire Tested: DFN2DS-SQ4F0-100DS935-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-SQ4F0-100DS935-RLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7310.0 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.92' x L: 3.92' x H: 0')
CIE Type: Direct

Input Watts (W): 100.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931150

CATALOG NUMBER: DFN2DS-SQ4F0-100DS935-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931150

CATALOG NUMBER: DFN2DS-SQ4F0-100DS935-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2494	2494	2494
5°	2504	2463	2476
10°	2484	2423	2402
15°	2456	2351	2283
20°	2416	2248	2135
25°	2376	2132	1992
30°	2320	2012	1809
35°	2265	1882	1648
40°	2210	1747	1461
45°	2145	1596	1293
50°	2079	1443	1127
55°	2011	1279	968
60°	1932	1106	804
65°	1843	929	732
70°	1736	765	673
75°	1604	698	628
80°	1416	623	572
85°	1113	492	492

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2145 cd/sqm

TEST NUMBER: P931150

CATALOG NUMBER: DFN2DS-SQ4F0-100DS935-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	333.1	4.6
10°-20°	914.5	12.5
20°-30°	1283.9	17.6
30°-40°	1399.5	19.1
40°-50°	1286.3	17.6
50°-60°	1010.2	13.8
60°-70°	657.6	9.0
70°-80°	338.5	4.6
80°-90°	86.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2531.5	34.6
0°-40°	3931.0	53.8
0°-60°	6227.6	85.2
0°-90°	7310.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7310.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3554	3554	3554	3554	3554	
5°	3554	3538	3496	3525	3516	337
15°	3381	3345	3236	3175	3143	953
25°	3069	2966	2753	2622	2573	1411
35°	2644	2480	2197	1994	1923	1655
45°	2162	1946	1608	1380	1303	1669
55°	1644	1393	1045	852	791	1469
65°	1110	849	560	450	441	1100
75°	592	366	257	235	232	626
85°	138	71	61	61	61	166
90°	0	0	0	0	0	

TEST NUMBER: P931150

CATALOG NUMBER: DFN2DS-SQ4F0-100DS935-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3554.4	3554.4	3554.4	3554.4	3554.4
2.5°	3570.4	3554.4	3518.9	3551.3	3544.8
5°	3554.4	3538.3	3496.3	3525.4	3515.8
7.5°	3525.4	3506.2	3461.2	3473.8	3457.8
10°	3486.8	3464.3	3400.1	3390.2	3371.1
12.5°	3438.7	3409.6	3322.6	3303.5	3268.0
15°	3380.7	3345.1	3235.9	3174.9	3142.8
17.5°	3313.1	3261.5	3126.4	3055.8	3004.2
20°	3235.9	3171.4	3010.7	2930.5	2859.5
22.5°	3152.3	3078.3	2891.6	2782.4	2734.3
25°	3068.7	2965.7	2753.4	2621.6	2573.2
27.5°	2969.1	2859.5	2624.7	2473.5	2399.5
30°	2862.9	2740.4	2483.1	2319.3	2232.3
32.5°	2759.9	2611.7	2348.3	2155.2	2074.6
35°	2644.2	2480.1	2197.1	1994.4	1923.4
37.5°	2531.6	2354.4	2055.5	1833.3	1753.1
40°	2412.5	2219.7	1907.4	1679.1	1595.5
42.5°	2290.3	2084.5	1759.6	1521.4	1441.2
45°	2161.6	1945.9	1608.5	1379.8	1302.6
47.5°	2039.5	1811.2	1463.7	1235.0	1164.4
50°	1904.3	1676.0	1322.1	1099.9	1032.7
52.5°	1772.2	1531.0	1187.0	974.6	913.6
55°	1643.5	1392.8	1045.3	852.5	791.4
57.5°	1511.9	1254.5	920.1	739.9	688.3
60°	1376.7	1119.4	788.0	624.2	572.7
62.5°	1244.9	987.6	675.4	521.2	495.5
65°	1109.8	849.1	559.7	450.5	440.6
67.5°	981.2	720.4	450.5	395.5	386.0
70°	846.0	595.2	373.0	340.9	328.0
72.5°	717.3	479.1	311.9	286.3	279.8
75°	591.8	366.5	257.3	234.8	231.7
77.5°	466.6	260.4	202.7	189.7	183.3
80°	350.4	186.7	154.3	141.6	141.6
82.5°	244.3	125.6	106.1	99.7	99.7
85°	138.2	70.6	61.1	61.1	61.1
87.5°	51.5	25.6	25.6	22.5	22.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931150

CATALOG NUMBER: DFN2DS-SQ4F0-100DS935-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.41	15.93	14.77	16.25	16.56	10.37	11.89	10.74	12.21	12.52
	3H	16.18	17.54	16.55	17.87	18.23	11.64	13.00	12.01	13.33	13.69
	4H	16.84	18.12	17.24	18.47	18.85	12.14	13.42	12.54	13.77	14.15
	6H	17.33	18.51	17.74	18.88	19.27	12.52	13.70	12.93	14.07	14.46
	8H	17.50	18.62	17.92	19.01	19.41	12.64	13.77	13.07	14.16	14.56
	12H	17.60	18.68	18.03	19.06	19.49	12.72	13.80	13.15	14.18	14.61
4H	2H	14.51	15.79	14.91	16.14	16.52	11.07	12.35	11.47	12.70	13.07
	3H	16.45	17.51	16.86	17.91	18.31	12.51	13.57	12.92	13.97	14.37
	4H	17.20	18.15	17.63	18.57	19.01	13.11	14.06	13.54	14.48	14.92
	6H	17.79	18.62	18.25	19.06	19.52	13.60	14.43	14.05	14.87	15.33
	8H	18.00	18.78	18.47	19.22	19.69	13.76	14.54	14.22	14.98	15.45
	12H	18.16	18.85	18.64	19.33	19.80	13.88	14.57	14.36	15.05	15.52
8H	4H	17.22	18.00	17.68	18.44	18.91	13.46	14.24	13.93	14.68	15.15
	6H	17.86	18.50	18.36	18.99	19.47	14.05	14.69	14.55	15.18	15.66
	8H	18.11	18.69	18.62	19.19	19.68	14.27	14.85	14.78	15.36	15.84
	12H	18.31	18.82	18.82	19.31	19.88	14.45	14.96	14.96	15.45	16.02
12H	4H	17.21	17.90	17.69	18.38	18.85	13.51	14.20	13.99	14.68	15.15
	6H	17.84	18.42	18.35	18.93	19.41	14.11	14.69	14.63	15.20	15.69
	8H	18.12	18.63	18.63	19.13	19.69	14.39	14.90	14.90	15.39	15.95