

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931232

Luminaire Tested: DFN2DS-TR2F0-020DS840-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR2F0-020DS840-RLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1701.7 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 2.36' x L: 2.04' x H: 0')
CIE Type: Direct

Input Watts (W): 17.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931232

CATALOG NUMBER: DFN2DS-TR2F0-020DS840-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931232

CATALOG NUMBER: DFN2DS-TR2F0-020DS840-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1845	1845	1845
5°	1853	1822	1832
10°	1838	1793	1777
15°	1817	1739	1689
20°	1788	1664	1580
25°	1758	1577	1474
30°	1717	1489	1338
35°	1676	1393	1219
40°	1635	1293	1081
45°	1587	1181	956
50°	1538	1068	834
55°	1488	946	716
60°	1430	819	595
65°	1364	688	541
70°	1284	566	498
75°	1187	516	465
80°	1048	461	423
85°	821	363	363

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1587 cd/sqm

TEST NUMBER: P931232

CATALOG NUMBER: DFN2DS-TR2F0-020DS840-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.5	4.6
10°-20°	212.9	12.5
20°-30°	298.9	17.6
30°-40°	325.8	19.1
40°-50°	299.4	17.6
50°-60°	235.2	13.8
60°-70°	153.1	9.0
70°-80°	78.8	4.6
80°-90°	20.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	589.3	34.6
0°-40°	915.1	53.8
0°-60°	1449.7	85.2
0°-90°	1701.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1701.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	827	824	814	821	818	78
15°	787	779	753	739	732	222
25°	714	690	641	610	599	329
35°	616	577	512	464	448	385
45°	503	453	374	321	303	389
55°	383	324	243	198	184	342
65°	258	198	130	105	103	256
75°	138	85	60	55	54	146
85°	32	16	14	14	14	39
90°	0	0	0	0	0	

TEST NUMBER: P931232

CATALOG NUMBER: DFN2DS-TR2F0-020DS840-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	827.4	827.4	827.4	827.4	827.4
2.5°	831.1	827.4	819.1	826.7	825.2
5°	827.4	823.7	813.9	820.7	818.4
7.5°	820.7	816.2	805.7	808.7	804.9
10°	811.7	806.4	791.5	789.2	784.8
12.5°	800.5	793.7	773.5	769.1	760.8
15°	787.0	778.7	753.3	739.0	731.6
17.5°	771.3	759.3	727.8	711.3	699.4
20°	753.3	738.2	700.9	682.2	665.7
22.5°	733.8	716.6	673.2	647.7	636.5
25°	714.4	690.4	640.9	610.3	599.0
27.5°	691.2	665.7	611.0	575.8	558.6
30°	666.5	637.9	578.1	539.9	519.6
32.5°	642.4	608.0	546.6	501.7	483.0
35°	615.5	577.4	511.5	464.3	447.7
37.5°	589.3	548.0	478.5	426.8	408.1
40°	561.6	516.7	444.0	390.9	371.4
42.5°	533.1	485.3	409.6	354.2	335.5
45°	503.2	453.0	374.5	321.2	303.2
47.5°	474.8	421.6	340.7	287.5	271.1
50°	443.3	390.2	307.8	256.1	240.4
52.5°	412.5	356.4	276.3	226.9	212.7
55°	382.6	324.2	243.3	198.5	184.2
57.5°	352.0	292.0	214.2	172.3	160.3
60°	320.5	260.6	183.5	145.3	133.3
62.5°	289.8	229.9	157.3	121.3	115.3
65°	258.4	197.7	130.3	104.9	102.6
67.5°	228.4	167.7	104.9	92.1	89.9
70°	196.9	138.5	86.8	79.4	76.4
72.5°	167.0	111.5	72.6	66.7	65.2
75°	137.7	85.3	59.9	54.7	54.0
77.5°	108.6	60.7	47.1	44.1	42.6
80°	81.6	43.4	35.9	32.9	32.9
82.5°	56.9	29.2	24.7	23.2	23.2
85°	32.1	16.4	14.2	14.2	14.2
87.5°	12.0	6.0	6.0	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931232

CATALOG NUMBER: DFN2DS-TR2F0-020DS840-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.36	14.88	13.73	15.20	15.51	9.33	10.85	9.69	11.16	11.48
	3H	15.13	16.49	15.51	16.82	17.18	10.59	11.96	10.97	12.28	12.65
	4H	15.79	17.07	16.19	17.42	17.80	11.09	12.37	11.49	12.72	13.10
	6H	16.28	17.47	16.70	17.83	18.22	11.47	12.66	11.89	13.02	13.41
	8H	16.45	17.58	16.88	17.97	18.37	11.60	12.72	12.02	13.11	13.51
	12H	16.55	17.63	16.98	18.01	18.44	11.68	12.76	12.11	13.14	13.57
4H	2H	13.47	14.75	13.87	15.10	15.48	10.02	11.30	10.42	11.65	12.03
	3H	15.40	16.46	15.81	16.86	17.26	11.47	12.53	11.88	12.93	13.33
	4H	16.15	17.11	16.58	17.52	17.96	12.06	13.02	12.50	13.44	13.88
	6H	16.74	17.57	17.20	18.02	18.48	12.55	13.38	13.01	13.83	14.29
	8H	16.96	17.73	17.42	18.18	18.64	12.71	13.49	13.18	13.93	14.40
	12H	17.11	17.80	17.59	18.28	18.75	12.83	13.52	13.31	14.00	14.47
8H	4H	16.17	16.95	16.64	17.39	17.86	12.42	13.20	12.88	13.64	14.11
	6H	16.81	17.45	17.31	17.94	18.42	13.00	13.64	13.50	14.14	14.61
	8H	17.06	17.64	17.58	18.15	18.64	13.22	13.80	13.74	14.31	14.80
	12H	17.27	17.77	17.77	18.27	18.83	13.40	13.91	13.91	14.40	14.97
12H	4H	16.16	16.85	16.64	17.33	17.80	12.46	13.16	12.94	13.63	14.11
	6H	16.79	17.37	17.31	17.88	18.37	13.07	13.64	13.58	14.15	14.64
	8H	17.08	17.59	17.59	18.08	18.64	13.34	13.85	13.85	14.34	14.91

END OF REPORT